

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0759000232

Status:

Active

Overview:

MX150™ Unshrouded Header

Description:

MX150 Single Row Header, Right-Angle, 3 Circuits, 1.25µm Nickel (Ni) Overall, 2.50µm Minimum Select Matte Tin (Sn) Plating on Tail, 0.05µm Minimum Select Gold (Au) Contact Area, 4.75mm PC Tail Length, Mating Pin Length 12.15mm

Documents:

3D Model

Product Specification PS-75757-000-001 (PDF)

Drawing (PDF)


Packaging Specification PK-36518-352 (PDF)

Product Specification PS-75757-000 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	75900
3D Viewer	Yes
Application	Power, Wire-to-Board
CURRENT-MAX-NUMERIC	17.0
Overview	MX150™ Unshrouded Header
PITCH-MATING-NUMERIC	3.50
Product Name	MX150
UPC	884982669673
Physical	
Breakaway	No
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.921/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	4.75mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	2.36mm
Packaging Type	Tube
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Plating min - Mating	2.540µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +125°C
Termination Interface: Style	Through Hole

Electrical



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/71/2019 (16 July 2019)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

75900 Series

Mates With

33471 Single Row MX150 Receptacles

Current - Maximum per Contact	17.0A
Voltage - Maximum	500V DC

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	245

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-36518-352
Product Specification	PS-75757-000, PS-75757-000-001
Sales Drawing	AS-75900-103, SD-75900-0001-001, SD-75900-002-001

This document was generated on 09/25/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION