

LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Sensor, thermocouple, Stainless Steel 310. Type K, Mineral Insulated,
1.0, 1.5, 3.0, & 6.0mm Diameters



- Mineral insulated K thermocouples
- Stainless steel (310) Sheath
- Very rugged and flexible
- Particularly suitable for high pressure, high vacuum or high vibration applications
- Max temperature of probe 1100°C (K)
- 8mm ISO pot seal (max temp 200°C)
- 7/0.2mm PTFE Insulated Lead 100mm Long

Dimensions		Farnell code	LAB code	Lab Data Ref	Lab Stock Code
Probe Dia	Probe Length				
mm	mm				
1.0	1000	TBA	MD-ISK-S10-1000-P5	FAR58/A	XF-515-D
1.5	2000	TBA	MD-ISK-S15-2000-P5	FAR58/B	XF-516-D
3.0	2000	TBA	MD-ISK-S30-2000-P5	FAR58/C	XF-517-D
6.0	1000	TBA	MD-ISK-S60-1000-P5	FAR58/D	XF-518-D
6.0	2000	TBA	MD-ISK-S60-2000-P5	FAR58/E	XF-519-D

Data Ref: FAR 58