




△ HOUSING MATERIAL: LIQUID CRYSTAL POLYMER
COLOR: NATURAL.

△ CONTACT MATERIAL: PHOSPHOR BRONZE PER UNS
ALLOY NO. C51100, TEMPER: H04.

△ CONTACT FINISH:(A)
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290
ON MATING SURFACES:
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT.
ON LEADS:
0.00381 MIN MATTE TIN PER ASTM B 545 OVER UNDERPLATE.
LUBRICATION (MIN MATING SURFACES):
SURFACE CONDITIONER AFTER PLATING.

△ PART MARKING PER TE SPEC 115-9009 LOCATED APPROXIMATELY
AS SHOWN BETWEEN RIBS/SLOTS ON EITHER SIDE OF HOUSING AT
MANUFACTURER'S DISCRETION.

△ PART TO BE MARKED WITH DATE CODE ONLY.

△ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

6	OBSOLETE	82	41	83.88		168	5223513-8	
		34	17	35.88		72	5223513-7	
6	OBSOLETE	58	29	59.88			120	5223513-6
		70	35	71.88			144	5223513-5
		94	47	95.88			192	5223513-4
		46	23	47.88			96	5223513-3
5		22	11	23.88			48	5223513-2
		10	5	11.88			24	5223513-1
		C	B	A	FINISH	NO OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.						DIN EN 60807-1	MCMMASTER	14DEG04	Tyco Electronics Corporation Harrisburg, PA 17105-3608		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		QW R.WERTZ	14DEG04	Tyco Electronics		NAME			
		0. PLC ± — 1. PLC ± — 2. PLC ± 0.13 3. PLC ± — 4. PLC ± — ANGLES ± —	APRO R.WERTZ	PRODUCT SPEC	14DEG04	ASSEMBLY, PIN, SIGNAL, RIGHT ANGLE, 4 ROW, Z-PACK 2mm FB					
MATERIAL FINISH				APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
				WEIGHT —	A1	00779	C=5223513				
CUSTOMER DRAWING						SCALE	4:1	SHEET	1 of 1	REV	A