







N=Number of poles



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

SIGN	DATE	DESCRIPTION	APPROVER
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	

- Material
- Terminal body (metal housing) : Steel stamping
 - Terminal screw : Steel Zinc plating "-" slot type
 - Contacts : Brass
 - Surface of solder tail : Tin plated
 - Insulator (housing) : Thermoplastic (UL94V-0)

- Electrical
- Voltage rating : 300V
 - Current rating : 57A
 - Wire range : Solid wire (AWG) : 8-22 Stranded wire (AWG) : 8-22
 - Torque (LB-In.) : 19
 - Screw : M4
 - Wire strip length : 10-11mm
 - Withstanding voltage : 1.6KV
 - Operating temperature : -30°C+105°C
 - Soldering temperature : 250°C+10°C/5 Sec
 - Safety Approval: US

RoHS Compliant

PART NUMBER:

OSTVPXX6585

No. of Poles	COLOR
02 2 Poles	0: Black
03 3 Poles	5: Green
... ..	6: Blue
12 12 Poles	8: Grey (Standard)



TITLE	OSTVP 10.16mm Series (double contact) with steel stamping, 2p-12p						
PART NO.	OSTVPXX6585			DWG NO.	OSTVPXX6585.DWG		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
Shi Jun 2006.10.23	Marvin 2006.10.23	Marvin 2006.10.23	Marvin 2006.10.23		UNIT: mm	Tolerance	
					SCALE: NONE	X. ±0.50	X.X ±0.30
						X.XX ±0.10	X° ±1°
				SHEET: 01/01	REV: F		