


PRELIMINARY DATA SHEET

AS202-321, AS202-321LF: PHEMT GaAs IC High-Power SP3T Switch LF–2 GHz

Features

- Positive low voltage control (0/2.75 V operation)
- Low insertion loss (< 0.8 dB @ 2 GHz)
- High isolation (25 dB at 1 and 2 GHz)
- Excellent harmonics performance
(–65 dBc @ 2.75 V 1 GHz, $P_{IN} = 34$ dBm)
- Miniature QFN-12 plastic package
- PHEMT process
- Available lead (Pb)-free and RoHS-compliant MSL-1 @ 260 °C per JEDEC J-STD-020

Functional Block Diagram

Description

The AS202-321 is a PHEMT GaAs IC SP3T antenna switch operating in the 900 MHz and 1800 MHz frequency bands. Switching between the antenna and Tx/Rx ports is accomplished with 3 control inputs. When the control inputs are driven with the appropriate voltages, a low insertion loss path is provided from an antenna port to an Rx or Tx port, while the other ports have high attenuation.

NEW

Skyworks offers lead (Pb)-free, RoHS (Restriction of Hazardous Substances)-compliant packaging.






Electrical Specifications at 25 °C (0, 2.75 V)

$Z_0 = 50 \Omega$, unless otherwise noted


Parameter		Frequency	Min.	Typ.	Max.	Unit
Insertion loss	Ant–RF1, RF2, RF3	LF–0.5 GHz		0.55	0.75	dB
		LF–1.0 GHz		0.60	0.80	dB
		LF–2.0 GHz		0.80	1.10	dB
Isolation	Ant–RF1, RF2, RF3	LF–0.5 GHz	25	28		dB
		LF–1.0 GHz	22	25		dB
		LF–2.0 GHz	22	25		dB
Return loss	Ant–RF1, RF2, RF3	LF–0.5 GHz		18		dB
		LF–1.0 GHz		18		dB
		LF–2.0 GHz		14		dB

Operating Characteristics at 25 °C (0, 2.75 V) **$Z_0 = 50 \Omega$, unless otherwise noted**

Parameter	Condition	Frequency	Min.	Typ.	Max.	Unit
2nd harmonic	34 dBm In @ 2.75 V	1 GHz		-72		dBc
3rd harmonic	34 dBm In @ 2.75 V	1 GHz		-65		dBc
2nd harmonic	32 dBm In @ 2.75 V	2 GHz		-70		dBc
3rd harmonic	32 dBm In @ 2.75 V	2 GHz		-65		dBc
Gate leakage current	34 dBm In @ 2.75 V				0.03	mA
Thermal resistance				25		°C/W
Control voltages	V_{HIGH} V_{LOW}		-0.25 2.60	0 2.75	0.25 5.00	V V


Typical Performance Data (0, 2.75 V, $C_{BL} = 47$ pF) **$Z_0 = 50 \Omega$, unless otherwise noted****Insertion Loss vs. Frequency****Isolation vs. Frequency****Return Loss vs. Frequency****2nd and 3rd Harmonics vs. Control Voltage**

Pin Out



LF blocks required. $C_{BL} = 47$ pF for operation >500 MHz.

QFN-12



Truth Table

V ₁	V ₂	V ₃	Ant-RF1	Ant-RF2	Ant-RF3
V _{HIGH}	V _{LOW}	V _{LOW}	Ins. loss	Isolation	Isolation
V _{LOW}	V _{HIGH}	V _{LOW}	Isolation	Ins. loss	Isolation
V _{LOW}	V _{LOW}	V _{HIGH}	Isolation	Isolation	Ins. loss

All other conditions not recommended.

V_{LOW} = 0–0.2 V.

V_{HIGH} = 2.75–5 V.

Absolute Maximum Ratings

Characteristic	Value
RF input power	4 W > 0.5 GHz 0/6 V control
Control voltage	6 V
Operating temperature	-40 °C to +85 °C
Storage temperature	-65 °C to +150 °C

Performance is guaranteed only under the conditions listed in the specifications table and is not guaranteed under the full range(s) described by the Absolute Maximum specifications. Exceeding any of the absolute maximum/minimum specifications may result in permanent damage to the device and will void the warranty.

CAUTION: Although this device is designed to be as robust as possible, ESD (Electrostatic Discharge) can damage this device. This device must be protected at all times from ESD. Static charges may easily produce potentials of several kilovolts on the human body or equipment, which can discharge without detection. Industry-standard ESD precautions must be employed at all times.

Recommended Solder Reflow Profiles

Refer to the [“Recommended Solder Reflow Profile”](#) Application Note.

Tape and Reel Information

Refer to the [“Discrete Devices and IC Switch/Attenuators Tape and Reel Package Orientation”](#) Application Note.

Copyright © 2002, 2003, 2004, 2005, 2006, Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of stated published specifications or parameters.

Skyworks, the Skyworks symbol, and "Breakthrough Simplicity" are trademarks or registered trademarks of Skyworks Solutions, Inc., in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.