

# TLS SERIES TELECOM POWER FUSE

170 Vdc • Current-Limiting • 1-125 A



## Description

Littelfuse TLS Series fuses are designed specifically for the protection of telecommunications equipment. TLS fuses have been engineered to operate up to 170 Vdc to provide current-limiting short-circuit protection for cables and components found in the DC power distribution circuits of telecommunications systems. The compact design and multiple mounting configurations of the TLS series allow it to be used in a variety of applications.

## Features

- 170 Vdc rating
- Current-limiting
- 1 to 125 amperes rating
- Multiple mounting configurations — Cartridge, Vertical, Leaded, Bolt-In, or Solder type. See dimensions on page 2 for mounting style details.
- RoHS Compliant

## Web Resources

For additional information, visit:

[littelfuse.com/tls](http://littelfuse.com/tls)

## Recommended Fuse Holders

LFTD series disconnect switches

LFT30060 for TLS series cartridge style fuse

Contact factory for more information.


## Specifications

<b>Voltage Rating</b>	170 Vdc
<b>Ampere Range</b>	1 – 125 A
<b>Interrupting Rating</b>	100 kA
<b>Approvals</b>	UL Recognized (File: E71611)
<b>Construction</b>	Body: Glass melamine Caps: Silver-plated brass
<b>Environmental</b>	RoHS Compliant, Lead (Pb) Free

## Ordering Information

AMPERE RATINGS				
1	6	25	50	90
2	10	30	60	100
3	15	35	70	110*
5	20	40	80	125*

\*Available in standard cartridge only.



### Mounting Options

Blank = Cartridge  
 XV = Vertical  
 XL = Leaded  
 LB = Bolt-In  
 LS = Solder  
 MB = Solder (Mid-Board Mount)

SERIES	AMP	Mounting Method	Mounting Suffix	Catalog Number	Ordering Number
TLS	6	Cartridge	—	TLS006	OTLS006.T
TLS	15	Vertical	V	TLS015V	OTLS015.TXV
TLS	35	Leaded	L	TLS035L	OTLS035.TXL
TLS	50	Bolt-In	LB	TLS050LB	OTLS050.TXLB
TLS	80	Solder	LS	TLS080LS	OTLS080.TXLS
TLS	100	Solder	MB	TLS100MB	OTLS100.TXMB

# TLS SERIES TELECOM POWER FUSE

## Dimensions Inches (mm)

