


CPR4-020
CPR4-040
CPR4-060

GLASS PASSIVATED
GENERAL PURPOSE RECTIFIER
3.0 AMP, 200 THRU 600 VOLTS



GPR-4AM CASE

CentralTM
Semiconductor Corp.

DESCRIPTION:

The CENTRAL SEMICONDUCTOR CPR4 Series are silicon rectifiers manufactured in a hermetically sealed, glass passivated package designed for use in all types of commercial, industrial, entertainment and automotive applications.

MARKING: FULL PART NUMBER

MAXIMUM RATINGS: ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

		CPR4			
	SYMBOL	-020	-040	-060	UNITS
Peak Repetitive Reverse Voltage	V_{RRM}	200	400	600	V
DC Blocking Voltage	V_R	200	400	600	V
RMS Reverse Voltage	$V_{R(RMS)}$	140	280	420	V
Average Forward Current ($T_A=70^{\circ}\text{C}$)	I_O		3.0		A
Peak Forward Surge Current, $t_p=8.3\text{ms}$	I_{FSM}		100		A
Operating and Storage Junction Temperature	T_J, T_{stg}		-65 to +175		$^{\circ}\text{C}$
Thermal Resistance	Θ_{JA}		55		$^{\circ}\text{C/W}$


ELECTRICAL CHARACTERISTICS: ($T_A=25^{\circ}\text{C}$ unless otherwise noted))

SYMBOL	TEST CONDITIONS	TYP	MAX	UNITS
I_R	$V_R=\text{Rated } V_{RRM}$		1.0	μA
I_R	$V_R=\text{Rated } V_{RRM}, T_A=100^{\circ}\text{C}$		100	μA
V_F	$I_F=3.0\text{A}$		1.1	V
C_J	$V_R=4.0\text{V}, f=1.0\text{MHz}$	40		pF
t_{rr}	$I_F=0.5\text{A}, I_R=1.0\text{A}, I_{rr}=0.25\text{A}$	3.0		μs

R0 (24-July 2008)

GLASS PASSIVATED
GENERAL PURPOSE RECTIFIER
3.0 AMP, 200 THRU 600 VOLTS

GPR-4AM CASE - MECHANICAL OUTLINE



DIMENSIONS				
SYMBOL	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.165	0.189	4.20	4.80
B	1.024	---	26.00	---
C	0.037	0.042	0.95	1.06
D	0.130	0.175	3.30	4.45

GPR-4AM (REV: R0)

MARKING CODE: FULL PART NUMBER

R0 (24-July 2008)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Central Semiconductor:](#)

[CPR4-020](#)