

1		2		3		4		5		6		7																																																																																																									
A	⑤ 300ft(91.44m)												A																																																																																																								
B													B																																																																																																								
C	0,95±0,1 A 1,27±0,07 B												C																																																																																																								
D													D																																																																																																								
E	<table><tr><th rowspan="2">Cores</th><th colspan="2">Size of conductor</th><th rowspan="2">A ②④</th><th rowspan="2">B ②④</th><th rowspan="2">Cores</th><th colspan="2">Size of conductor</th><th rowspan="2">A ②④</th><th rowspan="2">B ②④</th></tr><tr><th>AWG</th><th>Composition</th><th>AWG</th><th>Composition</th></tr><tr><td>09</td><td>28</td><td>7/0.127</td><td>10.16±0.25</td><td>11.43±0.25</td><td>25</td><td>28</td><td>7/0.127</td><td>30.48±0.35</td><td>31.75±0.35</td></tr><tr><td>10</td><td>28</td><td>7/0.127</td><td>11.43±0.25</td><td>12.70±0.25</td><td>26</td><td>28</td><td>7/0.127</td><td>31.75±0.35</td><td>33.02±0.35</td></tr><tr><td>12</td><td>28</td><td>7/0.127</td><td>13.97±0.25</td><td>15.24±0.25</td><td>30</td><td>28</td><td>7/0.127</td><td>36.83±0.38</td><td>38.10±0.38</td></tr><tr><td>14</td><td>28</td><td>7/0.127</td><td>16.51±0.25</td><td>17.78±0.25</td><td>34</td><td>28</td><td>7/0.127</td><td>41.91±0.38</td><td>43.18±0.38</td></tr><tr><td>③ 15</td><td>28</td><td>7/0.127</td><td>17.78±0.30</td><td>19.05±0.30</td><td>37</td><td>28</td><td>7/0.127</td><td>45.72±0.40</td><td>46.99±0.40</td></tr><tr><td>16</td><td>28</td><td>7/0.127</td><td>19.05±0.30</td><td>20.32±0.30</td><td>40</td><td>28</td><td>7/0.127</td><td>49.53±0.40</td><td>50.80±0.40</td></tr><tr><td>18</td><td>28</td><td>7/0.127</td><td>21.59±0.30</td><td>22.86±0.30</td><td>50</td><td>28</td><td>7/0.127</td><td>62.23±0.40</td><td>63.50±0.40 ①</td></tr><tr><td>20</td><td>28</td><td>7/0.127</td><td>24.13±0.30</td><td>25.40±0.30</td><td>60</td><td>28</td><td>7/0.127</td><td>74.93±0.45</td><td>76.20±0.45 ①</td></tr><tr><td>24</td><td>28</td><td>7/0.127</td><td>29.21±0.35</td><td>30.48±0.35</td><td>64</td><td>28</td><td>7/0.127</td><td>80.01±0.45</td><td>81.28±0.45 ①</td></tr></table>												Cores	Size of conductor		A ②④	B ②④	Cores	Size of conductor		A ②④	B ②④	AWG	Composition	AWG	Composition	09	28	7/0.127	10.16±0.25	11.43±0.25	25	28	7/0.127	30.48±0.35	31.75±0.35	10	28	7/0.127	11.43±0.25	12.70±0.25	26	28	7/0.127	31.75±0.35	33.02±0.35	12	28	7/0.127	13.97±0.25	15.24±0.25	30	28	7/0.127	36.83±0.38	38.10±0.38	14	28	7/0.127	16.51±0.25	17.78±0.25	34	28	7/0.127	41.91±0.38	43.18±0.38	③ 15	28	7/0.127	17.78±0.30	19.05±0.30	37	28	7/0.127	45.72±0.40	46.99±0.40	16	28	7/0.127	19.05±0.30	20.32±0.30	40	28	7/0.127	49.53±0.40	50.80±0.40	18	28	7/0.127	21.59±0.30	22.86±0.30	50	28	7/0.127	62.23±0.40	63.50±0.40 ①	20	28	7/0.127	24.13±0.30	25.40±0.30	60	28	7/0.127	74.93±0.45	76.20±0.45 ①	24	28	7/0.127	29.21±0.35	30.48±0.35	64	28	7/0.127	80.01±0.45	81.28±0.45 ①	E
Cores	Size of conductor		A ②④	B ②④	Cores	Size of conductor		A ②④	B ②④																																																																																																												
	AWG	Composition				AWG	Composition																																																																																																														
09	28	7/0.127	10.16±0.25	11.43±0.25	25	28	7/0.127	30.48±0.35	31.75±0.35																																																																																																												
10	28	7/0.127	11.43±0.25	12.70±0.25	26	28	7/0.127	31.75±0.35	33.02±0.35																																																																																																												
12	28	7/0.127	13.97±0.25	15.24±0.25	30	28	7/0.127	36.83±0.38	38.10±0.38																																																																																																												
14	28	7/0.127	16.51±0.25	17.78±0.25	34	28	7/0.127	41.91±0.38	43.18±0.38																																																																																																												
③ 15	28	7/0.127	17.78±0.30	19.05±0.30	37	28	7/0.127	45.72±0.40	46.99±0.40																																																																																																												
16	28	7/0.127	19.05±0.30	20.32±0.30	40	28	7/0.127	49.53±0.40	50.80±0.40																																																																																																												
18	28	7/0.127	21.59±0.30	22.86±0.30	50	28	7/0.127	62.23±0.40	63.50±0.40 ①																																																																																																												
20	28	7/0.127	24.13±0.30	25.40±0.30	60	28	7/0.127	74.93±0.45	76.20±0.45 ①																																																																																																												
24	28	7/0.127	29.21±0.35	30.48±0.35	64	28	7/0.127	80.01±0.45	81.28±0.45 ①																																																																																																												
F													F																																																																																																								
G	RoHS compliant Unit: mm <table><tr><td>Scale</td><td>Free</td><td>⑥</td><td>Correct cable appearance</td><td>20.05.2022</td><td>Daniel</td><td></td><td>Date</td><td>Name</td><td colspan="2">Description. Flat Cable Pitch 1.27mm</td></tr><tr><td colspan="2">TOLERANCE</td><td>⑤</td><td>Add the length dimension</td><td>20.04.2022</td><td>Peter</td><td>Drawn</td><td>30.01.2015</td><td>Amy</td><td colspan="2"></td></tr><tr><td></td><td></td><td>④</td><td>Update notes & tolerance</td><td>23.06.2020</td><td>Luca</td><td>Approved</td><td>20.05.2022</td><td>Daniel</td><td colspan="2">ASSMANN WSW-No. AWG28-xx/F/300</td></tr><tr><td></td><td></td><td>③</td><td>Add 15th core</td><td>05.08.2016</td><td>Amy</td><td></td><td></td><td></td><td colspan="2"></td></tr><tr><td>DIM</td><td>TOL</td><td>②</td><td>Update the tolerance</td><td>04.11.2015</td><td>Amy</td><td colspan="3" rowspan="3">ASSMANN WSW components</td><td>Drawing-No.</td><td></td></tr><tr><td></td><td></td><td>①</td><td>Update</td><td>08.04.2015</td><td>Amy</td><td>ASS 7310 CA</td><td>rev06</td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td>Customer-No.</td><td>Sheet 1 / 1</td></tr></table>												Scale	Free	⑥	Correct cable appearance	20.05.2022	Daniel		Date	Name	Description. Flat Cable Pitch 1.27mm		TOLERANCE		⑤	Add the length dimension	20.04.2022	Peter	Drawn	30.01.2015	Amy					④	Update notes & tolerance	23.06.2020	Luca	Approved	20.05.2022	Daniel	ASSMANN WSW-No. AWG28-xx/F/300				③	Add 15th core	05.08.2016	Amy						DIM	TOL	②	Update the tolerance	04.11.2015	Amy	ASSMANN WSW components			Drawing-No.				①	Update	08.04.2015	Amy	ASS 7310 CA	rev06	Angle	TOL	Id.	Modification	Date	Name	Customer-No.	Sheet 1 / 1	G																																	
Scale	Free	⑥	Correct cable appearance	20.05.2022	Daniel		Date	Name	Description. Flat Cable Pitch 1.27mm																																																																																																												
TOLERANCE		⑤	Add the length dimension	20.04.2022	Peter	Drawn	30.01.2015	Amy																																																																																																													
		④	Update notes & tolerance	23.06.2020	Luca	Approved	20.05.2022	Daniel	ASSMANN WSW-No. AWG28-xx/F/300																																																																																																												
		③	Add 15th core	05.08.2016	Amy																																																																																																																
DIM	TOL	②	Update the tolerance	04.11.2015	Amy	ASSMANN WSW components			Drawing-No.																																																																																																												
		①	Update	08.04.2015	Amy				ASS 7310 CA	rev06																																																																																																											
Angle	TOL	Id.	Modification	Date	Name				Customer-No.	Sheet 1 / 1																																																																																																											
H													H																																																																																																								
1		2		3		4		5		6		7																																																																																																									