

Home

Events

Careers

How To Buy

Contact

Products

Industries

Resources

News

About Us

▶ Cable Ties

▶ Cable Ties with Fasteners

▶ Cable Tie Tools

▶ Clamps and Clips

▶ Heatshrink Moulded Shapes

▶ Mounts

▶ Heavy Duty Mounts

▶ Wire Connectors

▼ Wiring Duct

Solid Wall

Slotted Wall

High Density Slotted Wall

Covers

Accessories

▶ Wiring Protection

▶ Labels, Printers and Software

▶ Pre-Terminated Networking

▶ Copper Network Solutions

▶ Fiber Network Solutions

▶ Jacks and Wall Plates

▶ Racks - Cable Management

▶ Surface Raceway Systems

181-44024

Slotted Wall Wiring Duct, Intrinsic Blue, 4" X 4", Non-Adhesive, PVC, Blue, 120ft/Carton

Article Number: 181-44024

Part Number: 181-44024

Type: SL4X4

➔Find a Distributor

➔Order Samples

➔Get Technical Drawings

Share

➔Base Data

Part No.	181-44024
Type	SL4X4
Color	Blue (BU)
Features	• Strong fingers prevent unwanted breaking. • Fingers are easily deflected outward, allowing ready positioning of the wires within the slotted wall duct. • Restricted opening design in the finger of the duct helps keep wires in place. • Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.

➔Product Dimensions

Length (L)	6.0ft / 1.83m
Width (W) (imperial)	4.0"
Width (W)	101.6mm
Width (W2)	4.0" / 10.6mm
Width (W3)	0.4" / 10.16mm
Width (W4)	1.0" / 25.4mm
Width (W5)	3.6" / 91.4mm
Width (W6)	1.5" / 38.1mm
Height (H)	4.0" / 101.6mm
Mounting Hole Centers	4.00" / 101.6mm

➔Material and Specifications

Material	Polyvinylchloride (PVC)
CSA Certified	Yes
Flammability	self-extinguishing
Material Specification	RoHS
Operating Temperature	+122 °F (+50 °C)
Specification	UL / CSA
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No / Yes

➔Logistic and Packaging

http://www.hellermannntyton.us/productDetail.aspx?lon=181-44024&ref=search.aspx[11/11/2013 1:02:43 PM]

Packaging Type	carton
Pkg. Qty.	120ft / 36.6m
Carton Qty.	120
UPC	089306294962

Find a Distributor

Get Product Samples

Get Technical Drawings