

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [74323-2031](#)
Status: **Active**
Overview: MicroCross™ DVI
Description: MicroCross™ DVI Digital/Analog Single Link Component, High Volume Plug Connector Sub-assembly, Vertical, Gold (Au) Flash, 23 Circuits, Lead-Free

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification


CSA LR19980
UL E29179

General

Product Family I/O Connectors
Series [74323](#)
Application Wire-to-Board
Comments DDWG (Digital Display Working Group) Standard
Component Type I/O Plug Connector Subassembly
Overview [MicroCross™ DVI](#)
Product Name MicroCross™ DVI
Type N/A
UPC 800754826037

Physical

Boot Color N/A
Circuits (Loaded) 23
Circuits (maximum) 29
Circuits Detail Circuits 1-3,6-8,9-11,14-16,17-19,22-24; C1-C5 are loaded.
Color - Resin Black
Durability (mating cycles max) 100
Flammability 94V-0
Keying to Mating Part Yes
Lock to Mating Part Yes
Material - Metal Copper Alloy
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Net Weight 7.936/g
Number of Rows 3
Orientation Vertical
PCB Retention None
Packaging Type Tray
Panel Mount N/A
Pitch - Mating Interface 1.90mm, 2.54mm
Pitch - Termination Interface 1.90mm, 2.54mm
Plating min - Mating 0.254µm
Plating min - Termination 3.810µm
Polarized to Mating Part Yes
Polarized to PCB Yes
Ports 1
Temperature Range - Operating -20°C to +85°C
Termination Interface: Style Solder or Weld
Waterproof / Dustproof No
Wire Size AWG N/A



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[74323Series](#)

Mates With
Other Receptacle components, [74320 DVI Receptacle](#), [67351 DVI Receptacle](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Soldering Fixture	0621003700

Electrical

Current - Maximum per Contact
Grounding to Panel
Shield Type
Shielded
Voltage - Maximum


Yes
Full Shield
Yes
40V AC (RMS)

Material Info

Reference - Drawing Numbers

Sales Drawing SD-74323-003

This document was generated on 01/21/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

onlinecomponents.com