


SKiiP 37NAB12T4V1



MiniSKiiP® 3

SKiiP 37NAB12T4V1

Features

- Trench 4 IGBTs
- Robust and soft freewheeling diodes in CAL technology
- Highly reliable spring contacts for electrical connections
- UL recognised file no. E63532

Typical Applications*


- Inverter up to 36 kVA
- Typical motor power 22 kW

Remarks

- V_{CEsat} , V_F = chip level value
- Case temp. limited to $T_C = 125^\circ\text{C}$ max. (for baseplateless modules $T_C = T_S$)
- product rel. results valid for $T_j \leq 150$ (recomm. $T_{op} = -40 \dots +150^\circ\text{C}$)


Absolute Maximum Ratings

Symbol	Conditions		Values	Unit
Inverter - IGBT				
V _{CES}	T _j = 25 °C		1200	V
I _C	T _j = 150 °C	T _s = 25 °C	81	A
		T _s = 70 °C	62	A
I _C	T _j = 175 °C	T _s = 25 °C	90	A
		T _s = 70 °C	73	A
I _{Cnom}			75	A
I _{CRM}	I _{CRM} = 3 x I _{Cnom}		225	A
V _{GES}			-20 ... 20	V
t _{psc}	V _{CC} = 800 V V _{GE} ≤ 15 V V _{CES} ≤ 1200 V	T _j = 150 °C	10	µs
T _j			-40 ... 175	°C
Chopper - IGBT				
V _{CES}	T _j = 25 °C		1200	V
I _C	T _j = 150 °C	T _s = 25 °C	81	A
		T _s = 70 °C	62	A
I _C	T _j = 175 °C	T _s = 25 °C	90	A
		T _s = 70 °C	73	A
I _{Cnom}			75	A
I _{CRM}	I _{CRM} = 3 x I _{Cnom}		225	A
V _{GES}			-20 ... 20	V
t _{psc}	V _{CC} = 800 V V _{GE} ≤ 15 V V _{CES} ≤ 1200 V	T _j = 150 °C	10	µs
T _j			-40 ... 175	°C
Inverse - Diode				
V _{RRM}	T _j = 25 °C		1200	V
I _F	T _j = 150 °C	T _s = 25 °C	74	A
		T _s = 70 °C	55	A
I _F	T _j = 175 °C	T _s = 25 °C	83	A
		T _s = 70 °C	66	A
I _{Fnom}			75	A
I _{FRM}	I _{FRM} = 3 x I _{Fnom}		225	A
I _{FSM}	t _p = 10 ms, sin 180°, T _j = 150 °C		430	A
T _j			-40 ... 175	°C
Freewheeling - Diode				
V _{RRM}	T _j = 25 °C		1200	V
I _F	T _j = 150 °C	T _s = 25 °C	74	A
		T _s = 70 °C	55	A
I _F	T _j = 175 °C	T _s = 25 °C	83	A
		T _s = 70 °C	66	A
I _{Fnom}			75	A
I _{FRM}	I _{FRM} = 3 x I _{Fnom}		225	A
I _{FSM}	t _p = 10 ms, sin 180°, T _j = 150 °C		430	A
T _i			-40 ... 175	°C



NAB

SKiiP 37NAB12T4V1



MiniSKiiP® 3

SKiiP 37NAB12T4V1

Features


- Trench 4 IGBTs
- Robust and soft freewheeling diodes in CAL technology
- Highly reliable spring contacts for electrical connections
- UL recognised file no. E63532

Typical Applications*

- Inverter up to 36 kVA
- Typical motor power 22 kW

Remarks

- V_{CEsat} , V_F = chip level value
- Case temp. limited to $T_C = 125^\circ\text{C}$ max. (for baseplateless modules $T_C = T_S$)
- product rel. results valid for $T_j \leq 150$ (recomm. $T_{op} = -40 \dots +150^\circ\text{C}$)



NAB


Absolute Maximum Ratings

Symbol	Conditions	Values	Unit
Rectifier - Diode			
V_{RRM}	$T_j = 25^\circ\text{C}$	1600	V
I_F	$T_s = 25^\circ\text{C}$, $T_j = 150^\circ\text{C}$	81	A
I_{Fnom}		25	A
I_{FSM}	10 ms	$T_j = 25^\circ\text{C}$	A
	sin 180°	$T_j = 150^\circ\text{C}$	A
I^2t	10 ms	$T_j = 25^\circ\text{C}$	A ² s
	sin 180°	$T_j = 150^\circ\text{C}$	A ² s
T_j		-40 ... 150	°C
Module			
$I_{t(RMS)}$	$T_{terminal} = 80^\circ\text{C}$, 20A per spring	80	A
T_{stg}		-40 ... 125	°C
V_{isol}	AC sinus 50Hz, 1 min	2500	V

Characteristics

Symbol	Conditions	min.	typ.	max.	Unit
Inverter - IGBT					
$V_{CE(sat)}$	$I_C = 75\text{ A}$ $V_{GE} = 15\text{ V}$ chipelevel	$T_j = 25^\circ\text{C}$	1.85	2.10	V
		$T_j = 150^\circ\text{C}$	2.25	2.45	V
V_{CE0}		$T_j = 25^\circ\text{C}$	0.8	0.9	V
		$T_j = 150^\circ\text{C}$	0.7	0.8	V
r_{CE}	$V_{GE} = 15\text{ V}$	$T_j = 25^\circ\text{C}$	14	16	mΩ
		$T_j = 150^\circ\text{C}$	21	22	mΩ
$V_{GE(th)}$	$V_{GE} = V_{CE}\text{ V}$, $I_C = 3\text{ mA}$	5	5.8	6.5	V
I_{CES}	$V_{GE} = 0\text{ V}$ $V_{CE} = 1200\text{ V}$	$T_j = 25^\circ\text{C}$	0.1	0.3	mA
					mA
C_{ies}	$V_{CE} = 25\text{ V}$ $V_{GE} = 0\text{ V}$	$f = 1\text{ MHz}$	4.40		nF
C_{oes}		$f = 1\text{ MHz}$	0.29		nF
C_{res}		$f = 1\text{ MHz}$	0.23		nF
Q_G	- 8 V...+ 15 V		425		nC
R_{Gint}	$T_j = 25^\circ\text{C}$		10.00		Ω
$t_{d(on)}$	$V_{CC} = 600\text{ V}$	$T_j = 150^\circ\text{C}$	150		ns
t_r	$I_C = 75\text{ A}$	$T_j = 150^\circ\text{C}$	35		ns
E_{on}	$R_{G on} = 2\text{ Ω}$	$T_j = 150^\circ\text{C}$	9.7		mJ
$t_{d(off)}$	$R_{G off} = 2\text{ Ω}$	$T_j = 150^\circ\text{C}$	355		ns
t_f		$T_j = 150^\circ\text{C}$	60		ns
E_{off}	$V_{GE} = +15/-15\text{ V}$	$T_j = 150^\circ\text{C}$	6.8		mJ
$R_{th(j-s)}$	per IGBT		0.58		K/W
Chopper - IGBT					
$V_{CE(sat)}$	$I_C = 75\text{ A}$ $V_{GE} = 15\text{ V}$ chipelevel	$T_j = 25^\circ\text{C}$	1.85	2.10	V
		$T_j = 150^\circ\text{C}$	2.25	2.45	V
V_{CE0}		$T_j = 25^\circ\text{C}$	0.8	0.9	V
		$T_j = 150^\circ\text{C}$	0.7	0.8	V
r_{CE}	$V_{GE} = 15\text{ V}$	$T_j = 25^\circ\text{C}$	14	16	mΩ
		$T_j = 150^\circ\text{C}$	21	22	mΩ
$V_{GE(th)}$	$V_{GE} = V_{CE}\text{ V}$, $I_C = 3\text{ mA}$	5	5.8	6.5	V
I_{CES}	$V_{GE} = 0\text{ V}$ $V_{CE} = 1200\text{ V}$	$T_j = 25^\circ\text{C}$	0.1	0.3	mA
		$T_j = 150^\circ\text{C}$			mA
Q_G	- 8 V...+ 15 V		425		nC
R_{Gint}	$T_j = 25^\circ\text{C}$		10.00		Ω

SKiiP 37NAB12T4V1



MiniSKiiP® 3

SKiiP 37NAB12T4V1

Features


- Trench 4 IGBTs
- Robust and soft freewheeling diodes in CAL technology
- Highly reliable spring contacts for electrical connections
- UL recognised file no. E63532

Typical Applications*

- Inverter up to 36 kVA
- Typical motor power 22 kW

Remarks

- V_{CEsat} , V_F = chip level value
- Case temp. limited to $T_C = 125^\circ\text{C}$ max. (for baseplateless modules $T_C = T_S$)
- product rel. results valid for $T_j \leq 150$ (recomm. $T_{op} = -40 \dots +150^\circ\text{C}$)



NAB

Characteristics					
Symbol	Conditions	min.	typ.	max.	Unit
Chopper - IGBT					
$t_{d(on)}$	$V_{CC} = 600\text{ V}$ $T_j = 150^\circ\text{C}$		150		ns
t_r	$I_C = 75\text{ A}$ $T_j = 150^\circ\text{C}$		35		ns
E_{on}	$R_{G\ on} = 2\ \Omega$ $T_j = 150^\circ\text{C}$		9.7		mJ
$t_{d(off)}$	$R_{G\ off} = 2\ \Omega$ $T_j = 150^\circ\text{C}$		355		ns
t_f	$T_j = 150^\circ\text{C}$		60		ns
E_{off}	$V_{GE} = +15/-15\text{ V}$ $T_j = 150^\circ\text{C}$		6.8		mJ
$R_{th(j-s)}$	per IGBT		0.58		K/W
Inverse - Diode					
$V_F = V_{EC}$	$I_F = 75\text{ A}$ $V_{GE} = 0\text{ V}$ chiplevel	$T_j = 25^\circ\text{C}$	2.2	2.5	V
		$T_j = 150^\circ\text{C}$	2.1	2.4	V
V_{F0}		$T_j = 25^\circ\text{C}$	1.3	1.5	V
		$T_j = 150^\circ\text{C}$	0.9	1.1	V
r_F		$T_j = 25^\circ\text{C}$	12	13	m Ω
		$T_j = 150^\circ\text{C}$	16	18	m Ω
I_{RRM}	$I_F = 75\text{ A}$ $di/dt_{off} = 1940\text{ A}/\mu\text{s}$	$T_j = 150^\circ\text{C}$	62		A
Q_{rr}	$V_{GE} = -15\text{ V}$ $V_{CC} = 600\text{ V}$	$T_j = 150^\circ\text{C}$	12.6		μC
E_{rr}		$T_j = 150^\circ\text{C}$	4.9		mJ
$R_{th(j-s)}$	per Diode		0.75		K/W
Freewheeling - Diode					
$V_F = V_{EC}$	$I_F = 75\text{ A}$ $V_{GE} = 0\text{ V}$ chiplevel	$T_j = 25^\circ\text{C}$	2.2	2.5	V
		$T_j = 150^\circ\text{C}$	2.1	2.4	V
V_{F0}		$T_j = 25^\circ\text{C}$	1.3	1.5	V
		$T_j = 150^\circ\text{C}$	0.9	1.1	V
r_F		$T_j = 25^\circ\text{C}$	12	13	m Ω
		$T_j = 150^\circ\text{C}$	16	18	m Ω
I_{RRM}	$I_F = 75\text{ A}$ $di/dt_{off} = 1940\text{ A}/\mu\text{s}$	$T_j = 150^\circ\text{C}$	62		A
Q_{rr}	$V_{GE} = -15\text{ V}$ $V_{CC} = 600\text{ V}$	$T_j = 150^\circ\text{C}$	12.6		μC
E_{rr}		$T_j = 150^\circ\text{C}$	4.9		mJ
$R_{th(j-s)}$	per Diode		0.75		K/W
Rectifier - Diode					
$V_F = V_{EC}$	$I_F = 25\text{ A}$ $V_{GE} = 0\text{ V}$ chiplevel	$T_j = 25^\circ\text{C}$	1	1.21	V
		$T_j = 125^\circ\text{C}$		1.1	V
V_{F0}		$T_j = 25^\circ\text{C}$		1.0	V
		$T_j = 125^\circ\text{C}$		0.8	V
r_F		$T_j = 25^\circ\text{C}$	4.8	9.3	m Ω
		$T_j = 125^\circ\text{C}$		11	m Ω
$R_{th(j-s)}$	per Diode		0.9		K/W
Module					
M_s	to heat sink	2		2.5	Nm
w			95		g
Temperatur Sensor					
R_{100}	$T_r = 100^\circ\text{C}$, tolerance = 3 %		1670 $\pm$ 3%		Ω
$R(T)$	$R(T) = 1000\Omega [1 + A(T - 25^\circ\text{C}) + B(T - 25^\circ\text{C})^2]$], $A = 7.635 \cdot 10^{-3} \text{ }^\circ\text{C}^{-1}$, $B = 1.731 \cdot 10^{-5} \text{ }^\circ\text{C}^{-2}$				




Fig. 1: Typ. output characteristic




Fig. 2: Typ. rated current vs. temperature $I_C = f(T_S)$




Fig. 3: Typ. turn-on /-off energy = $f(I_C)$




Fig. 4: Typ. turn-on /-off energy = $f(R_G)$




Fig. 5: Typ. transfer characteristic












Fig. 6: Typ. gate charge characteristic





pinout, dimensions



This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX

* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our staff.