




Technical Data Sheet

0.36" Triple Digit Displays

EVT-315SYGWA/S530-E2

■ Features :

- Industrial standard size.
- Low power consumption.
- Categorized for luminous intensity.
- Pb free
- The product itself will remain within RoHS compliant version



■ Descriptions :

- The EVT-315series is a large 9.2mm (0.36")high seven segment display designed for viewing distances up to 7 meters.
- These displays provide excellent reliability in bright ambient light.
- These devices are made with white segments and gray surface.

■ Applications :

- Audio equipment
- Instrument panels
- Digital read out display

PART NO.	Chip	
	Material	Emitted Color
EVT-315SYGWA/S530-E2	AlGaInP	Super Yellow Green

BG0505051

50009290




Technical Data Sheet

0.36" Triple Digit Displays


EVT-315SYGWA/S530-E2

Package Dimensions



COMMON CATHODE

- 1 ANODE E
- 2 ANODE D
- 3 ANODE DP
- 4 ANODE C
- 5 ANODE G
- 6 NO PIN
- 7 ANODE B
- 8 COMMON CATHODE DIG.3
- 9 COMMON CATHODE DIG.2
- 10 ANODE F
- 11 ANODE A
- 12 COMMON CATHODE DIG.1



Notes: 1.All dimensions are in millimeters , tolerance is 0.25mm unless otherwise noted.

2.Above specification may be changed without notice.

Supplier will reserve authority on material change for above specification.

**Technical Data Sheet**
0.36" Triple Digit Displays**EVT-315SYGWA/S530-E2**

■ Absolute maximum ratings at Ta = 25°C :

Parameter	Symbol	Rating	Unit
Reverse Voltage	VR	5	V
Forward Current	IF	25	mA
Operating Temperature	Topr	-40 to +85	°C
Storage Temperature	Tstg	-40 to +100	°C
Soldering Temperature	Tsol	260 ± 5	°C
Electrostatic Discharge	ESD	2000	V
Power Dissipation	Pd	60	mW

Note: *Soldering time ≤ 5 seconds.

■ Electronic optical characteristics :

Parameter		Symbol	Min.	Typ.	Max.	Unit	Condition	
Luminous Intensity	Per segment	Iv	----	0.7	----	mcd	IF=2mA	
			1.4	3.2	----	mcd	IF=10mA	
	Per decimal point		----	0.2	----	mcd	IF=2mA	
			0.4	0.7	----	mcd	IF=10mA	
Peak Wavelength		λ p	----	575	----	nm	IF=20mA	
Dominant Wavelength		λ d	----	573	----	nm	IF=20mA	
Spectrum Radiation Bandwidth		△ λ	----	20	----	nm	IF=20mA	
Forward Voltage		VF	-----	2.0	2.4	V	IF=20mA	
Reverse Current		IR	----	----	100	μ A	VR=5V	



EVE-LIGHT (XIAMEN) PHOTOELECTRICITY TECHNOLOGY. CO., LTD




Technical Data Sheet

0.36" Triple Digit Displays

EVT-315SYGWA/S530-E2

■ Typical Electro-Optical Characteristic Curves:

CHIP Material: AlGaInP
Emitted Color: Super Yellow Green



**Technical Data Sheet****0.36" Triple Digit Displays****EVT-315SYGWA/S530-E2****Reliability test items and conditions:**

The reliability of products shall be satisfied with items listed below.

Confidence level : 97%

LTPD : 3%

NO	Item	Test Conditions	Test Hours/Cycle	Sample Size	Failure Judgment Criteria	Ac/Re
1	Solder Heat	TEMP : 260°C ± 5 °C	5 SEC	76 PCS	$I_v \leq I_{vt} * 0.5$ or $V_f \geq U$ or $V_f \leq L$	0/1
2	Temperature Cycle	H : +85°C 30min § 5 min L : -55°C 30min	50 CYCLE	76 PCS		0/1
3	Thermal Shock	H : +100°C 5min § 10 sec L : -10°C 5min	50 CYCLE	76 PCS		0/1
4	High Temperature Storage	TEMP : 100°C	1000 HRS	76 PCS		0/1
5	Low Temperature Storage	TEMP : -55°C	1000 HRS	76 PCS		0/1
6	DC Operating Life	IF = 10 mA	1000 HRS	76 PCS		0/1
7	High Temperature / High Humidity	85°C/85% RH	1000 HRS	76 PCS		0/1

Note : I_{vt} : The test I_v value of the chip before the reliability test

I_v : The test value of the chip that has completed the reliability test

U : Upper Specification Limit

L : Lower Specification Limit



EVE-LIGHT (XIAMEN) PHOTOELECTRICITY TECHNOLOGY. CO., LTD

Technical Data Sheet

0.36" Triple Digit Displays

EVT-315SYGWA/S530-E2

■ Packing Quantity Specification

1.22PCS/tube, 56 tubes/box

2.4Boxes/Carton

Label Form Specification

<div>EVE-LIGHT</div>		CPN: Customer's Production Number
CPN:		P/N : Production Number
P/N:		QTY: Packing Quantity
	T315SYGWA/S530-E2	CAT: Ranks
QTY:		HUE: Dominant Wavelength
		REF: Reference
CAT:		LOT No: Lot Number
HUE:		MADE IN CHINA: Production Place
REF:		
LOT NO:		
MADE IN CHINA		

Notes :

1. Above specification may be changed without notice. EVE-LIGHT will reserve authority on material change for above specification.
2. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVE-LIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
3. These specification sheets include materials protected under copyright of EVE-LIGHT corporation. Please don't reproduce or cause anyone to reproduce them without EVE-LIGHT's consent.

