







NOTE:
MATES WITH : 5264 SERIES.



39.9	38.5	35	-7155	-15A	15
37.4	36	32.5	-7145	-14A	14
34.9	33.5	30	-7135	-13A	13
32.4	31	27.5	-7125	-12A	12
29.9	28.5	25	-7115	-11A	11
27.4	26	22.5	-7105	-10A	10
24.9	23.5	20	-7095	-09A	9
22.4	21	17.5	-7085	-08A	8
19.9	18.5	15	-7075	-07A	7
17.4	16	12.5	-7065	-06A	6
14.9	13.5	10	-7055	-05A	5
12.4	11	7.5	-7045	-04A	4
9.9	8.5	5	-7035	-03A	3
7.4	6	2.5	22-05-7025	5268-02A	2
C	B	A	EDP NO.	ENG.NO.	CKT.



REVISED EC NO: J2018-0076 DRAWN: KUSATO CHKD: AIDA APPR: KANEKO	2017/08/29 2017/08/29 2017/08/30	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 5:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION				
			0.25 UNDER	±	DRAWN BY	DATE	TITLE 2.5 LOW PROFILE WAFER ASSY 90° BEND							
			0.25 OVER	0.5 UNDER	K. TOJO	1991/11/05								
			0.5 OVER	1.0 UNDER	CHECKED BY	DATE								
			0	OVER	10 UNDER	± 0.2			H. HIRAMOTO		1992/08/31			
			0	OVER	10	UNDER	± 0.2	APPROVED BY	DATE		molex			
			10	OVER	30	UNDER	± 0.25	M. ENAMOTO	1992/08/31					
			30	OVER			± 0.3	MATERIAL NO.					DOCUMENT NO.	SHEET NO.
			ANGULAR ±3 °			SEE CHART		SD-5268-NA					1 OF 1	
			REV		DESCRIPTION	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			