

**CBRHD SERIES**

**SURFACE MOUNT SILICON  
HIGH DENSITY  
0.5 AMP  
BRIDGE RECTIFIER**

**HD  
BRIDGE****HD DIP CASE**[www.centralsemi.com](http://www.centralsemi.com)**DESCRIPTION:**

The CENTRAL SEMICONDUCTOR CBRHD series devices are silicon full wave bridge rectifiers mounted in a durable epoxy surface mount molded case, utilizing glass passivated chips.

**MARKING CODES:**

CBRHD-02: CBD2      CBRHD-04: CBD4  
CBRHD-06: CBD6      CBRHD-10: CBD10

**FEATURES:**

- Efficient use of board space: requires only 42mm<sup>2</sup> of board space vs. 120mm<sup>2</sup> of board space needed for industry standard 1.0 Amp surface mount bridge rectifier.
- 50% higher density (Amps/mm<sup>2</sup>) than the industry standard 1.0 Amp surface mount bridge rectifier.
- Glass passivated chips for high reliability.

**MAXIMUM RATINGS:** (T<sub>A</sub>=25°C unless otherwise noted)

		CBRHD				
	SYMBOL	-02	-04	-06	-10*	UNITS
Peak Repetitive Reverse Voltage	V <sub>RRM</sub>	200	400	600	1000	V
DC Blocking Voltage	V <sub>R</sub>	200	400	600	1000	V
RMS Reverse Voltage	V <sub>R</sub> (RMS)	140	280	420	700	V
Average Forward Current (T <sub>A</sub> =40°C) (Note 1)	I <sub>O</sub>			0.5		A
Average Forward Current (T <sub>A</sub> =40°C) (Note 2)	I <sub>O</sub>			0.8		A
Peak Forward Surge Current	I <sub>FSM</sub>			30		A
Operating & Storage Junction Temperature	T <sub>J</sub> , T <sub>stg</sub>			-65 to +150		°C

**ELECTRICAL CHARACTERISTICS PER DIODE:** (T<sub>A</sub>=25°C unless otherwise noted)

SYMBOL	TEST CONDITIONS	TYP	MAX	UNITS
I <sub>R</sub>	V <sub>R</sub> =Rated V <sub>RRM</sub>		5.0	µA
I <sub>R</sub>	V <sub>R</sub> =Rated V <sub>RRM</sub> , T <sub>A</sub> =125°C		500	µA
V <sub>F</sub>	I <sub>F</sub> =400mA		1.0	V
C <sub>J</sub>	V <sub>R</sub> =4.0V, f=1.0MHz	20		pF

Notes: (1) Mounted on Glass-Epoxy PCB.  
(2) Mounted on Ceramic PCB.



\* Available on special order, please consult factory.

CBRHD SERIES

SURFACE MOUNT SILICON  
HIGH DENSITY  
0.5 AMP  
BRIDGE RECTIFIER



HD DIP CASE - MECHANICAL OUTLINE



R2

SYMBOL	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.006	0.014	0.15	0.35
B	-	0.275	-	7.00
C	0.027	0.043	0.70	1.10
D	0.035	0.051	0.90	1.30
E	0.090	0.106	2.30	2.70
F	0.019	0.031	0.50	0.80
G	0.150	0.165	3.80	4.20
H	0.051	0.067	1.30	1.70
J	0.177	0.193	4.50	4.90
K	0.090	0.106	2.30	2.70
L	0.000	0.008	0.00	0.20

HD DIP (REV: R2)

MARKING CODES:  
CBRHD-02: CBD2  
CBRHD-04: CBD4  
CBRHD-06: CBD6  
CBRHD-10: CBD10

R5 (18-February 2016)

[www.centralsemi.com](http://www.centralsemi.com)

## OUTSTANDING SUPPORT AND SUPERIOR SERVICES



---

### PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- Consolidated shipping options
- Custom bar coding for shipments
- Custom product packing

---

### DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2<sup>nd</sup> day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities
- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- Application and design sample kits
- Custom product and package development

---

### REQUESTING PRODUCT PLATING

1. If requesting Tin/Lead plated devices, add the suffix " TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
2. If requesting Lead (Pb) Free plated devices, add the suffix " PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

---

### CONTACT US

#### Corporate Headquarters & Customer Support Team

Central Semiconductor Corp.

145 Adams Avenue

Hauppauge, NY 11788 USA

Main Tel: (631) 435-1110

Main Fax: (631) 435-1824

Support Team Fax: (631) 435-3388

[www.centralsemi.com](http://www.centralsemi.com)

#### Worldwide Field Representatives:

[www.centralsemi.com/wwreps](http://www.centralsemi.com/wwreps)

#### Worldwide Distributors:

[www.centralsemi.com/wwdistributors](http://www.centralsemi.com/wwdistributors)

---

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: [www.centralsemi.com/terms](http://www.centralsemi.com/terms)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Central Semiconductor:

[CBRHD-04 TR13](#) [CBRHD-06 TR13](#) [CBRHD-02 TR13](#) [CBRHD-10 TR13](#) [CBRHD-10 BK](#) [CBRHD-06 BK](#) [CBRHD-02 BK](#) [CBRHD-04 BK](#)