



Surface Mount Self-Leaded Inductor 150 kHz

Electrical Specifications at 25°C. Operating Temp. Range: -30°C to +130°C



Part Number	L ⁽¹⁾ with DC (μ H)	I _{DC} ⁽¹⁾ (Amps)	E-T ⁽¹⁾ Product (V- μ s)	DCR max. (Ω)
L-15338	79	0.25	9.9	1.5

- 1) Typical values for a 55°C Temperature rise at 150 kHz and E-T value above, the core loss is 10 % of copper loss.

Schematic Diagram




Physical Dimensions
inches (mm)



* Tolerance $\pm$.015 (0.38)

** Tolerance $\pm$.005 (0.15)



Suggested PCB Layout

RHOMBUS P/N: L-15338

CUST P/N:

NAME:

DATE: 7/30/96

SHEET: 1 OF 1