


P.C.PINS

10-8XX-X-04 P.C. PIN .050

MATERIAL: BRASS
STANDARD FINISH:
ELECTRO-TIN

BASIC PART NO. FINISH



*FOR -1A .071 BECOMES .056 FOR -1 .071 BECOMES .063

RECOMMENDED MOUNTING HOLE .064 DIA. (#52 DRILL)

PART NO.	H	L	THK	BOARD	PART NO.	H	L	THK	BOARD
10-829-11-04	.125	.047	1/64		10-833-1-04	.313	.063	1/32	
-1-04	.125	.063	1/32		-2-04	.313	.094	1/16	
-2-04	.125	.094	1/16		-3-04	.313	.125	3/32	
-3-04	.125	.125	3/32		-4-04	.313	.156	1/8	
-4-04	.125	.156	1/8		10-834-1-04	.375	.063	1/32	
10-831-11-04	.188	.047	1/65		-2-04	.375	.094	1/16	
-1-04	.188	.063	1/32		-3-04	.375	.125	3/32	
-2-04	.188	.093	1/16		-4-04	.375	.156	1/8	
-3-04	.188	.125	3/32		-6-04	.375	.219	3/16	
-4-04	.188	.156	1/8		-8-04	.375	.281	1/4	
-6-04	.188	.219	3/16		10-835-2-04	.438	.094	1/16	
-8-04	.188	.281	1/4		-3-04	.438	.125	3/32	
10-832-1-04	.250	.063	1/32		-4-04	.438	.156	1/8	
-2-04	.250	.094	1/16		10-836-2-04	.500	.094	1/16	
-3-04	.250	.125	3/32		-3-04	.500	.125	3/32	
-4-04	.250	.156	1/8		-4-04	.500	.156	1/8	


TOOLS

ANVIL	PUNCH
TA94-50-31	TP62-44

10-8XX-X-03 P.C. PIN .090

MATERIAL: BRASS
STANDARD FINISH (XX):
(02)NICKEL
(03)GOLD

09-8XXX-X-XX
BASIC PART NO. FINISH



RECOMMENDED MOUNTING HOLE .094 DIA. (3/32 DRILL)

PART NO.	H	L	K	P	BOARD THK.	ANVIL	PUNCH
10-873-1-03	.150	.075	.042	1/16	1/32	TA125-90-40	TP90-64
-2-03	.150	.105	.042	1/16	1/16	TA125-90-40	TP90-64
-3-03	.150	.135	.042	1/16	3/32	TA125-90-40	TP90-64
10-874-1-03	.300	.075	.042	1/16	1/32	TA125-90-40	TP90-64
-2-03	.300	.105	.042	1/16	3/32	TA125-90-40	TP90-64
-3-03	.300	.135	.042	1/16	3/32	TA125-90-40	TP90-64
09-8168-3-03	.555	.135	.042	1/16	3/32	TA125-90-40	TP90-64
09-8014-3-02	.625	.125	.063	-	3/32	TA125-90-60	TP90-64

10-895-X-02 P.C. PINS .020, .032, .040, .062

BASIC PART NO. FINISH


MATERIAL: BRASS
STANDARD FINISH: NICKEL

PART NO.	A	L
10-895-1-02	.020	.400
2-02	.020	.600
3-02	.020	.900
4-02	.032	.400
5-02	.032	.600
6-02	.032	.900
7-02	.040	.400
8-02	.040	.600
9-02	.040	.900
10-02	.062	.400
11-02	.062	.600
12-02	.062	.900

10-8008-X-XX P.C. PIN .080

MATERIAL: BRASS
STANDARD FINISH (XX):
(03)GOLD
(04)ELECTRO-TIN

BASIC PART NO. FINISH



RECOMMENDED MOUNTING HOLE .094 ±0.002 DIA. (3/32 DRILL)


PART NO.	L	BOARD THK.	TOOLS
10-8008-2-XX	.094	1/16	
-3-XX	.125	3/32	
-4-XX	.156	1/8	

ANVIL	PUNCH
TA125-80-25	TP90-64

09-81XX-X-03 P.C. PIN .025

MATERIAL: BRASS
STANDARD FINISH: GOLD

BASIC PART NO. FINISH



PART NO.	H	L	BOARD THK.
09-8186-1-03	.070	.047	1/32
-2A-03	.070	.060	3/64
-2-03	.070	.075	1/16
09-8188-1-03	.090	.047	1/32
-2A-03	.090	.060	1/64
-2-03	.090	.075	1/16


RECOMMENDED MOUNTING HOLE .035 DIA. (#64 DRILL)

TOOLS
ANVIL
TA20-25-20
PUNCH
TP30-20

10-8016-X-XX P.C. PIN .080

MATERIAL: BRASS
STANDARD FINISH (XX):
(03)GOLD
(04)ELECTRO-TIN

BASIC PART NO. FINISH



RECOMMENDED MOUNTING HOLE .094 ±0.002 DIA. (3/32 DRILL)


PART NO.	L	BOARD THK.	TOOLS
10-8016-2-XX	.051	.031	
-3-XX	.082	.062	
-4-XX	.113	.094	

ANVIL	PUNCH
TA156-80-30	TP90-64

09-8169-X-05 P.C. PIN .031

MATERIAL: BRASS
STANDARD FINISH:
ELECTRO-SOLDER

BASIC PART NO. FINISH



RECOMMENDED MOUNTING HOLE .0465 DIA. (#56 DRILL)

PART NO.	L	BOARD THK.	TOOLS
09-8169-1-05	.055	1/32	
-2-05	.087	1/16	

ANVIL	PUNCH
TA80-21-10	TP40-25

FOR ADDITIONAL SIZES AND MATERIALS, CONTACT FACTORY

CONCORD