



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
CPP48HDWBLY	6.15 LB/10 PCS (2788.0 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM.
2. THE HIGH DENSITY PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
3. PACKAGE CONTENTS:
 - (1) - 48 PORT STAMPING
 - (6) - 8 POSITION FACEPLATE (ASSEMBLED TO PANEL)
 - (1) - SCREW KIT (INCLUDES FOUR #12-24 SCREWS)
 - (1) - SCREW KIT (INCLUDES FOUR M6 SCREWS)
4. DIMENSIONS IN [] ARE IN METRIC.



PART NUMBER		CPP48HDWBLY									
TITLE		MINI-COM 48 PORT HIGH DENSITY MODULAR PATCH PANEL									
ITEM REVISION NAME		CUSTOMER DRAWING									
M02479DA/00											
DATASET FILE NAME		M02479DA_DC81/00B									
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:									
.X ± .010 [.3]		STAMPING: 18 GAGE C.R.S.									
.XX ± .031 [.8]		FACEPLATE: ABS									
ANGLES ±		DRAWING NUMBER:									
		02479-081									
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SIZE
1	6/13/14	JSP	REFR	MMR	A. REVISED DRAWING TITLE BLOCK.	02479-081	JSP	3-11-06	MJD	NONE	SHT 1 OF 1
R	3-11-06	JSP	MJD	MJD	RELEASED TO PRODUCTION	02479-081					A