

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

HA17431G Series

Adjustable Precision Shunt Regulators

REJ03D0805-0100

Rev.1.00

Mar 10, 2006

Description


The HA17431G series is temperature-compensated adjustable precision shunt regulators. The products have improved features such as wide operating cathode voltage range and precision than the previous products.

Output voltage can be set to any value in the range from the reference voltage (V_{ref}) to 40 V by two external resistors. There are two types of reference voltage accuracy sources such as $\pm 1.0\%$ standard version and $\pm 0.5\%$ A version with higher precision. As for the packages, small surface-mounted types such as MPAK, MPAK-5, and UPAK are available. Therefore, the HA17431G series is suitable for various applications that require high precision and miniaturization.


Features

- High-precision reference voltage : 2.500 V \pm 1.0% ($T_a = 25^\circ\text{C}$, Standard version)
: 2.500 V \pm 0.5% ($T_a = 25^\circ\text{C}$, A version)
- Maximum cathode voltage : 40 V
- Continuous cathode current : 100 mA
- K-REF pin reversing type : HA17432G (UPAK)
- Operating temperature range : -40°C to $+85^\circ\text{C}$

Block Diagram



Application Circuit Example




Ordering Information


Application	Type No.	Reference Voltage (Ta = 25°C)		Package Name (Package Code)	Operating Temperature Range
		Standard Version 2.500V ± 1.0%	A Version 2.500V ± 0.5%		
Industrial use	HA17431GP	○		TO-92 (PRSS0003DA-A)	-40°C to +85°C
	HA17431GPA		○		
	HA17431GLTP	○		MPAK (PLSP0003ZB-A)	
	HA17431GLTPA		○		
	HA17431GLP	○		MPAK-5 (PLSP0005ZB-A)	
	HA17431GLPA		○		
	HA17431GUP	○		UPAK (PLZZ0004CA-A)	
	HA17432GUP (K-REF pin reversing type)	○			

Pin Arrangement


- TO-92
HA17431GP
HA17431GPA




- MPAK
HA17431GLTP
HA17431GLTPA




- MPAK-5
HA17431GLP
HA17431GLPA



- UPAK
HA17431GUP



- UPAK
HA17432GUP



Note: REF : Reference
A : Anode
K : Cathode
NC : No connection

Absolute Maximum Ratings

(Ta = 25°C)

Item		Symbol	Ratings	Unit	Notes
Cathode voltage		V_{KA}	40	V	1
Continuous cathode current		I_K	-50 to +100	mA	
Reference input current		I_{ref}	-0.05 to +10	mA	
Power dissipation	TO-92	P_T	500	mW	2
	MPAK		150		3
	MPAK-5		150		3
	UPAK		800		4
Operating temperature range		T_{opr}	-40 to +85	°C	
Storage temperature		T_{stg}	-55 to +150	°C	

Notes: 1. Voltage values are with reference to the Anode pin.



2. $T_a \leq 25^\circ\text{C}$. If $T_a > 25^\circ\text{C}$, derate by $-4 \text{ mW}/^\circ\text{C}$.3. $T_a \leq 25^\circ\text{C}$. If $T_a > 25^\circ\text{C}$, derate by $-1.2 \text{ mW}/^\circ\text{C}$.4. $15 \text{ mm} \times 25 \text{ mm} \times 0.7 \text{ mm}$ alumina ceramic board, $T_a \leq 25^\circ\text{C}$. If $T_a > 25^\circ\text{C}$, derate by $-6.4 \text{ mW}/^\circ\text{C}$.

Electrical Characteristics

(Ta = 25°C, I_K = 10 mA, unless otherwise noted)

Item	Symbol	Min	Typ	Max	Unit	Test Conditions	Notes
Reference voltage	V _{ref}	2.487	2.500	2.513	V	V _{KA} = V _{ref}	A
		2.475	2.500	2.525			Standard
Reference voltage temperature deviation	V _{ref} (dev)	—	(14)	—	mV	V _{KA} = V _{ref} , Ta = -40°C to +85°C	1, 2
Reference voltage temperature coefficient	ΔV _{ref} /ΔTa	—	(±30)	—	ppm/°C	V _{KA} = V _{ref} , 0°C to 50°C gradient	1
Reference voltage regulation	ΔV _{ref} /ΔV _{KA}	—	2.0	3.7	mV/V	V _{KA} = V _{ref} to 10 V	
		—	2.0	3.7		V _{KA} = 10 V to 40 V	
Reference input current	I _{ref}	—	2	6	μA	R ₁ = 10 kΩ, R ₂ = ∞	
Reference current temperature deviation	I _{ref} (dev)	—	(0.9)	—	μA	R ₁ = 10 kΩ, R ₂ = ∞, Ta = -40°C to +85°C	1
Minimum cathode current	I _{min}	—	0.4	1.0	mA	V _{KA} = V _{ref}	3
Off state cathode current	I _{off}	—	0.001	1.0	μA	V _{KA} = 40 V, V _{ref} = 0 V	
Dynamic impedance	Z _{KA}	—	0.2	0.5	Ω	V _{KA} = V _{ref} , I _K = 1 mA to 100 mA	


Notes: 1. Reference values for design.

2. V_{ref}(dev) = (V_{ref} maximum value at Ta = -40°C to +85°C) – (V_{ref} minimum value at Ta = -40°C to +85°C)3. Definition of minimum cathode current. I_{min} is the cathode current value at which V_{ref} = V_{ref}(I_K=10mA) – 15 mV.


Marking Patterns

The marking patterns shown below are used on MPAK, MPAK-5 and UPAK products.


HA17431GLTP




HA17431GLP




HA17431GUP




HA17432GUP



HA17431GLTPA



HA17431GLPA





Note: Boxes (1) to (5) in the figures show the position of the letters or numerals, and are not actually marked on the package.

Markings

Position	Type of Marking	Meaning																																				
(1), (2)	Characters	Type No. code HA17431GLTP: 3G HA17431GLTPA: 3H HA17431GLP: 4H HA17431GLPA: 4K HA17431GUP: 4N HA17432GUP: 4U																																				
(3)		Production year code (The last digit of the year) Notes: 1. For UPAK products (HA17431GUP, HA17432GUP)																																				
(a), (b), (c)	Bar mark	Production year code <table border="1"><tr><td>Production Year</td><td>2006</td><td>2007</td><td>2008</td><td>2009</td><td>2010</td><td>2011</td><td>2012</td><td>2013</td></tr><tr><td>(a)</td><td>Bar</td><td>Bar</td><td>Bar</td><td>None</td><td>None</td><td>None</td><td>None</td><td>Bar</td></tr><tr><td>(b)</td><td>None</td><td>Bar</td><td>Bar</td><td>None</td><td>None</td><td>Bar</td><td>Bar</td><td>None</td></tr><tr><td>(c)</td><td>Bar</td><td>None</td><td>Bar</td><td>None</td><td>Bar</td><td>None</td><td>Bar</td><td>None</td></tr></table> Notes: 2. Repeated every 8 years from 2014 on. 3. For MPAK products (HA17431GLTP, HA17431GLTPA) For MPAK-5 products (HA17431GLP, HA17431GLPA)	Production Year	2006	2007	2008	2009	2010	2011	2012	2013	(a)	Bar	Bar	Bar	None	None	None	None	Bar	(b)	None	Bar	Bar	None	None	Bar	Bar	None	(c)	Bar	None	Bar	None	Bar	None	Bar	None
Production Year	2006	2007	2008	2009	2010	2011	2012	2013																														
(a)	Bar	Bar	Bar	None	None	None	None	Bar																														
(b)	None	Bar	Bar	None	None	Bar	Bar	None																														
(c)	Bar	None	Bar	None	Bar	None	Bar	None																														
(4)	Characters	Production month code <table border="1"><tr><td>Production Month</td><td>Jan.</td><td>Feb.</td><td>Mar.</td><td>Apr.</td><td>May</td><td>Jun.</td><td>Jul.</td><td>Aug.</td><td>Sep.</td><td>Oct.</td><td>Nov.</td><td>Dec.</td></tr><tr><td>Code</td><td>A</td><td>B</td><td>C</td><td>D</td><td>E</td><td>F</td><td>G</td><td>H</td><td>J</td><td>K</td><td>L</td><td>M</td></tr></table>	Production Month	Jan.	Feb.	Mar.	Apr.	May	Jun.	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.	Code	A	B	C	D	E	F	G	H	J	K	L	M										
Production Month		Jan.	Feb.	Mar.	Apr.	May	Jun.	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.																									
Code	A	B	C	D	E	F	G	H	J	K	L	M																										
(5)		Management code Notes: 4. For UPAK products (HA17431GUP, HA17432GUP)																																				


Characteristics Curves

Reference Voltage vs. Ambient Temperature Characteristics




Measurement Circuit



Cathode Current vs. Cathode Voltage Characteristics 1



Cathode Current vs. Cathode Voltage Characteristics 2





Reference Input Current vs. Ambient Temperature Characteristics





Measurement Circuit

Off State Cathode Current vs. Ambient Temperature Characteristics



Measurement Circuit



Reference Voltage Deviation vs. Cathode Voltage Characteristics



$$V_{KA} \cong V_{ref} \times \frac{R1 + R2}{R2}$$

Measurement Circuit



Open Loop Voltage Gain, Phase vs. Frequency Characteristics



$$G_{VOL} = 20 \log \left(\frac{V_o}{V_i} \right) \text{ (dB)}$$

Measurement Circuit





Dynamic Impedance vs. Frequency Characteristics



$$i_o = 707\text{mA}_{\text{rms}} (= 2\text{mA}_{\text{p-p}})$$



$$Z_{KA} = \frac{V_{KA}}{i_o} \text{ (Ω)}$$

Measurement Circuit



Note: In the unstable operation region, there is a possibility that the device oscillates.
Please change to the setting with an enough margin in consideration of the difference when you use it.


Package Dimensions



HA17431G Series


Package Name	JEITA Package Code	RENESAS Code	Previous Code	MASS[Typ.]
UPAK	SC-62	PLZZ0004CA-A	UPAK / UPAKV	0.050g

Unit: mm



Package Name	JEITA Package Code	RENESAS Code	Previous Code	MASS[Typ.]
TO-92(1)	SC-43A	PRSS0003DA-A	TO-92(1) / TO-92(1)V	0.25g

Unit: mm



Renesas Technology Corp. Sales Strategic Planning Div. Nippon Bldg., 2-6-2, Ohte-machi, Chiyoda-ku, Tokyo 100-0004, Japan

Keep safety first in your circuit designs!

1. Renesas Technology Corp. puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corp. product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corp. or a third party.
2. Renesas Technology Corp. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corp. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors.
Renesas Technology Corp. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Renesas Technology Corp. by various means, including the Renesas Technology Corp. Semiconductor home page (<http://www.renesas.com>).
4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corp. assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
5. Renesas Technology Corp. semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
6. The prior written approval of Renesas Technology Corp. is necessary to reprint or reproduce in whole or in part these materials.
7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
8. Please contact Renesas Technology Corp. for further details on these materials or the products contained therein.



RENESAS SALES OFFICES

<http://www.renesas.com>

Refer to "<http://www.renesas.com/en/network>" for the latest and detailed information.

Renesas Technology America, Inc.

450 Holger Way, San Jose, CA 95134-1368, U.S.A
Tel: <1> (408) 382-7500, Fax: <1> (408) 382-7501

Renesas Technology Europe Limited

Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K.
Tel: <44> (1628) 585-100, Fax: <44> (1628) 585-900

Renesas Technology (Shanghai) Co., Ltd.

Unit 204, 205, AZIA Center, No.1233 Lujiazui Ring Rd, Pudong District, Shanghai, China 200120
Tel: <86> (21) 5877-1818, Fax: <86> (21) 6887-7898

Renesas Technology Hong Kong Ltd.

7th Floor, North Tower, World Finance Centre, Harbour City, 1 Canton Road, Tsimshatsui, Kowloon, Hong Kong
Tel: <852> 2265-6688, Fax: <852> 2730-6071

Renesas Technology Taiwan Co., Ltd.

10th Floor, No.99, Fushing North Road, Taipei, Taiwan
Tel: <886> (2) 2715-2888, Fax: <886> (2) 2713-2999

Renesas Technology Singapore Pte. Ltd.

1 Harbour Front Avenue, #06-10, Keppel Bay Tower, Singapore 098632
Tel: <65> 6213-0200, Fax: <65> 6278-8001

Renesas Technology Korea Co., Ltd.

Kukje Center Bldg. 18th Fl., 191, 2-ka, Hangang-ro, Yongsan-ku, Seoul 140-702, Korea
Tel: <82> (2) 796-3115, Fax: <82> (2) 796-2145

Renesas Technology Malaysia Sdn. Bhd

Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No.18, Jalan Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: <603> 7955-9390, Fax: <603> 7955-9510