




FEATURES:

- Used to make your own attenuator, balun or filter.

MATERIALS:

Upper Connector: Double Banana Jack

Brass per QQ-B-626, Alloy 360, ½ hard.

Finish: Nickel plate per QQ-N-290 Class 2 (.0002/.0003)

Insulation: Polypropylene, molded to banana jacks and banana plug bodies. Color: Blue.

Marking: "POMONA ELECTRONICS, CALIF.", "MODEL 1837"

Lower Connector: Double Banana Plug

Spring - Beryllium Copper per QQ-C-533,

Berylco 25, Cond. H.T.

Plug Body – Brass per QQ-B-626, Alloy 360,

½ Hard.

Finish: Nickel plate per QQ-N-290 Class 2 (.0002/.0003)

Solder Turret Terminals:

Brass per QQ-B-626, Alloy 360, ½ Hard.

Finish: Bright tin plated per MIL-T-10727, Type I, (.0001/.0003).

RATINGS:

Operating Temperature: +55°C. (+131°F.) Max.

Operating Voltage: 2500 VDC

Current: 15 Amperes

Contact Resistance: Less than .001 Ohms per banana plug

ORDERING INFORMATION: Model 1837

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA