

4		3		2		1							
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION									
© COPYRIGHT - By -				ALL RIGHTS RESERVED.									
LOC G		DIST 14		REVISIONS									
		P		LTR		DESCRIPTION		DATE		DWN		APVD	
				S1		REVISED PER ECO-11-004917				11MAR11		RK HMR	

BODY

SLEEVE

SERRATION

3.56 ±0.13
[.140±.005]
(FOR #6 STUD)

6.35
[.250]

4.42
[.174] MIN

19.69
[.775] MAX

24.36
[.959] MAX

1

AMP WIRE RANGE

12-10 AWG
SOLID OR STRANDED

UL Listed
FILE E13288

12 AWG
STRANDED

LR7189
Certified

12-10 AWG
SOLID OR STRANDED

1 STAMP 6SAMP 12-10* APPROX AS SHOWN

2. WIRE INSUL DIA, 2.67-5.08 [.105-.200]

3. TONGUE MATL THK, 1.02±0.05 [.040±.002]

4 MATERIAL: BODY - BRASS PER ASTM B36
SLEEVE - PVC, COLOR - YELLOW

50	LOOSE PIECE, BOX	8-52961-2
2500	ON TAPE, REEL	52961-1
500	LOOSE PIECE	52961
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
105°C [221°F]

VOLTAGE RATING:
600V MAX
(1000V FIXTURE OR SIGN)

CIRCULAR MIL AREA:
2.62-6.64mm² [5,180-13,100]
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.
FOR AMP INCORPORATED, IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm[INCHES]

MATERIAL
4

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.20 [.008]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH
TIN PER ASTM B545

DWN
L OLMEDA
26JUN95

CHK
M ELLIS
26JUN95

APVD
G NGO
26JUN95

PRODUCT SPEC
UL 486A

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
TERMINAL, SPRING SPADE,
SHORT, PLASTI-GRIP
WIRE SIZE 12-10 AWG

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-52961

RESTRICTED TO
-

SCALE
6:1

SHEET
1 OF 1

REV
S1

1470-19 (3/11)