

2SB1154

Silicon PNP epitaxial planar type

For power switching


Complementary to 2SD1705

■ Features

- Low collector to emitter saturation voltage $V_{CE(sat)}$
- Satisfactory linearity of forward current transfer ratio h_{FE}
- Large collector current I_C
- Full-pack package which can be installed to the heat sink with one screw

■ Absolute Maximum Ratings ($T_C=25^\circ\text{C}$)

Parameter	Symbol	Ratings	Unit
Collector to base voltage	V_{CBO}	-130	V
Collector to emitter voltage	V_{CEO}	-80	V
Emitter to base voltage	V_{EBO}	-7	V
Peak collector current	I_{CP}	-20	A
Collector current	I_C	-10	A
Collector power dissipation	$T_C=25^\circ\text{C}$	P_C	70
	$T_a=25^\circ\text{C}$		
		3	W
Junction temperature	T_j	150	$^\circ\text{C}$
Storage temperature	T_{stg}	-55 to +150	$^\circ\text{C}$











■ Electrical Characteristics ($T_C=25^\circ\text{C}$)

Parameter	Symbol	Conditions	min	typ	max	Unit
Collector cutoff current	I_{CBO}	$V_{CB} = -100\text{V}, I_E = 0$			-10	μA
Emitter cutoff current	I_{EBO}	$V_{EB} = -5\text{V}, I_C = 0$			-50	μA
Collector to emitter voltage	V_{CEO}	$I_C = -10\text{mA}, I_B = 0$	-80			V
Forward current transfer ratio	h_{FE1}	$V_{CE} = -2\text{V}, I_C = -0.1\text{A}$	45			
	h_{FE2}^*	$V_{CE} = -2\text{V}, I_C = -3\text{A}$	90		260	
	h_{FE3}	$V_{CE} = -2\text{V}, I_C = -6\text{A}$	30			
Collector to emitter saturation voltage	$V_{CE(sat)1}$	$I_C = -6\text{A}, I_B = -0.3\text{A}$			-0.5	V
	$V_{CE(sat)2}$	$I_C = -10\text{A}, I_B = -1\text{A}$			-1.5	V
Base to emitter saturation voltage	$V_{BE(sat)1}$	$I_C = -6\text{A}, I_B = -0.3\text{A}$			-1.5	V
	$V_{BE(sat)2}$	$I_C = -10\text{A}, I_B = -1\text{A}$			-2.5	V
Transition frequency	f_T	$V_{CE} = -10\text{V}, I_C = -0.5\text{A}, f = 10\text{MHz}$		30		MHz
Turn-on time	t_{on}	$I_C = -6\text{A}, I_{B1} = -0.6\text{A}, I_{B2} = 0.6\text{A}, V_{CC} = -50\text{V}$		0.5		μs
Storage time	t_{stg}			1.0		μs
Fall time	t_f			0.2		μs

* h_{FE2} Rank classification

Rank	Q	P
h_{FE2}	90 to 180	130 to 260

$P_C - T_a$  $I_C - V_{CE}$  $V_{CE(\text{sat})} - I_C$  $V_{CE(\text{sat})} - I_C$  $V_{BE(\text{sat})} - I_C$  $h_{FE} - I_C$  $f_T - I_C$  $t_{on}, t_{stg}, t_f - I_C$ 

Area of safe operation (ASO)

