

Inductors, Commercial, Molded, Shielded, Miniature, Axial Leaded



ELECTRICAL SPECIFICATIONS

Inductance Tolerance: $\pm 10\%$ standard, $\pm 5\%$ available

Insulation Resistance: 1000 M Ω minimum per MIL-STD-202, method 302, test condition B

Dielectric Withstanding Voltage: 200 V_{AC} per MIL-STD-202, method 301 (at sea level)

Percent Coupling: 3 % maximum per MIL-PRF-15305

Operating Temperature: - 55 °C to + 105 °C

ENVIRONMENTAL PERFORMANCE		
TEST	CONDITIONS	SPECIFICATIONS
Barometric Pressure	C	MIL-STD-202, method 105
Thermal Shock	A-1	MIL-STD-202, method 107
Flammability	-	MIL-STD-202, method 111
Overload	-	MIL-PRF-15305
Low Temperature Storage	-	MIL-PRF-15305
Resistance to Soldering Heat	A	MIL-STD-202, method 210
Resistance to Solvents	-	MIL-STD-202, method 215

FEATURES

- Flame retardant coating
- Electromagnetic shield
- Small package for a shielded inductor
- Epoxy molded construction provides superior moisture protection
- Precision performance, excellent reliability, sturdy construction
- Compliant to RoHS Directive 2002/95/EC



RoHS
COMPLIANT

MECHANICAL SPECIFICATIONS

Terminal Strength: 3 lb pull per MIL-STD-202, method 211, test condition A, except 180° rotation for a total of 540°

Weight: IMS-2 = 0.30 g maximum

TEST EQUIPMENT ⁽¹⁾

- H/P 4342A Q-meter
- Measurements corporation megacycle meter, model 59
- Wheatstone bridge

Note


⁽¹⁾ Test procedure per MIL-PRF-15305

MATERIAL SPECIFICATIONS

Encapsulant: Epoxy

Standard Terminals: #24 AWG, tinned copper

DIMENSIONS in inches [millimeters]



STANDARD ELECTRICAL SPECIFICATIONS

MODEL	IND. (μH)	TOL. (%)	Q MIN.	TEST FREQUENCY L AND Q (MHz)	SRF MIN. (MHz) ⁽¹⁾	DCR MAX. (Ω)	RATED DC CURRENT (mA) ⁽²⁾	
IMS-2	0.10	± 10	54	25.0	490.0	0.10	670	IRON CORE
IMS-2	0.12	± 10	52	25.0	430.0	0.11	635	
IMS-2	0.15	± 10	50	25.0	415.0	0.12	610	
IMS-2	0.18	± 10	49	25.0	375.0	0.13	585	
IMS-2	0.22	± 10	47	25.0	330.0	0.15	545	
IMS-2	0.27	± 10	46	25.0	300.0	0.16	530	
IMS-2	0.33	± 10	44	25.0	260.0	0.18	495	
IMS-2	0.39	± 10	42	25.0	230.0	0.19	485	
IMS-2	0.47	± 10	41	25.0	220.0	0.21	460	
IMS-2	0.56	± 10	41	25.0	210.0	0.23	440	
IMS-2	0.68	± 10	39	25.0	180.0	0.24	430	
IMS-2	0.82	± 10	38	25.0	165.0	0.27	405	
IMS-2	1.0	± 10	37	25.0	150.0	0.30	385	

Notes

⁽¹⁾ Measured with full length lead

⁽²⁾ Rated DC current based on maximum temperature rise as shown in table

STANDARD ELECTRICAL SPECIFICATIONS

MODEL	IND. (μ H)	TOL. (%)	Q MIN.	TEST FREQUENCY L AND Q (MHz)	SRF MIN. (MHz) ⁽¹⁾	DCR MAX. (Ω)	RATED DC CURRENT (mA) ⁽²⁾	
IMS-2	1.2	± 10	40	7.9	130.0	0.73	247	IRON CORE
IMS-2	1.5	± 10	41	7.9	115.0	0.86	228	
IMS-2	1.8	± 10	43	7.9	105.0	0.95	217	
IMS-2	2.2	± 10	45	7.9	95.0	1.1	202	
IMS-2	2.7	± 10	48	7.9	90.0	1.2	193	
IMS-2	3.3	± 10	49	7.9	80.0	1.3	185	
IMS-2	3.9	± 10	50	7.9	75.0	1.5	173	
IMS-2	4.7	± 10	53	7.9	70.0	2.4	136	
IMS-2	5.6	± 10	54	7.9	60.0	2.9	124	
IMS-2	6.8	± 10	55	7.9	55.0	3.2	118	
IMS-2	8.2	± 10	55	7.9	53.0	3.6	111	
IMS-2	10.0	± 10	57	7.9	50.0	4.0	106	
IMS-2	12.0	± 10	36	2.5	35.0	3.0	122	
IMS-2	15.0	± 10	38	2.5	30.0	3.4	115	
IMS-2	18.0	± 10	40	2.5	26.0	3.8	108	
IMS-2	22.0	± 10	40	2.5	24.0	4.9	96	
IMS-2	27.0	± 10	40	2.5	21.0	5.8	88	
IMS-2	33.0	± 10	41	2.5	20.0	6.5	83	
IMS-2	39.0	± 10	42	2.5	19.0	7.9	75	
IMS-2	47.0	± 10	44	2.5	16.0	9.3	69	
IMS-2	56.0	± 10	44	2.5	15.0	11.0	64	
IMS-2	68.0	± 10	45	2.5	13.0	12.0	61	
IMS-2	82.0	± 10	45	2.5	11.0	13.0	59	
IMS-2	100.0	± 10	40	2.5	10.5	16.8	51	

Notes⁽¹⁾ Measured with full length lead⁽²⁾ Rated DC current based on maximum temperature rise as shown in table**ORDERING INFORMATION**

IMS-2	10 μ H	$\pm 10 \%$	ER	e2
MODEL	INDUCTANCE VALUE	INDUCTANCE TOLERANCE	PACKAGE CODE	JEDEC LEAD (Pb)-FREE STANDARD

GLOBAL PART NUMBER

I	M	S	0	2	E	R	1	0	0	K
MODEL					PACKAGE CODE		INDUCTANCE VALUE			INDUCTANCE TOLERANCE



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.