



Contact arrangement

19 CONTACTS


ARRANGEMENT
CONTACT SIZE
SERVICE RATING




20-A48
16
I



22-14
16
A




24-67
12
A



40-B19
8
A

20 CONTACTS


ARRANGEMENT
CONTACT SIZE
SERVICE RATING




28-16
16
A

22 CONTACTS


ARRANGEMENT
CONTACT SIZE
SERVICE RATING




28-11
4/12 , 18/16
A



32-B22
2/4 , 20/16
A




36-1
4/12 , 18/16
D




36-22
12
D

23 CONTACTS

ARRANGEMENT
CONTACT SIZE
SERVICE RATING




32-6
2/4 , 3/8 , 2/12 , 16/16
A



32-13
5/12 , 18/16
D


24 CONTACTS




24-28
16
I

25 CONTACTS

ARRANGEMENT
CONTACT SIZE
SERVICE RATING




24-A25
16
A




32-A25
12
A

26 CONTACTS



28-12
16
A



40-26
7/8 , 19/12
A

CONTACT LEGEND






CM1 3106 F

CM1 4106 F

Straight plug




Shell size	ØB ±0.1	L Max.	L1 Max.	ØQ ±0.2
10 SL	5.58	55.0	125	22.6
14 S	7.92	58.4	125	29.0
16 S	11.09	60.4	125	31.6
16	11.09	71.8	135	31.6
18	14.27	77.8	140	36.2
20	15.87	74.0	130	39.8
22	15.87	74.0	130	43.0
24	19.05	76.7	130	46.4
28	19.05	83.2	135	53.0
32	23.79	90.3	140	60.0
36	31.75	96.8	145	66.2
40	34.92	115.8	160	72.3

Straight plug.

Includes insulating grommet, backshell,
class A **CM3057** cable clamp and neoprene
sleeve.

No grommet supplied.




HOW TO ORDER

<u>FR</u>	<u>CM1</u>	<u>31</u>	<u>06</u>	<u>A</u>	<u>20-27</u>	<u>P</u>	<u>X</u>	<u>(...)</u>
<i>1</i>	<i>2</i>	<i>3</i>	<i>4</i>	<i>5</i>	<i>6</i>	<i>7</i>	<i>8</i>	<i>9</i>

- 1* Omitted : Standard
FR : Fire Resistant rubber
- 2* CM1 : Bayonet coupling
*CM4 : Bayonet coupling without stainless steel wear pins
- 3* 31 : Solder contacts
41 : Crimp contacts
- 4* Style : 00 - 01 - 02 - 03 - 030 - 05 - 06 - 07 - 070 - 078 - 08 - 26
- 5* Class : A - F - G - GR - RS - SP - Y
- 6* Contact arrangement
- 7* P : Pin contacts
S : Socket contacts
P/S : Contacts for 02PP connectors
- 8* W - X - Y - Z : Alternate positions of the inserts
- 9* Modifications (see the next page)

* Only for receptacles



Metal parts

Aluminium alloy with Cadmium free surface coatings with an olive drab passivation .

Contacts


The following contact types are available :
copper alloy with silver plating (Std) or gold plating (available on request).

Insulating parts

High insulation synthetic rubber resistant to oils and high range of temperatures
(-55°C to +125°C) in accordance with MIL-R-3065.
Are also available in fire resistant and halogen free materials.

Contacts

Contact size	Rated current at 20°C	Max. Contact resist.	Wire size
18	7.5 A	12.0 mΩ	20+26 AWG
16	22 A	6.0 mΩ	16+22 AWG
12	41 A	3.0 mΩ	12-14 AWG
8	73 A	1.0 mΩ	8-10 AWG
4	135 A	0.5 mΩ	4-6 AWG
0	245 A	0.3 mΩ	0+2 AWG
4/0	350 A	0.2 mΩ	4/0 AWG



Service rating (Min insulating resistance : $\geq 5 \times 10^3 \text{ M}\Omega$)

Class	Operating voltage Vdc	Operating voltage VacRMS	Test voltage Vac RMS
INST.	250 V	200 V	1000 V
A	700 V	500 V	2000 V
D	1250 V	900 V	2800 V
E	1750 V	1250 V	3500 V
B	2450 V	1750 V	4500 V
C	4200 V	3000 V	7000 V