

	13	12	11	10	9	8	7	6	5	4	3	2	1	
J	PART NO.	CIRCUITS	LENGTH ±.01 [.25]	WIDTH ±.004 [.10]	NOTES: 1. SUBSTRATE AND COVERLAY MATERIAL IS .001 [25uM] POLYIMIDE. 2. CONDUCTOR IS 1/2 OZ (.0007) [18uM] COPPER. 3. PLATING IS 2 MICRO INCHES MINIMUM OF HARD GOLD OVER 100 MICRO INCHES MINIMUM OF NICKEL. 4. TAIL ENDS ARE .008 [.20] THICK. 5. JUMPER CABLES ARE SUITABLE FOR USE WITH MOLEX 502598 SERIES CONNECTOR.									J
	150150223	23	2.00 [50.8]	.283 [7.2]										J
	150150423	23	4.00 [101.6]	.283 [7.2]										J
I	150150623	23	6.00 [152.4]	.283 [7.2]										I
	150150823	23	8.00 [203.2]	.283 [7.2]										I
	150151023	23	10.00 [254.0]	.283 [7.2]										I
H	150150225	25	2.00 [50.8]	.307 [7.8]										H
	150150425	25	4.00 [101.6]	.307 [7.8]										H
	150150625	25	6.00 [152.4]	.307 [7.8]										H
G	150150825	25	8.00 [203.2]	.307 [7.8]										G
	150151025	25	10.00 [254.0]	.307 [7.8]										G
	150150227	27	2.00 [50.8]	.331 [8.4]										G
F	150150427	27	4.00 [101.6]	.331 [8.4]										F
	150150627	27	6.00 [152.4]	.331 [8.4]										F
	150150827	27	8.00 [203.2]	.331 [8.4]										F
E	150151027	27	10.00 [254.0]	.331 [8.4]										E
	150150229	29	2.00 [50.8]	.354 [9.0]										E
	150150429	29	4.00 [101.6]	.354 [9.0]										E
D	150150629	29	6.00 [152.4]	.354 [9.0]										D
	150150829	29	8.00 [203.2]	.354 [9.0]										D
	150151029	29	10.00 [254.0]	.354 [9.0]										D
C	150150233	33	2.00 [50.8]	.403 [10.2]										C
	150150433	33	4.00 [101.6]	.403 [10.2]										C
	150150633	33	6.00 [152.4]	.403 [10.2]										C
B	150150833	33	8.00 [203.2]	.403 [10.2]										B
	150151033	33	10.00 [254.0]	.403 [10.2]										B
	150150239	39	2.00 [50.8]	.472 [12.0]										B
A	150150439	39	4.00 [101.6]	.472 [12.0]										A
	150150639	39	6.00 [152.4]	.472 [12.0]										A
	150150839	39	8.00 [203.2]	.472 [12.0]										A
A	150151039	39	10.00 [254.0]	.472 [12.0]										A
	150150245	45	2.00 [50.8]	.543 [13.8]										A
	150150445	45	4.00 [101.6]	.543 [13.8]										A
A	150150645	45	6.00 [152.4]	.543 [13.8]										A
	150150845	45	8.00 [203.2]	.543 [13.8]										A
	150151045	45	10.00 [254.0]	.543 [13.8]										A
A	150150251	51	2.00 [50.8]	.614 [15.6]										A
	150150451	51	4.00 [101.6]	.614 [15.6]										A
	150150651	51	6.00 [152.4]	.614 [15.6]										A
A	150150851	51	8.00 [203.2]	.614 [15.6]										A
	150151051	51	10.00 [254.0]	.614 [15.6]										A
15015 NUMBER OF CIRCUITS LENGTH SERIES NUMBER PART NUMBER CONSTRUCTION														
UPDATED NOTE 5 EC NO.: USW2013-0117 DRWN:MFI 2013/01/23 DESCRIPTION REV QUALITY SYMBOL ▽=0 ▽C=0 GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH DIMENSION STYLE INCH [MM] DRAWN BY DATE TITLE SCALE NONE DESIGN UNITS METRIC THIRD ANGLE PROJECTION APPROVED BY DATE MATERIAL NO. DOCUMENT NO. SHEET NO. SIZE C THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS ANGULAR ±1° MOLEX INCORPORATED SD-15015-001 1 OF 1														
13	12	11	10	9	8	7	6	5	4	3	2	1		