







MHSS Series

Microminiature Slide Switches

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

SPECIFICATIONS	FEATURES
Contact ratings: 300 mA at 6 VDC Initial contact resistance: 60 milliohms max. Insulation resistance: 100 megohms min. at 100 VDC Dielectric strength: 100 VAC for 1 minute Electrical life: 5000 cycles min. Operating temperature range: -20°C to +70°C Solder heat resistance: 350°C max. for 3 seconds Washing not recommended	- Excellent tactile feed-back (detent action). - Molded-in terminals minimize flux or solder entry. - Ultra-compact case size. - Low profile.
	MATERIALS
	Contacts & terminals: Silver plated Case: 30% Glass filled nylon, type 6/6, black Actuator: Nylon, type 6/6, black (blue for MHSS2220 only)

MODEL NO.	1P2T	.335 [8.50]	.079 (2.00) TRAVEL/THROW
MHSS1104			
	 ● = COMMON	 MECHANICAL OUTLINE	 P.C. BOARD LAYOUT
VERTICAL ACTUATOR	SCHEMATIC	MECHANICAL OUTLINE	P.C. BOARD LAYOUT
MODEL NO.	1P2T	.335 [8.50]	.079 (2.00) TRAVEL/THROW
MHSS1105			
	 ● = COMMON	 MECHANICAL OUTLINE	 P.C. BOARD LAYOUT
RIGHT ANGLE ACTUATOR	SCHEMATIC	MECHANICAL OUTLINE	P.C. BOARD LAYOUT