

## Features

## Unregulated Converters

- Fully RoHS 6/6 Conform
- Full Power at 100°C Ambient Temperature
- 1kVDC or 3kVDC Isolation Options
- Suitable for Fully Automated Assembly (including Vapor Phase Soldering)
- Optional Continuous Short Circuit Protection
- Built-In EN55022 Class A Filter

### Description

The R0.25S and R0.25D converters are of the enclosed open frame type, i.e. they are not potted. The converters are typically used in general purpose and industrial low over isolation and voltage matching applications where an SMD converter is required. The converter series feature an extended ambient temperature operating range of -40°C to +100°C without derating and optional continuous short circuit protection. In addition to single, dual and independent outputs, two isolation options and three different case formats, the converters are also available prepacked as tape and reel for use with automatic insertion machines.

### Selection Guide

| Part Number SMD  | (3kV) | Input Voltage (VDC) | Output Voltage (VDC) | Output Current (mA) | Capacitive Load (max.) |
|------------------|-------|---------------------|----------------------|---------------------|------------------------|
| R0.25S**-xx3.3   | (H)   | 3.3, 5, 12, 15, 24  | 3.3                  | 76                  | 1000µF                 |
| R0.25S**-xx05    | (H)   | 3.3, 5, 12, 15, 24  | 5                    | 50                  | 470µF                  |
| R0.25S**-xx09    | (H)   | 3.3, 5, 12, 15, 24  | 9                    | 28                  | 470µF                  |
| R0.25S**-xx12    | (H)   | 3.3, 5, 12, 15, 24  | 12                   | 21                  | 150µF                  |
| R0.25S**-xx15    | (H)   | 3.3, 5, 12, 15, 24  | 15                   | 17                  | 68µF                   |
| R0.25S**-xx24    | (H)   | 3.3, 5, 12, 15, 24  | 24                   | 10.4                | 68µF                   |
| R0.25D**-xx3.3   | (H)   | 3.3, 5, 12, 15, 24  | ±3.3                 | ±38                 | 470µF                  |
| R0.25D**-xx05    | (H)   | 3.3, 5, 12, 15, 24  | ±5                   | ±25                 | 220µF                  |
| R0.25D**-xx09    | (H)   | 3.3, 5, 12, 15, 24  | ±9                   | ±14                 | 68µF                   |
| R0.25D**-xx12    | (H)   | 3.3, 5, 12, 15, 24  | ±12                  | ±10.4               | 68µF                   |
| R0.25D**-xx15    | (H)   | 3.3, 5, 12, 15, 24  | ±15                  | ±8.3                | 68µF                   |
| R0.25D**-xx24    | (H)   | 3.3, 5, 12, 15, 24  | ±24                  | ±5.2                | 33µF                   |
| R0.25DA**-xx0505 |       | 3.3, 5, 12, 15, 24  | 5/5                  | 25/25               | 220µF/220µF            |
| R0.25DA**-xx1212 |       | 3.3, 5, 12, 15, 24  | 12/12                | 10/10               | 68µF/68µF              |

xx = Input Voltage (other input and output voltage combinations available on request)

\* add Suffix "H" for 3kV Isolation, e.g. R0.25S-0505/H, R0.25D-0505/H, R0.25S12-0505/H, R0.25D12-0505/H

\* add Suffix "P" for Continuous Short Circuit Protection, e.g. R0.25S8-0505/P, R0.25S-0505/HP, R0.25D12-0505/HP

\* add suffix -R for tape & reel packing e.g. R0.25S-0505-R. For more details see Application Notes.

### Case and Pinning Options (note restrictions on /H option)

- R0.25S\*\* : \*\* without marking denotes 5 pins out of 8 fitted (includes /H option)  
 \*\* with marking **8** denotes 8 pins out of 8 fitted (/H option not available)  
 \*\* with marking **12** denotes 10 pins out of 12 fitted (includes /H option)
- R0.25D\*\* : \*\* without marking denotes 6 pins out of 10 fitted (includes /H option, no DA option)  
 R0.25D(A) : \*\* with marking **10** denotes with 10 pins out of 10 fitted (/H option not available)  
 R0.25D(A) : \*\* with marking **12** denotes 10 pins out of 12 fitted (includes /H option - except R0.25DA)

### Specifications (measured at $T_A = 25^\circ\text{C}$ , nominal input voltage, full load and after warm-up)

|                                            |                                      |                    |
|--------------------------------------------|--------------------------------------|--------------------|
| Input Voltage Range                        | ±10%                                 |                    |
| Output Voltage Accuracy                    | ±5% typ., ±7% max.                   |                    |
| Line Voltage Regulation                    | (low line to high line at max. load) | 2% max.            |
| Load Voltage Regulation                    | 3.3V output types                    | 15% typ., 20% max. |
| (10% to 100% full load)                    | 5V, 5/5V output types                | 12% typ., 15% max. |
|                                            | 9V output type                       | 7% typ., 10% max.  |
|                                            | 12V, 12/12V, 15V, 24V output types   | 6% typ., 10% max.  |
| Output Ripple and Noise (20MHz BW limited) | 100mVp-p max.                        |                    |
| Operating Frequency                        | 20kHz min. / 50kHz typ. / 90kHz max. |                    |

continued on next page

# ECONOLINE

## DC/DC-Converter

# RECOM

## 0.25 Watt SMD Single, Dual & Independent Outputs




**UL-60950-1 Certified**  
**EN-60950-1 Certified**  
**EN-60601-1 Certified\***  
 \*(/H suffix)


# R0.25S R0.25D(A)

## Derating-Graph (Ambient Temperature)

### Standard Case



### Big Case (with marking 12)



Refer to Application Notes

[www.recom-power.com](http://www.recom-power.com)

**Specifications** (measured at  $T_A = 25^\circ\text{C}$ , nominal input voltage, full load and after warm-up)

|                                                   |                                                                                 |                                                                                                            |
|---------------------------------------------------|---------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------|
| Efficiency at Full Load                           |                                                                                 | 60%-70%                                                                                                    |
| Minimum Load = 0%                                 |                                                                                 | Specifications valid for 10% minimum load only                                                             |
| Isolation Voltage                                 | (tested for 1 second)<br>(rated for 1 minute***)                                | 1000VDC                                                                                                    |
|                                                   |                                                                                 | 500VAC / 60Hz                                                                                              |
| H-Suffix                                          | (tested for 1 second)<br>(rated for 1 minute***)                                | 3000VDC                                                                                                    |
|                                                   |                                                                                 | 1500VAC / 60Hz                                                                                             |
| R0.25DA Output/ Output Isolation Voltage          | (tested for 1 second)                                                           | 1000VDC                                                                                                    |
| Isolation Capacitance                             |                                                                                 | 75pF max.                                                                                                  |
| Isolation Resistance                              | $V_{iso}=500V$                                                                  | 10 $\text{G}\Omega$ min.                                                                                   |
| Short Circuit Protection                          |                                                                                 | 1 Second                                                                                                   |
| P-Suffix                                          |                                                                                 | Continuous                                                                                                 |
| Operating Temperature Range (free air convection) |                                                                                 | -40°C to +100°C (see Graph)                                                                                |
| Storage Temperature Range                         |                                                                                 | -50°C to +125°C                                                                                            |
| Reflow Temperature                                | ROHS compliant                                                                  | 245°C (30 sec), Peak 255°C (5 sec) max.                                                                    |
| Vapor Phase Process                               | (for more details see Application Notes)                                        | 230°C (90 sec) max.                                                                                        |
| Relative Humidity                                 |                                                                                 | 95% RH                                                                                                     |
| Humidity Susceptibility Test                      |                                                                                 | 1000 hrs / 90% humidity / +85°C ambient                                                                    |
| Package weight                                    |                                                                                 | 1.0g (R0.25S), 1.2g (R0.25D(A))                                                                            |
| Packing Quantity                                  | R0.25S, R0.25S8<br>R0.25S12, R0.25D, R0.25D10<br>R0.25D12, R0.25DA<br>All Types | 40 pcs per Tube<br>33 pcs per tube<br>33 pcs per tube<br>500 pcs per Reel                                  |
| MTBF (+25°C)<br>(+85°C)                           | Detailed Information see<br>Application Notes chapter "MTBF"                    | using MIL-HDBK 217F<br>4423 x 10 <sup>3</sup> hours<br>using MIL-HDBK 217F<br>2161 x 10 <sup>3</sup> hours |
| Certifications                                    |                                                                                 |                                                                                                            |
| Conducted / Radiated Emissions                    | EN55022                                                                         | Level A                                                                                                    |
| CB Test Report                                    | Report: US/14402A/UL                                                            | IEC 60950-1:2001 1st Ed.                                                                                   |
| UL General Safety                                 | Report: E358085                                                                 | UL 60950-1 2nd Ed.                                                                                         |
| CUL General Safety                                |                                                                                 | C22.2 No. 60950-1-03                                                                                       |
| EN Medical Safety                                 | Report: MDD1205098-2 + RM1205098-2<br>Medical Report + ISO14971 Risk Assessment | IEC/EN 60601-1 3rd Edition                                                                                 |
| EN General Safety                                 | Report: SPCLVD1211033-3                                                         | EN60950-1:2006 + A12:2011                                                                                  |


\*\*\*Any data referred to in this datasheet are of indicative nature and based on our practical experience only. For further details, please refer to our Application Notes.

**Notes**


Note 1: Maximum capacitive load is defined as the capacitive load that will allow start up in under 1 second without damage to the converter.

**Typical Characteristics**


**Tolerance Envelope**



**R0.25S\*\*-xx05**



**R0.25D\*\*-xx05**







**Package Style and Pinning (mm)**


**5 PIN Single SMD Package**

Note: /H option is available in these pin packages

**6 PIN Dual SMD Package**



**Recommended Footprint Details**



**Pin Connections**


| Pin # | Single | Dual   |
|-------|--------|--------|
| 1     | -Vin   | -Vin   |
| 2     | +Vin   | +Vin   |
| 4     | -Vout  | Com    |
| 5     | +Vout  | -Vout  |
| 7     | No Pin | +Vout  |
| 8     | NC     | No Pin |
| 10    | No Pin | NC     |

NC = No Connection

XX.X ± 0.5 mm

XX.XX ± 0.25 mm





**Recommended Footprint Details**




**8 PIN Single SMD Package**

Note: /H option is not available in these pin packages

**10 PIN Dual SMD Package**



**Recommended Footprint Details**



**Pin Connections**


| Pin # | Single | Dual  | Dual Independent |
|-------|--------|-------|------------------|
| 1     | -Vin   | -Vin  | -Vin             |
| 2     | +Vin   | +Vin  | +Vin             |
| 3     | NC     | NC    | No Pin           |
| 4     | -Vout  | Com   | -Vout1           |
| 5     | +Vout  | -Vout | +Vout1           |
| 6     | NC     | NC    | -Vout2           |
| 7     | NC     | +Vout | +Vout2           |
| 8     | NC     | NC    | No Pin           |
| 9     | -      | NC    | No Pin           |
| 10    | -      | NC    | NC               |

NC = No Connection


XX.X ± 0.5 mm

XX.XX ± 0.25 mm

**Recommended Footprint Details (Dual)**



**Recommended Footprint Details Dual Independent**



R0.25S\*\* : \*\* without marking denotes 5 pins out of 8 fitted (includes /H option)  
\*\* with marking **8** denotes 8 pins out of 8 fitted (/H option not available)

e.g. R0.25S-0505, R0.25S-0505/H, R0.25S-0505/HP  
e.g. R0.25S8-0505, R0.25S8-0505/P




R0.25D\*\* : \*\* without marking denotes 6 pins out of 10 fitted (includes /H option)  
\*\* with marking **10** denotes with 10 pins out of 10 fitted (/H option not available)

e.g. R0.25D-0505, R0.25D-0505/H, R0.25D-0505/HP  
e.g. R0.25D10-0505, R0.25D10-0505/P

## Package Style and Pinning (mm)

### 12 PIN Single and Dual SMD Package

Note: /H option is available in this pin package





#### Pin Connections

| Pin # | Single | Dual  |
|-------|--------|-------|
| 1     | -Vin   | -Vin  |
| 2     | +Vin   | +Vin  |
| 3     | NC     | NC    |
| 5     | -Vout  | Com   |
| 6     | NC     | -Vout |
| 7     | NC     | NC    |
| 8     | +Vout  | +Vout |
| 10    | NC     | NC    |
| 11    | NC     | NC    |
| 12    | NC     | NC    |

NC = No Connection  
XX.X ± 0.5 mm  
XX.XX ± 0.25 mm


#### Recommended Footprint Details



R0.25S\*\* : \*\* with marking **12** denotes 10 pins out of 12 fitted (includes /H option)  
e.g. R0.25S12-0505  
R0.25S12-0505/H  
R0.25S12-0505/HP

R0.25D\*\* : \*\* with marking **12** denotes 10 pins out of 12 fitted (includes /H option)  
e.g. R0.25D12-0505  
R0.25D12-0505/H  
R0.25D12-0505/HP

## EMC Filtering - Suggestion for EN55022 Class B (Conducted and Emitted)



#### Standard and /H versions

| C1    | L1    | Vin  |
|-------|-------|------|
| 2.2µF | 3.3µH | 3.3V |
| 2.2µF | 4.7µH | 5V   |
| 1.0µF | 22µH  | 12V  |
| 1.0µF | 22µH  | 15V  |
| 470nF | 47µH  | 24V  |

#### /P and /HP versions

| C1    | L1    | Vin  |
|-------|-------|------|
| 2.2µF | 3.3µH | 3.3V |
| 2.2µF | 4.7µH | 5V   |
| 1.0µF | 22µH  | 12V  |
| 1.0µF | 22µH  | 15V  |
| 470nF | 47µH  | 24V  |

C1 = MLCC  
L1 = SMD Inductor