

LEXANTM COPOLYMER EXL1112

REGION AMERICAS

DESCRIPTION

LEXAN EXL1112 polycarbonate (PC) siloxane copolymer resin is a high flow opaque injection molding (IM) grade. This resin offers good low temperature (-20 C) ductility in combination with excellent processability and release with opportunities for shorter IM cycle times compared to standard PC. LEXAN EXL1112 resin is a product available in wide range of opaque colors and may be an excellent candidate for a wide variety of applications.

TYPICAL PROPERTY VALUES

Revision 20190103

PROPERTIES	TYPICAL VALUES	UNITS	TEST METHODS
MECHANICAL			
Tensile Stress, yld, Type I, 50 mm/min	58	MPa	ASTM D 638
Tensile Stress, brk, Type I, 50 mm/min	58	MPa	ASTM D 638
Tensile Strain, yld, Type I, 50 mm/min	5.8	%	ASTM D 638
Tensile Strain, brk, Type I, 50 mm/min	109	%	ASTM D 638
Tensile Modulus, 50 mm/min	2280	MPa	ASTM D 638
Flexural Stress, yld, 1.3 mm/min, 50 mm span	95	MPa	ASTM D 790
Flexural Modulus, 1.3 mm/min, 50 mm span	2320	MPa	ASTM D 790
Tensile Stress, yield, 50 mm/min	57	MPa	ISO 527
Tensile Stress, break, 50 mm/min	55	MPa	ISO 527
Tensile Strain, yield, 50 mm/min	5	%	ISO 527
Tensile Strain, break, 50 mm/min	100	%	ISO 527
Tensile Modulus, 1 mm/min	2150	MPa	ISO 527
Flexural Stress, yield, 2 mm/min	85	MPa	ISO 178
Flexural Modulus, 2 mm/min	2240	MPa	ISO 178
Hardness, H358/30	95	MPa	ISO 2039-1
IMPACT			
Izod Impact, notched, 23°C	747	J/m	ASTM D 256
Izod Impact, notched, -30°C	667	J/m	ASTM D 256
Instrumented Impact Total Energy, 23°C	69	J	ASTM D 3763
Izod Impact, unnotched 80*10*3 +23°C	NB	kJ/m ²	ISO 180/1U
Izod Impact, unnotched 80*10*3 -30°C	NB	kJ/m ²	ISO 180/1U
Izod Impact, notched 80*10*3 +23°C	55	kJ/m ²	ISO 180/1A
Izod Impact, notched 80*10*3 -30°C	20	kJ/m ²	ISO 180/1A
Charpy 23°C, V-notch Edgew 80*10*3 sp=62mm	60	kJ/m ²	ISO 179/1eA
Charpy -30°C, V-notch Edgew 80*10*3 sp=62mm	25	kJ/m ²	ISO 179/1eA
Charpy 23°C, Unnotch Edgew 80*10*3 sp=62mm	NB	kJ/m ²	ISO 179/1eU
Charpy -30°C, Unnotch Edgew 80*10*3 sp=62mm	NB	kJ/m ²	ISO 179/1eU
THERMAL			
Vicat Softening Temp, Rate B/50	144	°C	ASTM D 1525
HDT, 0.45 MPa, 3.2 mm, unannealed	136	°C	ASTM D 648
HDT, 1.82 MPa, 3.2mm, unannealed	123	°C	ASTM D 648
CTE, -40°C to 40°C, flow	7.2E-05	1/°C	ASTM E 831
CTE, -40°C to 40°C, xflow	7.56E-05	1/°C	ASTM E 831

PROPERTIES	TYPICAL VALUES	UNITS	TEST METHODS
CTE, 23°C to 80°C, flow	7.5E-05	1/°C	ISO 11359-2
CTE, 23°C to 80°C, xflow	7.5E-05	1/°C	ISO 11359-2
Ball Pressure Test, 125°C +/- 2°C	PASSES	-	IEC 60695-10-2
Vicat Softening Temp, Rate B/50	144	°C	ISO 306
Vicat Softening Temp, Rate B/120	145	°C	ISO 306
HDT/Ae, 1.8 MPa Edgew. 120*10*4 sp=100mm	125	°C	ISO 75/Ae
HDT/Be, 0.45 MPa edgew. Annealed 80°C, 4 hrs	136	°C	ISO 75/Be
Relative Temp Index, Elec	130	°C	UL 746B
Relative Temp Index, Mech w/impact	120	°C	UL 746B
Relative Temp Index, Mech w/o impact	125	°C	UL 746B
PHYSICAL			
Specific Gravity	1.18	-	ASTM D 792
Mold Shrinkage, flow, 3.2 mm	0.4 – 0.8	%	SABIC method
Mold Shrinkage, xflow, 3.2 mm	0.4 – 0.8	%	SABIC method
Melt Flow Rate, 300°C/1.2 kgf	17	g/10 min	ASTM D 1238
Density	1.19	g/cm³	ISO 1183
Water Absorption, (23°C/sat)	0.35	%	ISO 62
Moisture Absorption (23°C / 50% RH)	0.15	%	ISO 62
Melt Volume Rate, MVR at 300°C/1.2 kg	16	cm³/10 min	ISO 1133
FLAME CHARACTERISTICS			
Glow Wire Flammability Index 850°C, passes at	0.8	mm	IEC 60695-2-12
Glow Wire Flammability Index 960°C, passes at	3	mm	IEC 60695-2-12
Glow Wire Ignitability Temperature, 1.0 mm	875	°C	IEC 60695-2-13
Glow Wire Ignitability Temperature, 3.0 mm	875	°C	IEC 60695-2-13
Oxygen Index (LOI)	32	%	ISO 4589
INJECTION MOLDING			
Drying Temperature	120	°C	
Drying Time	3 – 4	hrs	
Drying Time (Cumulative)	48	hrs	
Maximum Moisture Content	0.02	%	
Melt Temperature	295 – 315	°C	
Nozzle Temperature	290 – 310	°C	
Front - Zone 3 Temperature	295 – 315	°C	
Middle - Zone 2 Temperature	280 – 305	°C	
Rear - Zone 1 Temperature	270 – 295	°C	
Mold Temperature	70 – 95	°C	
Back Pressure	0.3 – 0.7	MPa	
Screw Speed	40 – 70	rpm	
Shot to Cylinder Size	40 – 60	%	
Vent Depth	0.025 – 0.076	mm	



DISCLAIMER

Any sale by SABIC, its subsidiaries and affiliates (each a "seller"), is made exclusively under seller's standard conditions of sale (available upon request) unless agreed otherwise in writing and signed on behalf of the seller. While the information contained herein is given in good faith, SELLER MAKES NO WARRANTY, EXPRESS OR IMPLIED, INCLUDING MERCHANTABILITY AND NONINFRINGEMENT OF INTELLECTUAL PROPERTY, NOR ASSUMES ANY LIABILITY, DIRECT OR INDIRECT, WITH RESPECT TO THE PERFORMANCE, SUITABILITY OR FITNESS FOR INTENDED USE OR PURPOSE OF THESE PRODUCTS IN ANY APPLICATION. Each customer must determine the suitability of seller materials for the customer's particular use through appropriate testing and analysis. No statement by seller concerning a possible use of any product, service or design is intended, or should be construed, to grant any license under any patent or other intellectual property right.