


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS				DOC. NO.	SPC-FD05	Effective:	12/21/98	DCP No:	880
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
	A	Redrawn in autocad	JAP	11/28/91					
1199	B	Renamed was CSS-TO-****-HT	JWM	1/7/02	JC	3/1/02	JC	3/1/02	



- NOTES
- 1. Material: Steel - Nickel Plated
 - 2. Operating Temp: 900°F [482°C]

SPC Type No.	Wire Range (AWG)	Stud Size	W	C	L	E	Thickness	Barrel Length	Barrel I.D.
CSS-TO-1010-HT	12 ~ 10	10	.38	.28	.73	.53	.040	.25	.135
CSS-TO-1410-HT	16 ~ 14		.34	.29	.70	.54	.030	.25	.090
CSS-TO-1810-HT	22 ~ 18		.34	.29	.70	.54	.030	.25	.070

DISCLAIMER

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

SPC TECHNOLOGY

DRAWING TITLE:

High Temperature Butted Seam Standard Fork Terminals

DRAWN BY:

JC

CHECKED BY:

JC

APPROVED BY:

JL

DATE:

3/1/91

DATE:

11/27/91

DATE:

11/27/91

SIZE

DWG. NO.

ELECTRONIC FILE

REV

A

TA-484

TA-484.dwg

B

SCALE:

NTS

U.O.M.: INCHES [mm]

SHEET:

1 OF 1

Tolerances: Unless Otherwise Specified:

X = ±.015

.XX = ±.010

.XXX = ±.005

SPC-FD05.DWG