

# Switch-mode Power Rectifiers

## DPAK Surface Mount Package

### MBRD320G, MBRD330G, MBRD340G, MBRD350G, MBRD360G

These state-of-the-art devices are designed for use as output rectifiers, free wheeling, protection and steering diodes in switching power supplies, inverters and other inductive switching circuits.

#### Features

- Extremely Fast Switching
- Extremely Low Forward Drop
- Platinum Barrier with Avalanche Guardrings
- NRVBD and SBRD Prefixes for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant


#### Mechanical Characteristics:

- Case: Epoxy, Molded
- Weight: 0.4 Gram (Approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead and Mounting Surface Temperature for Soldering Purposes; 260°C Max. for 10 Seconds
- ESD Ratings:
  - ♦ Machine Model = C
  - ♦ Human Body Model = 3B


## SCHOTTKY BARRIER RECTIFIERS 3.0 AMPERES, 20 – 60 VOLTS



DPAK  
CASE 369C



#### MARKING DIAGRAM



|      |                      |
|------|----------------------|
| A    | = Assembly Location* |
| Y    | = Year               |
| WW   | = Work Week          |
| B3x0 | = Device Code        |
| x    | = 2, 3, 4, 5, or 6   |
| G    | = Pb-Free Package    |

\* The Assembly Location Code (A) is front side optional. In cases where the Assembly Location is stamped in the package bottom (molding ejecter pin), the front side assembly code may be blank.

#### ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 3 of this data sheet.

NOTE: Some of the devices on this data sheet have been **DISCONTINUED**. Please refer to the table on page 3.

# MBRD320G, MBRD330G, MBRD340G, MBRD350G, MBRD360G

## MAXIMUM RATINGS

| Rating                                                                                                     | Symbol                          | MBRD/SBRD8  |     |     |     |     | Unit             |
|------------------------------------------------------------------------------------------------------------|---------------------------------|-------------|-----|-----|-----|-----|------------------|
|                                                                                                            |                                 | 320         | 330 | 340 | 350 | 360 |                  |
| Peak Repetitive Reverse Voltage<br>Working Peak Reverse Voltage<br>DC Blocking Voltage                     | $V_{RRM}$<br>$V_{RWM}$<br>$V_R$ | 20          | 30  | 40  | 50  | 60  | V                |
| Average Rectified Forward Current ( $T_C = +125^\circ\text{C}$ )                                           | $I_{F(AV)}$                     | 3           |     |     |     |     | A                |
| Peak Repetitive Forward Current, $T_C = +125^\circ\text{C}$<br>(Square Wave, Duty = 0.5)                   | $I_{FRM}$                       | 6           |     |     |     |     | A                |
| Nonrepetitive Peak Surge Current<br>(Surge applied at rated load conditions halfwave, single phase, 60 Hz) | $I_{FSM}$                       | 75          |     |     |     |     | A                |
| Peak Repetitive Reverse Surge Current (2 $\mu\text{s}$ , 1 kHz)                                            | $I_{RRM}$                       | 1           |     |     |     |     | A                |
| Operating Junction Temperature Range (Note 1)                                                              | $T_J$                           | -65 to +175 |     |     |     |     | $^\circ\text{C}$ |
| Storage Temperature Range                                                                                  | $T_{stg}$                       | -65 to +175 |     |     |     |     | $^\circ\text{C}$ |
| Voltage Rate of Change (Rated $V_R$ )                                                                      | $dv/dt$                         | 10,000      |     |     |     |     | V/ $\mu\text{s}$ |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. The heat generated must be less than the thermal conductivity from Junction-to-Ambient:  $dP_D/dT_J < 1/R_{\theta JA}$ .

## THERMAL CHARACTERISTICS

| Characteristic                                           | Symbol          | Value | Unit               |
|----------------------------------------------------------|-----------------|-------|--------------------|
| Maximum Thermal Resistance, Junction-to-Case             | $R_{\theta JC}$ | 6     | $^\circ\text{C/W}$ |
| Maximum Thermal Resistance, Junction-to-Ambient (Note 2) | $R_{\theta JA}$ | 80    | $^\circ\text{C/W}$ |

2. Rating applies when surface mounted on the minimum pad size recommended.

## ELECTRICAL CHARACTERISTICS

| Characteristic                                                                                                                                                                                                                                                           | Symbol | Value                       | Unit |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------|-----------------------------|------|
| Maximum Instantaneous Forward Voltage (Note 3)<br>$i_F = 3 \text{ Amps}$ , $T_C = +25^\circ\text{C}$<br>$i_F = 3 \text{ Amps}$ , $T_C = +125^\circ\text{C}$<br>$i_F = 6 \text{ Amps}$ , $T_C = +25^\circ\text{C}$<br>$i_F = 6 \text{ Amps}$ , $T_C = +125^\circ\text{C}$ | $V_F$  | 0.6<br>0.45<br>0.7<br>0.625 | V    |
| Maximum Instantaneous Reverse Current (Note 3)<br>(Rated dc Voltage, $T_C = +25^\circ\text{C}$ )<br>(Rated dc Voltage, $T_C = +125^\circ\text{C}$ )                                                                                                                      | $i_R$  | 0.2<br>20                   | mA   |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

3. Pulse Test: Pulse Width = 300  $\mu\text{s}$ , Duty Cycle  $\leq 2.0\%$ .

# MBRD320G, MBRD330G, MBRD340G, MBRD350G, MBRD360G

## ORDERING INFORMATION

| Device            | Package           | Shipping†         |
|-------------------|-------------------|-------------------|
| MBRD340T4G        | DPAK<br>(Pb-Free) | 2,500 Tape & Reel |
| SBRD8340T4G-VF01* |                   | 2,500 Tape & Reel |
| MBRD350T4G        |                   | 2,500 Tape & Reel |
| MBRD360T4G        |                   | 2,500 Tape & Reel |
| NRVBD360VT4G*     |                   | 2,500 Tape & Reel |

## DISCONTINUED (Note 4)

|                   |                   |                   |
|-------------------|-------------------|-------------------|
| MBRD320G          | DPAK<br>(Pb-Free) | 75 Units / Rail   |
| SBRD8320G*        |                   | 75 Units / Rail   |
| SBRD8320G-VF01*   |                   | 75 Units / Rail   |
| MBRD320RLG        |                   | 1,800 Tape & Reel |
| MBRD320T4G        |                   | 2,500 Tape & Reel |
| SBRD8320T4G*      |                   | 2,500 Tape & Reel |
| SBRD8320T4G-VF01* |                   | 2,500 Tape & Reel |
| MBRD330G          |                   | 75 Units / Rail   |
| SBRD8330G*        |                   | 75 Units / Rail   |
| SBRD8330G-VF01*   |                   | 75 Units / Rail   |
| MBRD330RLG        |                   | 1,800 Tape & Reel |
| MBRD330T4G        |                   | 2,500 Tape & Reel |
| SBRD8330T4G*      |                   | 2,500 Tape & Reel |
| SBRD8330T4G-VF01* |                   | 2,500 Tape & Reel |
| MBRD340G          |                   | 75 Units / Rail   |
| SBRD8340G*        |                   | 75 Units / Rail   |
| SBRD8340G-VF01*   |                   | 75 Units / Rail   |
| MBRD340RLG        |                   | 1,800 Tape & Reel |
| SBRD8340T4G*      |                   | 2,500 Tape & Reel |
| MBRD350G          |                   | 75 Units / Rail   |
| SBRD8350G*        |                   | 75 Units / Rail   |
| SBRD8350G-VF01*   |                   | 75 Units / Rail   |
| MBRD350RLG        |                   | 1,800 Tape & Reel |
| SBRD8350RLG*      |                   | 1,800 Tape & Reel |
| SBRD8350RLG-VF01* |                   | 1,800 Tape & Reel |
| SBRD8350T4G*      |                   | 2,500 Tape & Reel |
| SBRD8350T4G-VF01* |                   | 2,500 Tape & Reel |
| MBRD360G          |                   | 75 Units / Rail   |
| SBRD8360G*        |                   | 75 Units / Rail   |
| SBRD8360G-VF01*   |                   | 75 Units / Rail   |
| MBRD360RLG        |                   | 1,800 Tape & Reel |
| SBRD8360RLG*      |                   | 1,800 Tape & Reel |
| SBRD8360RLG-VF01* |                   | 1,800 Tape & Reel |
| SBRD8360T4G*      |                   | 2,500 Tape & Reel |

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

\*NRVBD and SBRD Prefixes for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable.

4. **DISCONTINUED:** These devices are not recommended for new design. Please contact your **onsemi** representative for information. The most current information on these devices may be available on [www.onsemi.com](http://www.onsemi.com).

# TYPICAL CHARACTERISTICS





Figure 1. Typical Forward Voltage



\*The curves shown are typical for the highest voltage device in the voltage grouping. Typical reverse current for lower voltage selections can be estimated from these curves if  $V_R$  is sufficient below rated  $V_R$ .

Figure 2. Typical Reverse Current




Figure 3. Average Power Dissipation

# TYPICAL CHARACTERISTICS




Figure 4. Current Derating, Case




Figure 5. Current Derating, Ambient







Figure 6. Typical Capacitance








DPAK3 6.10x6.54x2.28, 2.29P  
CASE 369C  
ISSUE H

DATE 15 JUL 2025

SCALE 1:1





| MILLIMETERS |          |       |       |
|-------------|----------|-------|-------|
| DIM         | MIN      | NOM   | MAX   |
| A           | 2.18     | 2.28  | 2.38  |
| A1          | 0.00     | ---   | 0.13  |
| b           | 0.63     | 0.76  | 0.89  |
| b2          | 0.72     | 0.93  | 1.14  |
| b3          | 4.57     | 5.02  | 5.46  |
| c           | 0.46     | 0.54  | 0.61  |
| c2          | 0.46     | 0.54  | 0.61  |
| D           | 5.97     | 6.10  | 6.22  |
| E           | 6.35     | 6.54  | 6.73  |
| e           | 2.29 BSC |       |       |
| H           | 9.40     | 9.91  | 10.41 |
| L           | 1.40     | 10.10 | 1.78  |
| L1          | 2.90 REF |       |       |
| L2          | 0.51 BSC |       |       |
| L3          | 0.89     | ---   | 1.27  |
| L4          | ---      | ---   | 1.01  |
| Z           | 3.93     | ---   | ---   |



ALTERNATE CONSTRUCTIONS

NOTES:

1. DIMENSIONING AND TOLERANCING ASME Y14.5M, 2018.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSIONS b3, L3, AND Z.
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.15mm PER SIDE.
5. DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
6. DATUMS A AND B ARE DETERMINED AT DATUM PLANE H.
7. OPTIONAL MOLD FEATURE.



RECOMMENDED MOUNTING FOOTPRINT\*

\*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ONSEMI SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.


|                  |                             |                                                                                                                                                                                  |
|------------------|-----------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DOCUMENT NUMBER: | 98AON10527D                 | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | DPAK3 6.10x6.54x2.28, 2.29P | PAGE 1 OF 2                                                                                                                                                                      |

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**DPAK3 6.10x6.54x2.28, 2.29P**  
CASE 369C  
ISSUE H

DATE 15 JUL 2025

**GENERIC  
MARKING DIAGRAM\***



XXXXXX = Device Code  
A = Assembly Location  
L = Wafer Lot  
Y = Year  
WW = Work Week  
G = Pb-Free Package

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

|                                                                       |                                                                       |                                                                  |                                                                            |                                                                   |
|-----------------------------------------------------------------------|-----------------------------------------------------------------------|------------------------------------------------------------------|----------------------------------------------------------------------------|-------------------------------------------------------------------|
| STYLE 1:<br>PIN 1. BASE<br>2. COLLECTOR<br>3. EMITTER<br>4. COLLECTOR | STYLE 2:<br>PIN 1. GATE<br>2. DRAIN<br>3. SOURCE<br>4. DRAIN          | STYLE 3:<br>PIN 1. ANODE<br>2. CATHODE<br>3. ANODE<br>4. CATHODE | STYLE 4:<br>PIN 1. CATHODE<br>2. ANODE<br>3. GATE<br>4. ANODE              | STYLE 5:<br>PIN 1. GATE<br>2. ANODE<br>3. CATHODE<br>4. ANODE     |
| STYLE 6:<br>PIN 1. MT1<br>2. MT2<br>3. GATE<br>4. MT2                 | STYLE 7:<br>PIN 1. GATE<br>2. COLLECTOR<br>3. EMITTER<br>4. COLLECTOR | STYLE 8:<br>PIN 1. N/C<br>2. CATHODE<br>3. ANODE<br>4. CATHODE   | STYLE 9:<br>PIN 1. ANODE<br>2. CATHODE<br>3. RESISTOR ADJUST<br>4. CATHODE | STYLE 10:<br>PIN 1. CATHODE<br>2. ANODE<br>3. CATHODE<br>4. ANODE |

|                  |                             |                                                                                                                                                                                     |
|------------------|-----------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DOCUMENT NUMBER: | 98AON10527D                 | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | DPAK3 6.10x6.54x2.28, 2.29P | PAGE 2 OF 2                                                                                                                                                                         |

**onsemi** and **Onsemi** are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)