PNS40010ER

400 V, 1 A high power density, standard switching time PN-rectifier

Rev. 2 — 21 August 2012 **Product data sheet**

1. Product profile

1.1 General description

High power density, standard switching time PN-rectifier with high-efficiency planar technology, encapsulated in a small and flat lead SOD123W Surface-Mounted Device (SMD) plastic package.

1.2 Features and benefits

- Forward current $I_F \leq 1$ A
- Reverse voltage $V_R \leq 400$ V
- Standard switching time
- Low forward voltage
- Low reverse current
- Low inductance
- Small and flat lead SMD plastic package
- Package height typ. 1 mm
- High power capability
- AEC-Q101 qualified

1.3 Applications

- General-purpose rectification
- Reverse polarity protection
- Standard switching applications

1.4 Quick reference data

Table 1. Quick reference data

Symbol	Parameter	Conditions		Min	Typ	Max	Unit
I_F	forward current	$T_{sp} \leq 160$ °C		-	-	1.4	A
V_{RRM}	repetitive peak reverse voltage			-	-	400	V
V_R	reverse voltage			-	-	400	V
I_{FSM}	non-repetitive peak forward current	$T_{j(init)} = 25$ °C; $t_p = 8$ ms; square wave		-	-	32	A
V_F	forward voltage	$I_F = 1$ A; $t_p \leq 300$ µs; $\delta \leq 0.02$; $T_j = 25$ °C		-	0.93	1.1	V
$I_{F(AV)}$	average forward current	$\delta = 0.5$; f = 20 kHz; $T_{amb} \leq 115$ °C; square wave	[1]	-	-	1	A
		$\delta = 0.5$; f = 20 kHz; $T_{sp} \leq 170$ °C; square wave		-	-	1	A

[1] Device mounted on a ceramic Printed-Circuit Board (PCB), Al_2O_3, standard footprint.

2. Pinning information

Table 2. Pinning information

Pin	Symbol	Description	Simplified outline	Graphic symbol
1	K	cathode	 SOD123W	 006aab040
2	A	anode		

3. Ordering information

Table 3. Ordering information

Type number	Package		
	Name	Description	Version
PNS40010ER	SOD123W	plastic surface mounted package; 2 leads	SOD123W

4. Marking

Table 4. Marking codes

Type number	Marking code
PNS40010ER	EH

5. Limiting values

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions		Min	Max	Unit
V_{RRM}	repetitive peak reverse voltage			-	400	V
V_R	reverse voltage			-	400	V
V_{RMS}	RMS voltage			-	280	V
I_F	forward current	$T_{sp} \leq 160$ °C		-	1.4	A
$I_{F(AV)}$	average forward current	δ = 0.5 ; f = 20 kHz; square wave; $T_{amb} \leq 115$ °C	[1]	-	1	A
		δ = 0.5 ; f = 20 kHz; $T_{sp} \leq 170$ °C; square wave		-	1	A
I_{FSM}	non-repetitive peak forward current	square wave; $T_{j(init)}$ = 25 °C; t_p = 8 ms		-	32	A
P_{tot}	total power dissipation	$T_{amb} \leq 25$ °C	[2]	-	750	mW
			[3]	-	1300	mW
			[4]	-	2300	mW
T_j	junction temperature			-	175	°C
T_{amb}	ambient temperature			-55	175	°C
T_{stg}	storage temperature			-65	175	°C

[1] Device mounted on a ceramic Printed-Circuit Board (PCB), Al_2O_3, standard footprint.

[2] Device mounted on an FR4 PCB, single-sided copper, tin-plated and standard footprint.

[3] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for cathode 1 cm^2.

[4] Device mounted on a ceramic PCB, Al_2O_3, standard footprint.

6. Thermal characteristics

Table 6. Thermal characteristics

Symbol	Parameter	Conditions		Min	Typ	Max	Unit
$R_{th(j-a)}$	thermal resistance from junction to ambient	in free air	[1]	-	-	200	K/W
			[2]	-	-	115	K/W
			[3]	-	-	65	K/W
$R_{th(j-sp)}$	thermal resistance from junction to solder point		[4]	-	-	15	K/W

[1] Device mounted on an FR4 PCB, single-sided copper, tin-plated and standard footprint.

[2] Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for cathode 1 cm^2.

[3] Device mounted on an FR4 PCB, Al_2O_3, standard footprint.

[4] Soldering point of cathode tab.



FR4 PCB, standard footprint

Fig 1. Transient thermal impedance from junction to ambient as a function of pulse duration; typical values



FR4 PCB, mounting pad for cathode 1 cm^2

Fig 2. Transient thermal impedance from junction to ambient as a function of pulse duration; typical values



Ceramic PCB, Al_2O_3, standard footprint

Fig 3. Transient thermal impedance from junction to ambient as a function of pulse duration; typical values

7. Characteristics

Table 7. Characteristics

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
V_F	forward voltage	I_F = 0.5 A; $t_p \leq$ 300 µs; $\delta \leq$ 0.02 ; T_j = 25 °C	-	0.89	1.05	V
		I_F = 0.7 A; $t_p \leq$ 300 µs; $\delta \leq$ 0.02 ; T_j = 25 °C	-	0.91	1.07	V
		I_F = 1 A; $t_p \leq$ 300 µs; $\delta \leq$ 0.02 ; T_j = 25 °C	-	0.93	1.1	V
		I_F = 0.5 A; $t_p \leq$ 300 µs; $\delta \leq$ 0.02 ; T_j = 125 °C	-	0.76	0.92	V
		I_F = 0.7 A; $t_p \leq$ 300 µs; $\delta \leq$ 0.02 ; T_j = 125 °C	-	0.78	0.95	V
		I_F = 1 A; $t_p \leq$ 300 µs; $\delta \leq$ 0.02 ; T_j = 125 °C	-	0.81	0.98	V
		I_F = 1 A; $t_p \leq$ 300 µs; $\delta \leq$ 0.02 ; T_j = -40 °C	-	1.01	1.18	V
		I_F = 1 A; $t_p \leq$ 300 µs; $\delta \leq$ 0.02 ; T_j = 150 °C	-	0.78	0.95	V
		I_F = 1 A; $t_p \leq$ 300 µs; $\delta \leq$ 0.02 ; T_j = 175 °C	-	0.75	0.92	V

Table 7. Characteristics *...continued*

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
I_R	reverse current	V_R = 400 V; T_j = -40 °C	-	0.1	10	nA
		V_R = 400 V; T_j = 25 °C	-	0.001	1	µA
		V_R = 400 V; T_j = 125 °C	-	1	50	µA
		V_R = 400 V; T_j = 150 °C	-	5	250	µA
		V_R = 400 V; T_j = 175 °C	-	10	500	µA
C_d	diode capacitance	V_R = 4 V; f = 1 MHz; T_{amb} = 25 °C	-	8	20	pF
t_{rr}	reverse recovery time	I_F = 0.5 A; I_R = 1 A; $I_{R(meas)}$ = 0.25 A; T_{amb} = 25 °C	-	0.8	1.8	µs



(1) T_j = 175 °C
(2) T_j = 150 °C
(3) T_j = 125°C
(4) T_j = 85 °C
(5) T_j = 25 °C
(6) T_j = −40 °C

Fig 4. Forward current as a function of forward voltage; typical values



(1) T_j = 175 °C
(2) T_j = 150 °C
(3) T_j = 125 °C
(4) T_j = 85 °C
(5) T_j = 25 °C
(6) T_j = −40 °C

Fig 5. Reverse current as a function of reverse voltage; typical values



f = 1 MHz; T_{amb} = 25 °C

Fig 6. Diode capacitance as a function of reverse voltage; typical values



T_{amb} = 25 °C

Fig 7. Non-repetitive peak forward current as a function of pulse duration; typical values



T_j = 175 °C

(1) δ = 0.1

(2) δ = 0.2

(3) δ = 0.5

(4) δ = 1

Fig 8. Average forward power dissipation as a function of average forward current; typical values



T_j = 175 °C

(1) δ = 1

(2) δ = 0.9

(3) δ = 0.8

(4) δ = 0.5

Fig 9. Average reverse power dissipation as a function of reverse voltage; typical values



FR4 PCB, standard footprint

T_j = 175 °C

(1) δ = 1 (DC)

(2) δ = 0.5; f = 20 kHz

(3) δ = 0.2; f = 20 kHz

(4) δ = 0.1; f = 20 kHz

Fig 10. Average forward current as a function of ambient temperature; typical values



FR4 PCB, mounting pad for cathode 1 cm^2

T_j = 175 °C

(1) δ = 1 (DC)

(2) δ = 0.5; f = 20 kHz

(3) δ = 0.2; f = 20 kHz

(4) δ = 0.1; f = 20 kHz

Fig 11. Average forward current as a function of ambient temperature; typical values



Ceramic PCB, Al_2O_3, standard footprint

T_j = 175 °C

(1) δ = 1 (DC)

(2) δ = 0.5; f = 20 kHz

(3) δ = 0.2; f = 20 kHz

(4) δ = 0.1; f = 20 kHz

Fig 12. Average forward current as a function of ambient temperature; typical values



T_j = 175 °C

(1) δ = 1 (DC)

(2) δ = 0.5; f = 20 kHz

(3) δ = 0.2; f = 20 kHz

(4) δ = 0.1; f = 20 kHz

Fig 13. Average forward current as a function of solder point temperature; typical values

8. Test information



Fig 14. Reverse recovery time: test circuit and waveforms



Fig 15. Duty cycle definition

The current ratings for the typical waveforms are calculated according to the equations: $I_{F(AV)} = I_M \times \delta$ with I_M defined as peak current, $I_{RMS} = I_{F(AV)}$ at DC, and $I_{RMS} = I_M \times \sqrt{\delta}$ with I_{RMS} defined as RMS current.

8.1 Quality information

This product has been qualified in accordance with the Automotive Electronics Council (AEC) standard Q101 - Stress test qualification for discrete semiconductors, and is suitable for use in automotive applications.

9. Package outline



Fig 16. Package outline SOD123W

10. Soldering



Fig 17. Reflow soldering footprint for SOD123W

11. Revision history

Table 8. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
PNS40010ER v.2	20120821	Product data sheet	-	PNS40010ER v.1
Modifications:	• Data sheet status updated			
PNS40010ER v.1	20120615	Preliminary data sheet	-	-

12. Legal information

12.1 Data sheet status

Document status[1] [2]	Product status[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

12.2 Definitions

Preview — The document is a preview version only. The document is still subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

12.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use in automotive applications — This NXP Semiconductors product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the

Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

12.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Adelante,**Bitport**,**Bitsound**,**CoolFlux**,**CoReUse**,**DESFire**,**EZ-HV**,**FabKey**,**GreenChip**,**HiPerSmart**,**HITAG**,**I²C-bus** logo,**ICODE**,**I-CODE**,**ITEC**,**Labelution**,**MIFARE**,**MIFARE Plus**,**MIFARE Ultralight**,**MoReUse**,**QLPAK**,**Silicon Tuner**,**SiliconMAX**,**SmartXA**,**STARplug**,**TOPFET**,**TrenchMOS**,**TriMedia** and**UCODE** — are trademarks of NXP B.V.

HD Radio and**HD Radio** logo — are trademarks of iBiquity Digital Corporation.

13. Contact information

For more information, please visit:http://www.nxp.com

For sales office addresses, please send an email to:salesaddresses@nxp.com

14. Contents

For more information, please visit: http://www.nxp.com
For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 21 August 2012
Document identifier: PNS40010ER