

Specification Status: Released

Maximum Electrical Rating

Operating Voltage: 16Vdc
Interrupt Current: 100A

Chip Size: 3.6 x 10mm

Leads: Nickel 1/4H
0.125mm nominal thickness

Solder: Lead-free

Tape: Polyester (White)
11mm nominal width

Marking: (Color: Green)

— Manufacturer's Mark
XX V1X — Part Identification
□□□□ — Lot Identification




TABLE I. DIMENSIONS:

	A		B		C		D		E		F	
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX
mm:	25.8	28.2	3.5	3.9	---	0.8	5.7	7.3	8.7	10.3	2.4	2.6
in*:	(1.02)	(1.11)	(0.14)	(0.15)	---	(0.03)	(0.22)	(0.29)	(0.34)	(0.41)	(0.09)	(0.10)

*Rounded off approximation

TABLE II. PERFORMANCE RATINGS: As measured in Mueller Kelvin Clips model BU-75K

I HOLD	CURRENT TRIP LIMITS								TIME TO TRIP		REFERENCE RESISTANCE		ONE-HOUR POST-TRIP RESISTANCE		TRIPPED-STATE POWER DISSIPATION		
	AMPS 25°C		AMPS AT 0°C		AMPS AT 25°C		AMPS AT 60°C		AMPS AT --°C		SECONDS AT 25°C, 8.75A		OHMS AT 25°C		OHMS AT 25°C		WATTS AT 25°C,16V
	HOLD	TRIP	HOLD	TRIP	HOLD	TRIP	HOLD	TRIP	HOLD	TRIP	MIN	MAX	MIN	MAX	MIN	MAX	MAX
	1.75	4.7	2.2	3.6	0.8	1.9	---	---	---	5	0.029	0.051	0.029	0.102	1.4		

Agency Recognitions:
Reference Documents:
Precedence: This
Effectivity: Reference
CAUTION: Operation
Materials Information:

UL, TUV, CSA
PS300
specification takes precedence over documents referenced herein.
documents shall be the issue in effect on the date of invitation for bid.
beyond the rated voltage or current may result in rupture, electrical arcing or flame.

ROHS Compliant

ELV Compliant

Pb-Free

Directive 2002/95/EC
Compliant

Directive 2000/53/EC
Compliant



PolySwitch®
PTC Devices
Overcurrent Protection Device

PRODUCT: VTP175LF

DOCUMENT: SCD25934
PCN: D16304
REV LETTER: D
REV DATE: JULY 26, 2016
PAGE NO.: 2 OF 2

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, military, aerospace, medical, lifesaving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.