







Copyright FCI.



Pro/E File - REV C - 2009-06-09



MOUNTED ON PC BOARD
SHOWN THRU RECOMMENDED BEZEL




MOUNTED BELLY TO BELLY ON PC BOARD
SHOWN THRU RECOMMENDED BEZEL


spec ref		RELEASE			dr	Art Lin	2014-01-13	projection 		size A4	scale 1:1
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Zhen Luo	2014-01-13			ecn no	
ISO406					chr	Collins Lu	2014-01-14				
ISO1101					appr	JEFFREY QIN	2014-01-14	product family SFP+		rel level	Released
surface  ISO1302	linear	0.X		±0.25		title SFP+ 1X4 CAGE ASSEMBLY EMI SPRING TYPE PRESS FIT WITH LIGHTPIPE			dwg no 10126909	rev C	
		0.XX		±0.20							
		0.XXX		±0.15							
		angular	0°		±0.5°	www.fci.com	cat. no.	-	Product-Customer Drw		

1 2 3 4

A



RECOMMENDED PCB CONFIGURATION WITH KEEP-OUT AREAS
SINGLE SIDED APPLICATIONS




Detail A
SCALE 2.5:1


B

A

B



RECOMMENDED PCB CONFIGURATION WITH KEEP-OUT AREAS
BELLY TO BELLY APPLICATIONS



Detail A
SCALE 2.5:1

C

D



Copyright FCI.

D

spec ref		RELEASE			dr	Art Lin	2014-01-13	projection	MM	size	A4	scale	1:1					
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Zhen Luo	2014-01-13			ecn no								
ISO406					chr	Collins Lu	2014-01-14											
ISO1101					appr	JEFFREY QIN	2014-01-14	product family		SFP+		rel level		Released				
surface ISO1302		linear	0.X		±0.25			title	SFP+ 1X4 CAGE ASSEMBLY EMI SPRING TYPE PRESS FIT WITH LIGHTPIPE				dwg no		10126909		rev	C
			0.XX		±0.20													
			0.XXX		±0.15													
				angular	0°		±0.5°		www.fci.com	cat. no.	-		Product-Customer Drw				sheet 3 of 3	

Proj/E File - REV C - 2009-06-09

1 2 3 4