

Data sheet

Function Generators

Models 4010A & 4011A



4010A

2 MHz Function Generator

- 0.2 Hz to 2 MHz
- Sine, Square, Triangle, Pulse & Ramp output
- Variable duty cycle
- Variable DC offset
- Variable amplitude output plus 20dB attenuator
- 20Vpp output into open circuit (10Vpp into 50 Ω s)
- cUL certified



4011A

5 MHz Function Generator

- 0.5 Hz to 5 MHz
- Sine, Square, Triangle, Pulse, & Ramp output
- Coarse and Fine tuning
- 4 digit LED display
- Variable duty cycle
- Variable DC offset
- Variable amplitude output plus 20dB attenuator
- 20Vpp output into open circuit (10Vpp into 50 Ω s)
- cUL certified



Specifications	4010A	4011A
Frequency Characteristics		
Waveforms	Sine, Square, Triangle, ±Pulse, ±Ramp	
Range	0.2 Hz to 2 MHz in 7 ranges	0.5 Hz to 5 MHz in 7 ranges
Resolution	NA	4 digits
Dial Accuracy	±5% typical	NA
Tuning Range	10:1 Does not apply	Coarse, 10:1 Fine±5% of coarse setting
Variable Duty Cycle	15:85:15 cont variable	15:85:15 Cont variable
Operating Modes	Normal, VCG	
Output Characteristics		
Impedance	50Ω ±10%	
Level	20 V p-p Open circuit, 10V p-p into 50Ω	
Amplitude	Variable, 20 dB range typical	
Attenuation	-20 dB ±1dB	
DC Offset	Preset ±0.1 V typ Variable: ±10V open-circuit ±5 into 50Ω	
Distortion	≤ 4% @ 1 kHz	≤ 3% @ 1 kHz
Flatness	≤ 5% (.45 dB)	
Symmetry	0.5 Hz to 100 KHz ≤ 2%	
Risetime (Into 50Ω)	≤ 120 nS	≤ 20 nS
Linearity	≥ 98% to 100 KHz, ≥ 95% to 2 MHz	
TTL Output		
Level	0.8V to 2.4V	
Rise time (0.8V to 2.9V)	≤ 50 nS	≤ 20 nS
Duty Cycle	50% typical	
CMOS Output		
Max. Frequency	2 MHz	
Level	4V to 14V ±0.5 p-p cont. variable	
Rise Time	≤ 120 nS	
Input VCG		
Input Voltage	0-10V ±1V causes a 100:1 frequency change	
Impedance	10KΩ ±5%	
Frequency Counter INT		
Accuracy	NA	Time Base Accy ±1 count
Time Base Accuracy	NA	±10 PPM (23°C ±5°C)
General		
Display	NA	4 digit LED
Power Source	120/230 VAC ±10%, 50/60 Hz, internal jumper selectable	
Dimensions (H x W x D)	4.5 x 11.75 x 10.375", (114 x 298 x 264 mm)	
Weight	4 lbs. (1.8 kg)	
Two Year Warranty		
Supplies Accessories	Output cable with BNC to alligator clips, Instruction Manual, Line Cord	
Optionmal Accessories	Carrying Case (not included): LC-40, TLFG kit	