


# **$\mu$ A78M06QB**

## **3-Terminal Positive Voltage Regulator**

Aerospace and Defense Data Sheet  
Linear Products**Description**

The  $\mu$ A78M06QB 3-Terminal Medium Current Positive Voltage Regulator is constructed using the Fairchild Planar Epitaxial process. This regulator employs internal current-limiting, thermal shutdown and safe-area compensation, making it essentially indestructible. If adequate heat sinking is provided, it can deliver in excess of 500 mA output current. It is intended as a fixed voltage regulator in a wide range of applications including local, on-card regulation for elimination of noise and distribution problems associated with single point regulation. In addition to use as a fixed voltage regulator, this device can be used with external components to obtain adjustable output voltages and currents.<sup>6</sup>

- Output Current In Excess Of 0.5 A
- No External Components
- Internal Thermal Overload Protection
- Internal Short Circuit Current-Limiting
- Output Transistor Safe-Area Compensation

**Connection Diagram**  
**3-Lead TO-39 Can**  
**(Top View)****Order Information**

	Case/ Finish	Package Code
Part No.	XC	Mil-M-38510, Appendix C 3-Lead Can

**Absolute Maximum Ratings**

Storage Temperature Range	-65°C to +175°C
Operating Temperature Range	-55°C to +125°C
Lead Temperature (soldering, 60 s)	300°C
Internal Power Dissipation <sup>9</sup>	
Can Without Heat Sink <sup>10</sup>	0.18 W
Can With Heat Sink <sup>11</sup>	0.5 W
Input Voltage	35 V

**Processing:** MIL-STD-883, Method 5004

**Burn-In:** Method 1015, Condition A, PDA calculated using Method 5005, Subgroup 1

**Quality Conformance Inspection:** MIL-STD-883, Method 5005

**Group A Electrical Tests Subgroups:**

1. Static tests at 25°C
2. Static tests at 125°C
3. Static tests at -55°C
4. Dynamic tests at 25°C
9. AC tests at 25°C

**Group C and D Endpoints: Group A, Subgroup 1**

**Notes**


1. 100% Test and Group A
2. Group A
3. Periodic tests, Group C
4. Guaranteed but not tested
5. When changes occur, FSC will make data sheet revisions available. Contact local sales representative for the latest revision.
6. For more information on device function, refer to the Fairchild Linear Data Book Commercial Section.
7. All characteristics except line and load transient response and noise are measured using pulse techniques ( $t_W \leq 10$  ms, duty cycle  $\leq 5\%$ ). Output voltage changes due to changes in the internal temperature must be taken into account separately.
8. Conditions given will result in the following:  $P_B \leq 4$  W.
9. Internally limited.
10. Rating applies to ambient temperatures up to 125°C. Above 125°C, derate linearly at 140°C/W.
11. Rating applies to ambient temperatures up to 125°C. Above 125°C, derate linearly at 50°C/W.

**μA78M06QB**

**Electrical Characteristics**  $V_I = 11$  V,  $I_L = 350$  mA,  $C_I = 0.33$   $\mu$ F,  $C_O = 0.1$   $\mu$ F, unless otherwise specified.<sup>7</sup>

Symbol	Characteristic	Condition		Min	Max	Unit	Note	Subgrp
$V_O$	Output Voltage <sup>8</sup>			5.75	6.25	V	1	1
		5.0 mA $\leq I_L \leq 350$ mA	$V_I = 9.0$ V	5.7	6.3	V	1	1,2,3
			$V_I = 21$ V	5.7	6.3	V	1	1,2,3
$\Delta V_O/\Delta T$	Average Temperature Coefficient of Output Voltage	$I_L = 5.0$ mA, $25^\circ\text{C} \leq T_A \leq 125^\circ\text{C}$		1.5	mV/ $^\circ\text{C}$		4	2
		$I_L = 5.0$ mA, $-55^\circ\text{C} \leq T_A \leq 25^\circ\text{C}$		2.0	mV/ $^\circ\text{C}$		4	3
$V_R$ LINE	Line Regulation	$8.0$ V $\leq V_I \leq 25$ V, $I_L = 200$ mA		60	mV		1	1
		$9.0$ V $\leq V_I \leq 20$ V, $I_L = 200$ mA		30	mV		1	1
$V_R$ LOAD	Load Regulation	$5.0$ mA $\leq I_L \leq 500$ mA		60	mV		1	1
		$5.0$ mA $\leq I_L \leq 200$ mA		30	mV		1	1
$I_{SCD}$	Standby Current Drain			7.0	mA		1	1
$\Delta I_{SCD}$ (LINE)	Standby Current Drain Change (vs Line Voltage)	$9.0$ V $\leq V_I \leq 25$ V, $I_L = 200$ mA		0.8	mA		1	1,2,3
$\Delta I_{SCD}$ (LOAD)	Standby Current Drain Change (vs Load Current)	$5.0$ mA $\leq I_L \leq 350$ mA		0.5	mA		1	1,2,3
$V_{DO}$	Dropout Voltage			2.5	V		1	1
$I_{OS}$	Output Short Circuit Current	$V_I = 35$ V		1.0	A		1	1
$I_{OL}$	Overload Current	$V_I = 13$ V		0.5	2.0	A	1	1
$\Delta V_I/\Delta V_O$	Ripple Rejection	$V_I = 11$ V, $I_L = 125$ mA, $e_I = 1.0$ V <sub>rms</sub> , $f = 2400$ Hz		59	dB		1	4
$N_O$	Noise	$V_I = 11$ V, $I_L = 50$ mA, $10$ Hz $\leq f \leq 10$ kHz			125	$\mu$ V <sub>rms</sub>	4	9

**Primary Burn-In Circuit**



**Note**

1. Capacitor value necessary to suppress oscillations.

**Equivalent Circuit**

