



Sales Outline Drawing

Revision

A**Specifications:**

Oscillation Frequency (Hz)	1250 $\pm$ 200
Operating Voltage (Vp-p)	2.0 ~ 5.0
Rated Voltage (Vp-p)	3.0
Input Watt (W/max)	0.2
Sound Pressure Level (dB/min)	85 at 10cm at Rated Voltage
Coil Resistance (Ω)	8.0 $\pm$ 2
Operating Temperature ($^{\circ}$ C)	-20 ~ +70
Storage Temperature ($^{\circ}$ C)	-30 ~ +80
Housing	ABS 707 UL94HB plastic resin (Color: Black)
Lead Wire	28 AWG
Weight (Grams)	4.2
Condition by wave soldering ($^{\circ}$ C)	245 $\pm$ 5 / 3 $\pm$ 0.5 sec
Condition by hand soldering ($^{\circ}$ C)	350 $\pm$ 20 / within 5 sec
Options	For other options contact factory

PS: Vp-p = 1/2duty, square wave

RoHS Compliant**Dimensions:** (units: mm)**Recommended Driving Circuit:**

The base current I_b should be high enough so that it saturates the collector current of the transistor with the CB load.