




LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			M2	REVISED PER ECO-11-004835	11MAR11	RK	HMR



- ① HOUSING FULLY LOADED WITH CONTACTS.
- ② NUMBER ON CONTACT INDICATES WIRE RANGE.
- ③ CONTACT INSULATION RANGE: .060 MAXIMUM O.D.
- ④ CONTACTS PLATED .000030 GOLD ON MATING END FOR .100 MIN LENGTH. .000100—.000200 THICK BRIGHT TIN OR BRIGHT TIN—LEAD IN AREA SHOWN. .000050 THICK NICKEL UNDERPLATE ON ENTIRE CONTACT.
- ⑤ CONTACTS PLATED WITH GOLD FLASH ON MATING END FOR .100 MIN LENGTH. .000100—.000200 THICK BRIGHT TIN OR BRIGHT TIN—LEAD IN AREA SHOWN. .000030 THICK NICKEL UNDERPLATE ON ENTIRE CONTACT.
- ⑥ CONTACTS PLATED .000030 GOLD ON MATING END FOR .100 MIN LENGTH. .000100—.000200 THICK MATTE TIN IN AREA SHOWN. .000050 THICK NICKEL UNDERPLATE ON ENTIRE CONTACT.
- ⑦ CONTACTS PLATED WITH GOLD FLASH ON MATING END FOR .100 MIN LENGTH, .000100—.000200 THICK MATTE TIN IN AREA SHOWN. .000030 MIN THICK NICKEL UNDERPLATE ON ENTIRE CONTACT.
- ⑧ HOUSING: BLACK THERMOPLASTIC 94V-0 RATED.
CONTACTS: PHOSPHOR BRONZE.

			2	#22-26	745201-9
	OBSOLETE		3	#20-22	745201-8
			2	#22-26	745201-7
SUPD BY 745201-3			3	#20-22	745201-6
	OBSOLETE		2	#22-26	745201-5
	OBSOLETE		1	#26-30	745201-4
	OBSOLETE		3	#20-22	745201-3
	OBSOLETE		2	#22-26	745201-2
	OBSOLETE		1	#26-30	745201-1
		FINISH 	AWG WIRE RANGE		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				OWN L. VARELA - DOCKS 11-15-04				TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		DWG J. GERACE 11-13-04		NAME M. WALMSLEY 11-15-04		ASSEMBLY RECEPTACLE, SIZE 1, 9 POSITION, AMPLITUDE	
		Ø .PLC ± . 1 PLC ± . 2 PLC ± . 4 PLC ± .005 6 PLC ± . ANGLES ± °		PRODUCT SPEC 108-40011		SIZE CASE CODE DRAWING NO A1 00779 C=745201		RESTRICTED TO —	
				APPLICATION SPEC 114-40002					
MATERIAL 		FINISH SEE TABLE		WEIGHT —		SCALE 4:1 SHEET 1 OF 1 REV M2			
				CUSTOMER DRAWING					