





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		M	REVISED PER ECR-12-013518	23NOV2012	KH	PD

- 1
- DIMENSIONS IN BRACKETS ARE IN INCHES.
- 2
- CONTINUOUS STRIP ON REELS.
- 3
- MATING TAB THK TO BE 0.81±0.025
[.032±.001].
- 4
- WIRE SIZE IS [#18-#14] AWG.
- 5
- INTERLEAVING PAPER REQUIRED.
- 6
- PRELIMINARY - NOT FOR PRODUCTION



VIEW A-A



SECTION B-B

PART NO	WIRE		WIRE BARREL CRIMP				TENSILE STRENGTH POUNDS
	QTY	SIZE AWG	WIDTH	CRIMP HEIGHT	CRIMPER	ANVIL	
63317	1	14	.120	.071	F	FLAT	50
	1	16		.063			30
	1	18		.057			20

OBSOLETE	-	56	63317-3
	- TIN PLATED		63317-2
	-		63317-1
	FINISH		PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 6/16/87		 TE Connectivity			
		CHK G YETTER 6/16/87					
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD R KUZO 6/16/87		NAME	
		0 PLC ± -		PRODUCT SPEC		RECEPTACLE, FASTON, FLAG, .187 SERIES -	
		1 PLC ± -		—			
		2 PLC ± -		APPLICATION SPEC			
		3 PLC ± 0.25[.010]		—			
		4 PLC ± -				SIZE	
		ANGLES ± ±				CAGE CODE	
MATERIAL		FINISH		WEIGHT —		DRAWING NO	
BRASS		SEE TABLE		A2 00779		C=63317	
				CUSTOMER DRAWING		RESTRICTED TO —	
						SCALE NTS	
						SHEET 1 of 1	
						REV M	