

# Amphenol

MS & 97B - Series

ACRMS02 0313



---

# Amphenol




# Introduction


Amphenol MS & 97B series are two series of thread & Bayonet coupled connectors designed to meet the operating requirements of MIL-C-5015. available in a variety of styles & classes, these connectors are primarily used in a range of military and industrial applications where specific degrees of environmental protection are required.

Although MS series have identical insert arrangements and other similar components parts, the two series differ in that Amphenol MS series of connectors are also qualified to meet the operating requirements of Defence Standard Joint Services Specifications JSS50812, issued by the Electronics Components Standardization Organisation (LCSO)

Amphenol 97B connectors feature a quick a mating bayonet coupling with an audible full mating feature. This series uses the same MIL-C-5015 insert patterns and are used in high shock and vibration environments encountered in commercial, geophysical, aerospace, ground support and shipboard applications.

| Content                                 | Page  |
|-----------------------------------------|-------|
| Introduction - - - - -                  | 1     |
| Connector style - - - - -               | 2-3   |
| General description - - - - -           | 4     |
| Electrical data - - - - -               | 5     |
| Insert orientations - - - - -           | 6     |
| Insert arrangements - - - - -           | 7-17  |
| MS threaded series connector - - - - -  | 19-22 |
| 97B reverse bayonet connector - - - - - | 23-49 |
| Ordering information - - - - -          | 50    |





These electrical connectors are designated MS because the interchangeability and operating characteristics are determined by U.S. Military Specifications. These specifications are revised from time to time to incorporate performance requirements dictated by design advances and more stringent requirements of allied equipment. The several designations of MS and 97B connectors meet different requirements of MIL-C-5015. These designations and general descriptions are as follows :

### Shell

Shell constructions include solid back shell (A) and environmental resistant (E, F & R). Environmental resistant connectors provide a moisture barrier and assure a positive seal. Shell styles consist of wall type receptacles (3100), cable receptacles (3101), box receptacles (3102), straight plugs (3106) and angle plugs (3108). Shell hardware is manufactured from aluminium alloy and cadmium plated with olive drab chromate finish. This finish has excellent conductivity; it is non-reflecting and corrosion resistant. Black anodised finish and cadmium-free zinc plating with olive drab chromate finish are also available. For details, contact factory.

### Contacts

Pin and socket contacts are of brass and generally silver plated. Gold plating is also available. For details contact factory. These contacts are available for solder or crimp termination. Special arrangements of contacts for pre-mating and pre-earth are also available.

### Inserts and grommet

Synthetic inserts and grommet manufactured according to MIL-R-3065, offer high dielectric strength and are resistant to oils, gasoline and low temperature. DAP is dimensionally stable, has high arc resistance and high insulation resistance under both humidity and thermal stress.

### General description

Plugs are available in A, F and R types. Receptacles are available in A, E, F and R types.

#### A Solid back shell

Intended for general service usage to provide convenient means of connecting and disconnecting electrical circuits in industrial and military applications.

#### Environmental resisting

Intended for use where the connector will be subject to heavy condensation and rapid changes in temperature or pressure and/or where the connector is subjected to high vibratory conditions.

**E** Environmental resisting with grommet seal and strain relief backshell except for 3102 type.

**F** Environmental resisting with grommet seal, strain relief backshell and front gasket seal for plug type.

**R** Environmental resisting with grommet seal, shorter and lightweight.

### Features for 97B reverse bayonet coupling connectors with Mil-C-5015 insert patterns:

- Quick positive coupling
- Audible and tactile indication of full coupling
- Waterproof
- No lockwiring required
- High shock and vibration capabilities
- Insert available in Neoprene material (alternate inserts materials available upon request)
- Operating temperature range with Neoprene inserts: -55°C to +125°C
- Available in both crimp and solder terminations
- Contacts available in gold and silver plating
- Numerous finishes available
- Zinc alloy plating (cadmium free) available
- Rugged construction; aluminum or stainless steel components
- Intermateable with existing VG95234 connectors
- 500 couplings minimum

### Dielectric strength

| Service rating | Test Voltage<br>Vac rms |
|----------------|-------------------------|
| Inst.          | 1000V                   |
| A              | 2000V                   |
| D              | 2800V                   |
| E              | 3500V                   |
| B              | 4500V                   |
| C              | 7000V                   |

### Contact rating


| Contact<br>Size | Rated<br>Current | Contact<br>Resistance<br>miliohms |
|-----------------|------------------|-----------------------------------|
| 16              | 13A              | 3.46                              |
| 12              | 23A              | 1.83                              |
| 8               | 46A              | 0.52                              |
| 4               | 80A              | 0.26                              |
| 0               | 150A             | 0.14                              |

### Service rating

| Service rating | Operating Voltage<br>DC at Sea Level | Operating Voltage<br>AC at Sea Level |
|----------------|--------------------------------------|--------------------------------------|
| Inst.          | 250V                                 | 200V                                 |
| A              | 700V                                 | 500V                                 |
| D              | 1250V                                | 900V                                 |
| E              | 1750V                                | 1250V                                |
| B              | 2450V                                | 1750V                                |
| C              | 4200V                                | 3000V                                |

To avoid cross-plugging problems in applications requiring the use of more than one connector of the same size and arrangement, alternate insert rotations are available as indicated in the accompanying chart.

As shown in the daigram below, the front face of the pin insert is rotated within the shell in a clockwise direction from the normal shell key. The socket insert would be rotated counterclockwise the same number of degrees with respect to the normal shell key.



The following insert arrangements have the same alternate insert rotations for W, X, Y and Z which are as below :

| Degree |     |     |     |
|--------|-----|-----|-----|
| W      | X   | Y   | Z   |
| 80     | 110 | 250 | 280 |

|       |       |       |       |       |       |       |
|-------|-------|-------|-------|-------|-------|-------|
| 16-7  | 20-16 | 22-18 | 24-4  | 24-21 | 28-15 | 36-1  |
| 18-5  | 20-20 | 22-19 | 24-5  | 24-28 | 28-16 | 36-7  |
| 18-9  | 20-22 | 22-21 | 24-6  | 28-1  | 28-17 | 36-8  |
| 18-13 | 22-3  | 22-24 | 24-7  | 28-4  | 28-19 | 36-13 |
| 18-14 | 22-6  | 22-25 | 24-12 | 28-8  | 28-20 |       |
| 20-7  | 22-12 | 22-29 | 24-14 | 28-9  | 28-21 |       |
| 20-8  | 22-14 | 22-33 | 24-16 | 28-10 | 32-1  |       |
| 20-9  | 22-15 | 22-34 | 24-17 | 28-11 | 32-3  |       |
| 20-12 | 22-16 | 24-1  | 24-20 | 28-14 | 32-4  |       |
| 20-14 | 22-17 | 24-3  |       |       |       |       |

| Insert Arrangement | Degrees |     |     |     |
|--------------------|---------|-----|-----|-----|
|                    | W       | X   | Y   | Z   |
| 12S-3              | 70      | 145 | 215 | 290 |
| 14S-2              | -       | 120 | 240 | -   |
| 14S-5              | -       | 110 | -   | -   |
| 14S-7              | 90      | 180 | 270 | -   |
| 14S-9              | 70      | 145 | 215 | 290 |
| 16-9               | 35      | 110 | 250 | 325 |
| 16-10              | 90      | 180 | 270 | -   |
| 16-11              | 35      | 110 | 250 | 325 |
| 16-13              | 35      | 110 | 250 | 325 |
| 16S-1              | 80      | -   | -   | 280 |
| 16S-4              | 35      | 110 | 250 | 325 |
| 16S-5              | 70      | 145 | 215 | 290 |
| 16S-6              | 90      | 180 | 270 | -   |
| 16S-8              | -       | 170 | 265 | -   |
| 18-1               | 70      | 145 | 215 | 290 |
| 18-3               | 35      | 110 | 250 | 325 |
| 18-4               | 35      | 110 | 250 | 325 |
| 18-8               | 70      | -   | -   | 290 |
| 18-10              | -       | 120 | 240 | -   |
| 18-11              | -       | 170 | 265 | -   |
| 18-12              | 80      | -   | -   | 280 |
| 18-15              | -       | 120 | 240 | -   |
| 18-20              | 90      | 180 | 270 | -   |
| 18-22              | 70      | 145 | 215 | 290 |
| 18-29              | 90      | 180 | 270 | -   |
| 20-3               | 70      | 145 | 215 | 290 |
| 20-4               | 45      | 110 | 250 | -   |
| 20-5               | 35      | 110 | 250 | 325 |

| Insert Arrangement | Degrees |     |     |     |
|--------------------|---------|-----|-----|-----|
|                    | W       | X   | Y   | Z   |
| 20-6               | 70      | 145 | 215 | 290 |
| 20-15              | 80      | -   | -   | 280 |
| 20-17              | 90      | 180 | 270 | -   |
| 20-18              | 35      | 110 | 250 | 325 |
| 20-19              | 90      | 180 | 270 | -   |
| 20-21              | 35      | 110 | 250 | 325 |
| 20-23              | 35      | 110 | 250 | 325 |
| 20-24              | 35      | 110 | 250 | 325 |
| 20-27              | 35      | 110 | 250 | 325 |
| 20-29              | 80      | -   | -   | 280 |
| 22-1               | 35      | 110 | 250 | 325 |
| 22-2               | 70      | 145 | 215 | 290 |
| 22-4               | 35      | 110 | 250 | 325 |
| 22-5               | 35      | 110 | 250 | 325 |
| 22-8               | 35      | 110 | 250 | 325 |
| 22-9               | 70      | 145 | 215 | 290 |
| 22-10              | 35      | 110 | 250 | 325 |
| 22-11              | 35      | 110 | 250 | 325 |
| 22-13              | 35      | 110 | 250 | 325 |
| 22-20              | 35      | 110 | 250 | 325 |
| 22-22              | -       | 110 | 250 | -   |
| 22-23              | 35      | -   | 250 | -   |
| 22-27              | 80      | -   | 250 | 280 |
| 22-28              | 80      | -   | -   | 280 |
| 24-2               | 80      | -   | -   | 280 |
| 24-9               | 35      | 110 | 250 | 325 |
| 24-10              | 80      | -   | -   | 280 |
| 24-11              | 35      | 110 | 250 | 325 |

| Insert Arrangement | Degrees |     |     |     |
|--------------------|---------|-----|-----|-----|
|                    | W       | X   | Y   | Z   |
| 24-22              | 45      | 110 | 250 | -   |
| 24-27              | 80      | -   | -   | 280 |
| 28-2               | 35      | 110 | 250 | 325 |
| 28-3               | 70      | 145 | 215 | 290 |
| 28-5               | 35      | 110 | 250 | 325 |
| 28-6               | 70      | 145 | 215 | 290 |
| 28-7               | 35      | 110 | 250 | 325 |
| 28-12              | 90      | 180 | 270 | -   |
| 28-18              | 70      | 145 | 215 | 290 |
| 28-22              | 70      | 145 | 215 | 290 |
| 32-8               | 80      | 125 | 235 | 280 |
| 36-3               | 70      | 145 | 215 | 290 |
| 36-4               | 70      | 145 | 215 | 290 |
| 36-5               | -       | 120 | 240 | -   |
| 36-6               | 35      | 110 | 250 | 325 |
| 36-9               | 80      | 125 | 235 | 280 |
| 36-10              | 80      | 125 | 235 | 280 |
| 36-14              | 90      | 180 | 270 | -   |
| 36-15              | 60      | 125 | 245 | 305 |
| 40-56              | 72      | 144 | 216 | 288 |
|                    |         |     |     |     |
|                    |         |     |     |     |
|                    |         |     |     |     |
|                    |         |     |     |     |
|                    |         |     |     |     |
|                    |         |     |     |     |
|                    |         |     |     |     |
|                    |         |     |     |     |

# Insert Arrangements


| Insert Arrangement | Service Rating | Total Cont-acts | Contact Size |   |   |    |    |
|--------------------|----------------|-----------------|--------------|---|---|----|----|
|                    |                |                 | 0            | 4 | 8 | 12 | 16 |
| 10S-2              | A              | 1               |              |   |   |    | 1  |
| 10SL-3             | A              | 3               |              |   |   |    | 3  |
| 10SL-4             | A              | 2               |              |   |   |    | 2  |
| 12S-3              | A              | 2               |              |   |   |    | 2  |
| 12S-4              | D              | 1               |              |   |   |    | 1  |
| 12-5               | D              | 1               |              |   |   |    | 1  |
| 14S-1              | A              | 3               |              |   |   |    | 3  |
| 14S-2              | Inst           | 4               |              |   |   |    | 4  |
| 14S-4              | D              | 1               |              |   |   |    | 1  |
| 14S-5              | Inst           | 5               |              |   |   |    | 5  |
| 14S-6              | Inst           | 6               |              |   |   |    | 6  |
| 14S-7              | A              | 3               |              |   |   |    | 3  |
| 14S-9              | A              | 2               |              |   |   |    | 2  |
| 14S-10             | Inst           | 4               |              |   |   |    | 4  |
| 14S-12             | A              | 3               |              |   |   |    | 3  |
| 14-3               | A              | 1               |              |   | 1 |    |    |
| 14S-A7             | A              | 19              | 19           |   |   |    |    |
| 16S-1              | A              | 7               |              |   |   |    | 7  |
| 16S-3              | B              | 1               |              |   |   |    | 1  |
| 16S-4              | D              | 2               |              |   |   |    | 2  |
| 16S-5              | A              | 3               |              |   |   |    | 3  |
| 16S-6              | A              | 3               |              |   |   |    | 3  |
| 16S-8              | A              | 5               |              |   |   |    | 5  |
| 16-2               | E              | 1               |              |   |   | 1  |    |
| 16-7               | A              | 3               |              |   | 1 | 2  |    |
| 16-9               | A              | 4               |              |   |   | 2  | 2  |
| 16-10              | A              | 3               |              |   |   | 3  |    |
| 16-11              | A              | 2               |              |   |   | 2  |    |
| 16-12              | A              | 1               |              | 1 |   |    |    |
| 16-13              | A              | 2               |              |   |   | 2  |    |
| 18-1               | A/Inst         | 10              |              |   |   |    | 10 |
| 18-3               | D              | 2               |              |   |   | 2  |    |
| 18-4               | D              | 4               |              |   |   |    | 4  |
| 18-5               | D              | 3               |              |   |   | 2  | 1  |
| 18-06              |                | 6               |              |   |   | 4  | 2  |
| 18-6               | D              | 1               |              | 1 |   |    |    |
| 18-7               | B              | 1               |              |   | 1 |    |    |
| 18-8               | A              | 8               |              |   |   | 1  | 7  |
| 18-9               | Inst           | 7               |              |   |   | 2  | 5  |
| 18-10              | A              | 4               |              |   |   | 4  |    |
| 18-11              | A              | 5               |              |   |   | 5  |    |
| 18-12              | A              | 6               |              |   |   |    | 6  |
| 18-13              | A              | 4               |              |   | 1 | 3  |    |
| 18-14              | A              | 2               |              | 1 |   |    | 1  |
| 18-15              | A              | 4               |              |   |   | 4  |    |
| 18-16              | C              | 1               |              |   |   | 1  |    |
| 18-17              | Inst           | 7               |              |   |   | 2  | 5  |
| 18-19              | A              | 10              |              |   |   |    | 10 |
| 18-20              | A              | 5               |              |   |   |    | 5  |
| 18-22              | D              | 3               |              |   |   |    | 3  |
| 18-24              | A/Inst         | 10              |              |   |   |    | 10 |
| 18-29              | A              | 5               |              |   |   |    | 5  |
| 18-30              | A              | 5               |              |   |   |    | 5  |
| 18-31              | A              | 5               |              |   |   |    | 5  |
| 20-2               |                | 1               | 1            |   |   |    |    |
| 20-3               | D              | 3               |              |   |   | 3  |    |
| 20-4               | D              | 4               |              |   |   | 4  |    |
| 20-6               | D              | 3               |              |   |   |    | 3  |
| 20-7               | D/A            | 8               |              |   |   |    | 8  |

| Insert Arrangement | Service Rating | Total Cont-acts | Contact Size |   |   |    |    |
|--------------------|----------------|-----------------|--------------|---|---|----|----|
|                    |                |                 | 0            | 4 | 8 | 12 | 16 |
| 20-8               | Inst           | 6               |              |   | 2 |    | 4  |
| 20-9               | D/A            | 8               |              |   |   | 1  | 7  |
| 20-11              | Inst           | 13              |              |   |   |    | 13 |
| 20-12              | A              | 2               |              | 1 |   |    | 1  |
| 20-14              | A              | 5               |              |   | 2 | 3  |    |
| 20-15              | A              | 7               |              |   |   | 7  |    |
| 20-16              | A              | 9               |              |   |   | 2  | 7  |
| 20-17              | A              | 6               |              |   |   | 5  | 1  |
| 20-18              | A              | 9               |              |   |   | 3  | 6  |
| 20-19              | A              | 3               |              |   | 3 |    |    |
| 20-20              | A              | 4               |              | 1 |   | 3  |    |
| 20-21              | A              | 9               |              |   |   | 1  | 8  |
| 20-22              | A              | 6               |              |   | 3 |    | 3  |
| 20-23              | A              | 2               |              |   | 2 |    |    |
| 20-24              | A              | 4               |              |   | 2 |    | 2  |
| 20-25              | Inst           | 13              |              |   |   |    | 13 |
| 20-27              | A              | 14              |              |   |   |    | 14 |
| 20-29              | A              | 17              |              |   |   |    | 17 |
| 20-30              | Inst           | 13              |              |   |   |    | 13 |
| 20-33              | A              | 11              |              |   |   |    | 11 |
| 20-A48             | A              | 19              |              |   |   |    |    |
| 22-1               | D              | 2               |              |   | 2 |    |    |
| 22-2               | D              | 3               |              |   | 3 |    |    |
| 22-4               | A              | 4               |              |   | 2 | 2  |    |
| 22-5               | D              | 6               |              |   |   | 2  | 4  |
| 22-6               | D              | 3               |              |   | 2 |    | 1  |
| 22-7               | E              | 1               | 1            |   |   |    |    |
| 22-8               | E              | 2               |              |   |   | 2  |    |
| 22-9               | E              | 3               |              |   |   | 3  |    |
| 22-10              | E              | 4               |              |   |   |    | 4  |
| 22-11              | B              | 2               |              |   |   |    | 2  |
| 22-12              | D              | 5               |              |   | 2 |    | 3  |
| 22-13              | D/A            | 5               |              |   |   | 4  | 1  |
| 22-14              | A              | 19              |              |   |   |    | 19 |
| 22-15              | E/A            | 6               |              |   |   | 5  | 1  |
| 22-16              | A              | 9               |              |   |   | 3  | 6  |
| 22-17              | D/A            | 9               |              |   |   | 1  | 8  |
| 22-18              | D/A            | 8               |              |   |   |    | 8  |
| 22-19              | A              | 14              |              |   |   |    | 14 |
| 22-20              | A              | 9               |              |   |   |    | 9  |
| 22-21              | A              | 3               | 1            |   |   |    | 2  |
| 22-22              | A              | 4               |              |   | 4 |    |    |
| 22-23              | D/A            | 8               |              |   |   | 8  |    |
| 22-24              | D/A            | 6               |              |   |   | 2  | 4  |
| 22-27              | D/A            | 9               |              |   | 1 |    | 8  |
| 22-28              | A              | 7               |              |   |   | 7  |    |
| 22-34              | D              | 5               |              |   |   | 3  | 2  |
| 24-2               | D              | 7               |              |   |   | 7  |    |
| 24-3               | D              | 7               |              |   |   | 2  | 5  |
| 24-4               |                | 1               |              |   |   |    | 3  |
| 24-5               | A              | 16              |              |   |   |    | 16 |
| 24-6               | D/A            | 8               |              |   |   | 8  |    |
| 24-06              | A              | 6               |              | 4 |   |    | 2  |
| 24-7               | A              | 16              |              |   |   | 2  | 14 |
| 24-9               | A              | 2               |              | 2 |   |    |    |
| 24-10              | A              | 7               |              |   | 7 |    |    |

| Insert Arrangement | Service Rating | Total Cont-acts | Contact Size |   |    |    |    |
|--------------------|----------------|-----------------|--------------|---|----|----|----|
|                    |                |                 | 0            | 4 | 8  | 12 | 16 |
| 24-11              | A              | 9               |              |   |    | 3  | 6  |
| 24-12              | A              | 5               |              |   | 2  |    | 3  |
| 24-16              | D/A            | 7               |              |   | 1  | 3  | 3  |
| 24-17              | D              | 5               |              |   |    | 2  | 3  |
| 24-20              | D              | 11              |              |   |    | 2  | 9  |
| 24-21              | D              | 10              |              |   | 1  |    | 9  |
| 24-22              | D              | 4               |              |   | 4  |    |    |
| 24-27              | E              | 7               |              |   |    |    | 7  |
| 24-28              | Inst           | 24              |              |   |    |    | 24 |
| 28-1               | D/A            | 9               |              |   | 3  | 6  |    |
| 28-2               | D              | 14              |              |   |    | 2  | 12 |
| 28-3               | E              | 3               |              |   | 3  |    |    |
| 28-4               | E/D            | 9               |              |   |    | 2  | 7  |
| 28-5               | D              | 5               |              | 2 |    | 1  | 2  |
| 28-6               | D              | 3               |              | 3 |    |    |    |
| 28-7               | D              | 2               |              | 2 |    |    |    |
| 28-8               | E/D/A          | 12              |              |   |    | 2  | 10 |
| 28-9               | D              | 12              |              |   |    | 6  | 6  |
| 28-09              | A              | 9               |              | 4 |    |    | 5  |
| 28-10              | D/A            | 7               |              | 2 | 2  | 3  |    |
| 28-11              | A              | 22              |              |   |    | 4  | 18 |
| 28-12              | A              | 26              |              |   |    |    | 26 |
| 28-13              | A              | 26              |              |   |    |    | 26 |
| 28-15              | A              | 35              |              |   |    |    | 35 |
| 28-16              | A              | 20              |              |   |    |    | 20 |
| 28-17              | B/D/A          | 15              |              |   |    |    | 15 |
| 28-18              | C/D/A/Inst     | 12              |              |   |    |    | 12 |
| 28-19              | B/D/A          | 10              |              |   |    | 4  | 6  |
| 28-20              | A              | 14              |              |   |    | 10 | 4  |
| 28-21              | A              | 37              |              |   |    |    | 37 |
| 28-22              | D              | 6               |              | 3 |    |    | 3  |
| 28-51              | D              | 12              |              |   |    |    | 12 |
| 32-1               | D/A            | 5               | 2            |   |    | 3  |    |
| 32-3               | D              | 9               | 1            | 2 |    | 2  | 4  |
| 32-5               | D              | 2               | 2            |   |    |    |    |
| 32-6               | A              | 23              |              | 2 | 3  | 2  | 16 |
| 32-7               | INSTA          | 35              |              |   |    | 7  | 28 |
| 32-8               | A              | 30              |              |   |    | 6  | 24 |
| 32B-13             | D              | 13              |              |   | 13 |    |    |
| 32-17              | D              | 4               |              | 4 |    |    |    |
| 32-22              | A              | 54              |              |   |    |    | 54 |
| 36-1               | D              | 22              |              |   |    | 4  | 18 |
| 36-3               | D              | 6               | 3            |   |    | 3  |    |
| 36-4               | D/A            | 3               | 3            |   |    |    |    |
| 36-5               | A              | 4               | 4            |   |    |    |    |
| 36-6               | A              | 6               | 2            | 4 |    |    |    |
| 36-7               | A              | 47              |              |   |    | 7  | 40 |
| 36-8               | A              | 47              |              |   |    | 1  | 46 |
| 36-9               | A              | 31              |              | 1 | 2  | 14 | 14 |
| 36-10              | A              | 48              |              |   |    |    | 48 |
| 36-11              | A              | 48              |              |   |    |    | 48 |
| 36-12              | A              | 48              |              |   |    |    | 48 |
| 36-13              | E/A            | 17              |              |   |    | 2  | 15 |
| 36-14              | D              | 16              |              |   | 5  | 5  | 6  |
| 36-15              | D/A            | 35              |              |   |    |    | 35 |
| 36-16              | A              | 47              |              |   |    | 7  | 40 |
| 36-17              | A              | 47              |              |   |    | 7  | 40 |
| 38-18              | A              | 31              |              | 1 | 2  | 14 | 14 |
| 36-20              | A              | 34              |              |   | 2  | 2  | 30 |
| 36-46              | A              | 27              |              |   |    |    | 27 |
| 36-52              | A              | 52              |              |   |    |    | 52 |
| 40-56              | A              | 85              |              |   |    |    | 85 |
| 40-63              | A              | 61              |              |   |    |    |    |

# Insert Arrangements

Front face of pin insert or rear of socket insert illustrated










|                    |        |        |        |        |       |       |
|--------------------|--------|--------|--------|--------|-------|-------|
|                    |        |        |        |        |       |       |
| Insert arrangement | 10S-2  | 10SL-3 | 10SL-4 | 12S-3  | 12S-4 | 12-5  |
| Service rating     | A      | A      | A      | A      | A     | D     |
| Number of contacts | 1      | 3      | 2      | 2      | 1     | 1     |
| Contact size       | 16     | 16     | 16     | 16     | 16    | 12    |
| Premating contact  | —      | C      | —      | —      | —     | —     |
|                    |        |        |        |        |       |       |
| Insert arrangement | 14S-A7 | 14S-1  | 14S-2  | 14S-4  | 14S-5 | 14S-6 |
| Service rating     | A      | A      | Inst.  | D      | Inst. | Inst. |
| Number of contacts | 7      | 3      | 4      | 1      | 5     | 6     |
| Contact size       | 16     | 16     | 16     | 16     | 16    | 16    |
| Premating contact  | —      | —      | —      | —      | —     | —     |
|                    |        |        |        |        |       |       |
| Insert arrangement | 14S-7  | 14S-9  | 14S-10 | 14S-12 | 14-3  | 16S-1 |
| Service rating     | A      | A      | Inst.  | A      | A     | A     |
| Number of contacts | 3      | 2      | 4      | 3      | 1     | 7     |
| Contact size       | 16     | 16     | 16     | 16     | 8     | 16    |
| Premating contact  | B      | —      | —      | B      | —     | G     |
|                    |        |        |        |        |       |       |
| Insert arrangement | *16S-3 | 16S-4  | 16S-5  | 16S-6  | 16S-8 | *16-2 |
| Service rating     | B      | D      | A      | A      | A     | E     |
| Number of contacts | 1      | 2      | 3      | 3      | 5     | 1     |
| Contact size       | 16     | 16     | 16     | 16     | 16    | 12    |
| Premating contact  | —      | —      | A      | B      | E     | —     |

\*Not tooled up, can be tooled up on request. Contact Factory.

# Insert Arrangements

Front face of pin insert or rear of socket insert illustrated



Insert arrangement  
Service rating  
Number of contacts  
Contact size  
Premating contact

16-7  
A  
1 2  
8 16  
C








16-9  
A  
2 2  
12 16  
—

16-10  
A  
3  
12  
B

16-11  
A  
2  
12  
—

16-12  
A  
1  
4  
—

\*16-13  
A  
2  
12  
—



Insert arrangement  
Service rating  
Number of contacts  
Contact size  
Premating contact

18-1  
B,C,F,G=A; Bal.=Inst.  
10  
16  
—

18-3  
D  
2  
12  
—







18-4  
D  
4  
16  
A

18-5  
D  
2 1  
12 16  
C

\*18-6  
D  
1  
4  
—

18-06  
A  
2 4  
16 12  
—

18-7  
B  
1  
8  
—



Insert arrangement  
Service rating  
Number of contacts  
Contact size  
Premating contact

18-8  
A  
1 7  
12 16  
H







18-9  
Inst.  
2 5  
12 16  
—

18-10  
A  
4  
12  
D

18-11  
A  
5  
12  
E

18-12  
A  
6  
16  
C or D

\*18-13  
A  
1 3  
8 12  
A



100° rotation  
of 18-9

Insert arrangement  
Service rating  
Number of contacts  
Contact size  
Premating contact

\*18-14  
A  
1 1  
4 16  
—

18-15  
A  
4  
12  
—

18-16  
C  
1  
12  
—

\*18-17  
Inst.  
2 5  
12 16  
—



18-19  
A  
10  
16  
K

18-20  
A  
5  
16  
D


\*Not tooled up, can be tooled up on request. Contact Factory.

# Insert Arrangements

Front face of pin insert or rear of socket insert illustrated




| Insert arrangement | 18-22 | 250° rotation<br>of 18-1 | *18-24                   | *18-29 | 110° rotation<br>of 18-20 | 260° rotation<br>of 18-20 | 20-2 | 20-3 |
|--------------------|-------|--------------------------|--------------------------|--------|---------------------------|---------------------------|------|------|
| Service rating     | D     |                          | B, C, F, G=A; Bal.=Inst. | A      | A                         | A                         | D    | D    |
| Number of contacts | 3     |                          | 10                       | 5      | 5                         | 5                         | 1    | 4    |
| Contact size       | 16    |                          | 16                       | 16     | 16                        | 16                        | 0    | 12   |
| Premating contact  | C     |                          | —                        | D      | C                         | C                         | —    | A    |



| Insert arrangement | 20-4   | *20-6 | 20-7                       | 20-8  | 20-9        | 20A-9 |
|--------------------|--------|-------|----------------------------|-------|-------------|-------|
| Service rating     | D      | D     | A, B, H, G=D; C, D, E, F=A | Inst. | H=D; Bal.=A | A     |
| Number of contacts | 4      | 3     | 8                          | 2 4   | 1 7         | 9     |
| Contact size       | 12     | 16    | 16                         | 8 16  | 12 16       | 12    |
| Premating contact  | C or D | A     | A                          | —     | H           | —     |



| Insert arrangement | 20-11 | *20-12 | 20-14 | 20-15  | 20-16 | 20-17  |
|--------------------|-------|--------|-------|--------|-------|--------|
| Service rating     | Inst. | A      | A     | A      | A     | A      |
| Number of contacts | 13    | 1 1    | 2 3   | 7      | 2 7   | 5 1    |
| Contact size       | 16    | 4 16   | 8 12  | 12     | 12 16 | 12 16  |
| Premating contact  | —     | —      | D     | A or D | E     | E or F |




| Insert arrangement | 20-18 | 20-19 | 20-20 | *20-21 | 20-22 | 20-23 |
|--------------------|-------|-------|-------|--------|-------|-------|
| Service rating     | A     | A     | A     | A      | A     | A     |
| Number of contacts | 3 6   | 3     | 1 3   | 1 8    | 3 3   | 2     |
| Contact size       | 12 16 | 8     | 4 12  | 12 16  | 8 16  | 8     |
| Premating contact  | D     | C     | A     | 1      | —     | —     |

\*Not tooled up, can be tooled up on request. Contact Factory.

# Insert Arrangements

Front face of pin insert or rear of socket insert illustrated





|                    |       |           |       |                |                        |
|--------------------|-------|-----------|-------|----------------|------------------------|
|                    |       |           |       |                |                        |
| Insert arrangement | 20-24 | *20-25    | 20-27 | 20-29          | 250° rotation of 20-11 |
| Service rating     | A     | Inst.     | A     | A              | *20-30                 |
| Number of contacts | 2 2   | 13        | 14    | 17             | Inst.                  |
| Contact size       | 8 16  | 16        | 16    | 16             | 13                     |
| Premating contact  | —     | —         | M     | G              | —                      |
|                    |       |           |       |                |                        |
| Insert arrangement | 20-33 | 20 A - 48 | 22-1  | 22-2           | *22-4                  |
| Service rating     | A     | A         | D     | D              | A                      |
| Number of contacts | 11    | 19        | 2     | 3              | 2 2                    |
| Contact size       | 16    | 16        | 8     | 8              | 8 12                   |
| Premating contact  | E     | —         | —     | A              | C                      |
|                    |       |           |       |                |                        |
| Insert arrangement | 22-5  | *22-6     | 22-7  | *22-8          | 22-9                   |
| Service rating     | D     | D         | E     | E              | E                      |
| Number of contacts | 2 4   | 2 1       | 1     | 2              | 3                      |
| Contact size       | 12 16 | 8 16      | 0     | 12             | 12                     |
| Premating contact  | D     | B         | —     | —              | A                      |
|                    |       |           |       |                |                        |
| Insert arrangement | 22-10 | 22-11     | 22-12 | 22-13          | 22-14                  |
| Service rating     | E     | B         | D     | E=D; A,B,C,D=A | A                      |
| Number of contacts | 4     | 2         | 2 3   | 4 1            | 19                     |
| Contact size       | 16    | 16        | 8 16  | 12 16          | 16                     |
| Premating contact  | C     | —         | A     | E              | A                      |


\*Not tooled up, can be tooled up on request. Contact Factory.

# Insert Arrangements


Front face of pin insert or rear of socket insert illustrated



|                    |                 |       |            |                     |       |       |
|--------------------|-----------------|-------|------------|---------------------|-------|-------|
| Insert arrangement | 22-15           | 22-16 | *22-17     | 22-18               | 22-19 | 22-20 |
| Service rating     | D=E;A,B,C,E,F=A | A     | A=D;Bal.=A | A,B,F,G,H=D;C,D,E=A | A     | A     |
| Number of contacts | 5 1             | 3 6   | 1 8        | 8                   | 14    | 9     |
| Contact size       | 12 16           | 12 16 | 12 16      | 16                  | 16    | 16    |
| Premating contact  | D               | D     | E          | D                   | F     | D     |



|                    |        |        |            |                 |            |       |
|--------------------|--------|--------|------------|-----------------|------------|-------|
| Insert arrangement | *22-21 | 22-22  | 22-23      | 22-24           | 22-27      | 22-28 |
| Service rating     | A      | A      | H=D;Bal.=A | C,D,E=D;A,B,F=A | J=D;Bal.=A | A     |
| Number of contacts | 1 2    | 4      | 8          | 2 4             | 1 8        | 7     |
| Contact size       | 0 16   | 8      | 12         | 12 16           | 8 16       | 12    |
| Premating contact  | —      | C or D | A or D     | D               | —          | G     |




|                    |        |      |       |      |      |                |
|--------------------|--------|------|-------|------|------|----------------|
| Insert arrangement | *22-34 | 24-2 | *24-3 | 24-4 | 24-5 | 24-6           |
| Service rating     | D      | D    | D     | A    | A    | A,G,H=D;Bal.=A |
| Number of contacts | 3 2    | 7    | 2 5   | 3 1  | 16   | 8              |
| Contact size       | 12 16  | 12   | 12 16 | 16 0 | 16   | 12             |
| Premating contact  | E      | A    | D     | —    | S    | D              |

\*Not tooled up, can be tooled up on request. Contact Factory.

# Insert Arrangements

Front face of pin insert or rear of socket insert illustrated


|                |    |    |   |   |   |
|----------------|----|----|---|---|---|
|                |    |    |   |   |   |
| CONTACT LEGEND | 16 | 12 | 8 | 4 | 0 |



24-06


Insert arrangement  
Service rating  
Number of contacts  
Contact size  
Premating contact

A  
2 4  
16 8  
—




24-7

A  
2 14  
12 16  
G




24-9

A  
2  
4  
—




24-10

A  
7  
8  
D or E or G



24-11


A  
3 6  
8 12  
E



24-12


Insert arrangement  
Service rating  
Number of contacts  
Contact size  
Premating contact

A  
2 3  
4 12  
—




\*24-16

A, B, F, G=D; C, D, E=A  
1 3 3  
8 12 16  
G




\*24-17

D  
2 3  
12 16  
D




24-20

D  
2 9  
12 16  
A



24-21


D  
1 9  
8 16  
E



24-22


Insert arrangement  
Service rating  
Number of contacts  
Contact size  
Premating contact

D  
4  
8  
D




\*24-27

E  
7  
16  
D




24-28

Inst.  
24  
16  
—



28-1

A, J, E=D; Bal.=A  
3 6  
8 12  
E





\*28-2

D  
2 12  
12 16  
E


\*Not tooled up, can be tooled up on request. Contact Factory.

Front face of pin insert or rear of socket insert illustrated




Insert arrangement  
Service rating  
Number of contacts  
Contact size  
Premating contact


28-3  
E  
3  
8  
A




\*28-4  
G,S,P=E; Bal.=D  
2 7  
12 16  
E



\*28-5  
D  
2 1 2  
4 12 16  
—




28-6  
D  
3  
4  
A




Insert arrangement  
Service rating  
Number of contacts  
Contact size  
Premating contact


28-7  
D  
2  
4  
—




28-8  
L,M=E; B=D; Bal.=A  
2 10  
12 16  
D



28-9  
D  
6 6  
12 16  
E




28-09  
A  
5 4  
16 4  
—




Insert arrangement  
Service rating  
Number of contacts  
Contact size  
Premating contact


28-10  
G=D; Bal.=A  
2 2 3  
4 8 12  
G



28-11  
A  
4 18  
12 16  
M



28-12  
A  
26  
16  
H








100° rotation  
of 28-12  
\*28-13  
A  
26  
16  
H

\*Not tooled up, can be tooled up on request. Contact Factory.

# Insert Arrangements

Front face of pin insert or rear of socket insert illustrated







Insert arrangement  
Service rating  
Number of contacts  
Contact size  
Premating contact

28-15  
A  
35  
16  
M

28-16  
A  
20  
16  
F

\*28-17  
R=B;M,N,P=D;A to L=A  
15  
16  
N

28-18  
M=C;G,H,J,K,L=D;A,B=ABal.=Inst.  
12  
16  
—







Insert arrangement  
Service rating  
Number of contacts  
Contact size  
Premating contact

28-19  
H,M=B;A,B=D;Bal.=A  
4 6  
12 16  
H

28-20  
A  
10 4  
12 16  
E

28-21  
A  
37  
16  
A

28-22  
D  
3 3  
4 16  
—



Insert arrangement  
Service rating  
Number of contacts  
Contact size  
Premating contact

28-51  
D  
12  
12  
—



32-1  
A=E;B,C,D,E=A  
2 3  
0 12  
—

\*32-3  
D  
1 2 2 4  
0 4 12 16  
—


32-5  
D  
2  
0

\*Not tooled up, can be tooled up on request. Contact Factory.


Front face of pin insert or rear of socket insert illustrated




32-6  
A  
16 2 3 2  
16 12 8 4  
—




32-7  
INST , A  
4 24 7  
16 12  
—




32-8  
A  
6 24  
12 16  
S




32-17  
D  
4  
4  
—




32-22  
A  
54  
16  
—



32B-13  
D  
13  
8  
—  
—





\*36-1  
D  
4 18  
12 16  
—



36-3  
D  
3 3  
0 12  
—


\*Not tooled up, can be tooled up on request. Contact Factory.

Front face of pin insert or rear of socket insert illustrated




Insert arrangement  
Service rating  
Number of contacts  
Contact size  
Premating contact


36-4  
A=D; B, C=A  
3  
0  
—



36-5  
A  
4  
0  
—




36-6  
A  
2 4  
0 4  
—




Insert arrangement  
Service rating  
Number of contacts  
Contact size  
Premating contact


\*36-7  
A  
7 40  
12 16  
x or y



\*36-8  
A  
1 46  
12 16  
Y




\*36-9  
A  
1 2 14 14  
4 8 12 16  
P




Insert arrangement  
Service rating  
Number of contacts  
Contact size  
Premating contact

36-10  
A  
48  
16  
A



100° rotation  
of 36-10  
\*36-11  
A  
48  
16  
A







250° rotation  
of 36-10  
\*36-12  
A  
48  
16  
A

\*Not tooled up, can be tooled up on request. Contact Factory.

# Insert Arrangements

Front face of pin insert or rear of socket insert illustrated






Insert arrangement  
Service rating  
Number of contacts  
Contact size  
Premating contact

\*36-13  
N,P,Q=E; Bal.=A  
2 15  
12 16  
—

\*36-14  
D  
5 5 6  
8 12 16  
—

\*36-15  
M=D; Bal.=A  
35  
16  
J



100°rotation  
of 36-7

250°rotation  
of 36-7






100°rotation  
of 36-9

Insert arrangement  
Service rating  
Number of contacts  
Contact size  
Premating contact

\*36-16  
A  
7 40  
12 16  
x or y

\*36-17  
A  
7 40  
12 16  
x or y

\*36-18  
A  
1 2 14 16  
4 8 12 16  
—



Insert arrangement  
Service rating  
Number of contacts  
Contact size  
Premating contact

\*36-20  
A  
2 2 30  
8 12 16  
k

36-46  
A  
27  
16  
—

36-52  
A  
52  
16  
—

40-56  
A  
85  
16  
—

40-63  
A  
61  
16  
—

\*Not tooled up, can be tooled up on request. Contact Factory.



# MIL -C-5015




MS Threaded Version  
connector

## Wall mounting receptacle

MS-3100 MS-4100



MOUNTING HOLES  
4.39 DIA. FOR SIZE 32 AND 36  
3.73 DIA. FOR SIZE 24 AND 28  
3.05 DIA. FOR ALL OTHER SIZES  
4.55 DIA. FOR 40 SIZE





All dimensions are in mm

| Connector Size | A Thread in inches | K    | M     | O     | R     | S     | V Thread in inches |
|----------------|--------------------|------|-------|-------|-------|-------|--------------------|
| 10SL           | 5/8-24 UNEF        | 1.98 | 14.29 | 20.62 | 18.25 | 25.68 | 5/8-24 NEF         |
| 12S            | 3/4-20 UNEF        | 1.98 | 14.29 | 20.62 | 20.64 | 27.76 | 11/16-24NEF        |
| 12             | 3/4-20 UNEF        | 1.98 | 19.05 | 20.62 | 20.64 | 27.76 | 11/16-24NEF        |
| 14S            | 7/8-20 UNEF        | 1.98 | 14.29 | 23.82 | 23.02 | 30.43 | 3/4-20 UNEF        |
| 14             | 7/8-20 UNEF        | 1.98 | 19.05 | 23.82 | 23.02 | 30.43 | 3/4-20 UNEF        |
| 16S            | 1-20 UNEF          | 1.98 | 14.29 | 26.97 | 24.61 | 32.82 | 7/8-20 UNEF        |
| 16             | 1-20 UNEF          | 3.17 | 19.05 | 26.97 | 24.61 | 32.82 | 7/8-20 UNEF        |
| 18             | 1 1/8-18 UNEF      | 3.17 | 19.05 | 30.17 | 26.99 | 35.07 | 1-20 UNEF          |
| 20             | 1 1/4-18 UNEF      | 3.17 | 19.05 | 33.32 | 29.37 | 38.38 | 1 1/8-18 NS        |
| 22             | 1 3/8-18 UNEF      | 3.17 | 19.05 | 36.52 | 31.75 | 41.55 | 1 1/4-18 NEF       |
| 24             | 1 1/2-18 UNEF      | 3.17 | 20.64 | 39.67 | 34.92 | 44.70 | 1 3/8-18 NEF       |
| 28             | 1 3/4-18 UNS       | 3.17 | 20.64 | 46.02 | 39.69 | 51.08 | 1 5/8-18 NEF       |
| 32             | 2.00-18 UNS        | 3.17 | 22.25 | 53.0  | 44.45 | 57.15 | 1 7/8-16UN         |
| 36             | 2 1/4-16 UN        | 3.17 | 22.22 | 58.72 | 49.21 | 63.78 | 2 1/16-16UN        |
| 40             | 2 1/2-16 UN        | 3.45 | 22.22 | 62.00 | 55.58 | 69.85 | 2 5/16-16 UN       |

## Cable Connecting Receptacle

MS-3101 MS-4101




All dimensions are in mm

| Connector Size | A Thread in inches | V Thread in inches |
|----------------|--------------------|--------------------|
| 10SL           | 5/8-24 UNEF        | 5/8-24 NEF         |
| 12S            | 3/4-20 UNEF        | 11/16-24 NEF       |
| 12             | 3/4-20 UNEF        | 11/16-24 NEF       |
| 14S            | 7/8-20 UNEF        | 3/4-20 UNEF        |
| 14             | 7/8-20 UNEF        | 3/4-20 UNEF        |
| 16S            | 1-20 UNEF          | 7/8-20 UNEF        |
| 16             | 1-20 UNEF          | 7/8-20 UNEF        |
| 18             | 1 1/8-18 UNEF      | 1-20 UNEF          |
| 20             | 1 1/4-18 UNEF      | 1 1/8-18 NS        |
| 22             | 1 3/8-18 UNEF      | 1 1/4-18 NEF       |
| 24             | 1 1/2-18 UNEF      | 1 3/8-18 NEF       |
| 28             | 1 3/4-18 UNS       | 1 5/8-18 NEF       |
| 32             | 2-18 UNS           | 1 7/8-16UN         |
| 36             | 2 1/4-16 UN        | 2 1/16-16UN        |
| 40             | 2 1/2-16 UN        | 2 5/16-16 UN       |

## Box mounting receptacle

MS-3102 MS-4102



### MOUNTING HOLES

4.39 DIA. FOR SIZE 32 AND 36

3.73 DIA. FOR SIZE 24 AND 28

3.05 DIA. FOR ALL OTHER SIZES


4.55 FOR 40 SIZE

All dimensions are in mm

| Connector Size | A Thread in inches | K    | L     | M     | N     | R     | S     |
|----------------|--------------------|------|-------|-------|-------|-------|-------|
| 10SL           | 5/8-24 UNEF        | 1.98 | 30.18 | 13.89 | 15.87 | 18.25 | 25.68 |
| 12S            | 3/4-20 UNEF        | 1.98 | 30.18 | 14.28 | 17.46 | 20.64 | 28.04 |
| 12             | 3/4-20 UNEF        | 1.98 | 41.28 | 19.05 | 17.46 | 20.64 | 28.04 |
| 14S            | 7/8-20 UNEF        | 1.98 | 30.18 | 14.28 | 19.05 | 23.02 | 30.43 |
| 14             | 7/8-20 UNEF        | 1.98 | 41.28 | 19.05 | 19.05 | 23.02 | 30.43 |
| 16S            | 1-20 UNEF          | 1.98 | 30.18 | 14.28 | 22.22 | 24.61 | 32.82 |
| 16             | 1-20 UNEF          | 3.17 | 41.28 | 19.05 | 22.22 | 24.61 | 32.82 |
| 18             | 1 1/8-18 UNEF      | 3.17 | 49.28 | 19.05 | 25.40 | 26.99 | 35.08 |
| 20             | 1 1/4-18 UNEF      | 3.17 | 49.28 | 19.05 | 28.57 | 29.37 | 38.38 |
| 22             | 1 3/8-18 UNEF      | 3.17 | 49.28 | 19.05 | 31.75 | 31.75 | 41.55 |
| 24             | 1 1/2-18 UNEF      | 3.17 | 49.28 | 20.64 | 34.92 | 34.92 | 44.73 |
| 28             | 1 3/4-18 UNS       | 3.17 | 49.28 | 20.64 | 41.27 | 39.69 | 51.08 |
| 32             | 2-18 UNS           | 3.17 | 49.28 | 22.22 | 48.26 | 44.45 | 57.15 |
| 36             | 2 1/4-16 UN        | 3.17 | 49.28 | 22.22 | 53.97 | 49.21 | 63.78 |
| 40             | 2 1/2-16 UN        | 3.45 | 49.28 | 22.22 | 58.25 | 55.58 | 69.85 |

## Straight Plug

MS-3106 MS-4106




All dimensions are in mm

| Connector Size | A Thread in inches | Q max | V Thread in inches |
|----------------|--------------------|-------|--------------------|
| 10SL           | 5/8-24 UNEF        | 19.05 | 5/8-24 NEF         |
| 12S            | 3/4-20 UNEF        | 19.84 | 11/16-24NEF        |
| 12             | 3/4-20 UNEF        | 19.84 | 11/16-24NEF        |
| 14S            | 7/8-20 UNEF        | 22.22 | 3/4-20 UNEF        |
| 14             | 7/8-20 UNEF        | 22.22 | 3/4-20 UNEF        |
| 16S            | 1-20 UNEF          | 25.40 | 7/8-20 UNEF        |
| 16             | 1-20 UNEF          | 25.40 | 7/8-20 UNEF        |
| 18             | 1 1/8-18 UNEF      | 28.57 | 1-20 UNEF          |
| 20             | 1 1/4-18 UNEF      | 31.75 | 1 1/8-18 NS        |
| 22             | 1 3/8-18 UNEF      | 34.92 | 1 1/4-18 NEF       |
| 24             | 1 1/2-18 UNEF      | 38.10 | 1 3/8-18 NEF       |
| 28             | 1 3/4-18 UNS       | 44.45 | 1 5/8-18 NEF       |
| 32             | 2-18 UNS           | 51.75 | 1 7/8-16UN         |
| 36             | 2 1/4-16 UN        | 57.15 | 2 1/16-16UN        |
| 40             | 2 1/2-16 UN        | 63.50 | 2 5/16-20 UN       |

Note - Both versions, straight and diamond knurling available on coupling ring. For details, contact factory.

## Right angle plug MS-3108 MS-4108




All dimensions are in mm

| Connector Size | A Thread in inches | Q max | V Thread in inches |
|----------------|--------------------|-------|--------------------|
| 10SL           | 5/8-24 UNEF        | 19.05 | 5/8-24 NEF         |
| 12S            | 3/4-20 UNEF        | 19.84 | 11/16-24 NEF       |
| 12             | 3/4-20 UNEF        | 19.84 | 11/16-24 NEF       |
| 14S            | 7/8-20 UNEF        | 22.22 | 3/4-20 UNEF        |
| 14             | 7/8-20 UNEF        | 22.22 | 3/4-20 UNEF        |
| 16S            | 1-20 UNEF          | 25.40 | 7/8-20 UNEF        |
| 16             | 1-20 UNEF          | 25.40 | 7/8-20 UNEF        |
| 18             | 1 1/8-18 UNEF      | 28.57 | 1-20 UNEF          |
| 20             | 1 1/4-18 UNEF      | 31.75 | 1 1/8-18 NS        |
| 22             | 1 3/8-18 UNEF      | 34.92 | 1 1/4-18 NEF       |
| 24             | 1 1/2-18 UNEF      | 38.10 | 1 3/8-18 NEF       |
| 28             | 1 3/4-18 UNS       | 44.45 | 1 5/8-18 NEF       |
| 32             | 2-18 UNS           | 51.75 | 1 29/32-18 NS      |
| 36             | 2 1/4-16 NS        | 57.15 | 2 1/16-20 UNS      |
| 40             | 2 1/2-16 UN        | 63.50 | 2 5/16-16 UN       |

Note - Both versions, straight and diamond knurling available on coupling ring. For details, contact factory.

## Other Accessories Dummy receptacle MS-3105




All dimensions are in mm

| Part number (see note) | A     | B     | C    | D Thread in inches | E     | F max. | G     |
|------------------------|-------|-------|------|--------------------|-------|--------|-------|
| MS-3105-10S            | 25.4  | 18.26 | 3.05 | 5/8-24             | 14.27 | 3.96   | 8.20  |
| MS-3105-12S            | 27.79 | 20.62 | 3.05 | 3/4-20             | 14.27 | 3.96   | 11.43 |
| MS-3105-12             | 27.79 | 20.62 | 3.05 | 3/4-20             | 19.05 | 3.96   | 11.43 |
| MS-3105-14S            | 30.17 | 23.01 | 3.05 | 7/8-20             | 14.27 | 3.96   | 13.36 |
| MS-3105-14             | 30.17 | 23.01 | 3.05 | 7/8-20             | 19.05 | 3.96   | 13.36 |
| MS-3105-16S            | 32.54 | 24.61 | 3.05 | 1-20               | 14.27 | 3.96   | 16.41 |
| MS-3105-16             | 32.54 | 24.61 | 3.05 | 1-20               | 19.05 | 3.96   | 16.41 |
| MS-3105-18             | 34.92 | 26.97 | 3.05 | 1 1/8-18           | 19.05 | 5.16   | 18.03 |
| MS-3105-20             | 38.10 | 29.36 | 3.05 | 1 1/4-18           | 19.05 | 5.16   | 23.54 |
| MS-3105-22             | 41.27 | 31.75 | 3.05 | 1 3/8-18           | 19.05 | 5.16   | 25.93 |
| MS-3105-24             | 44.45 | 34.92 | 3.73 | 1 1/2-18           | 20.62 | 5.16   | 29.21 |
| MS-3105-28             | 50.8  | 39.67 | 3.73 | 1 3/4-18           | 20.62 | 5.16   | 34.67 |
| MS-3105-36             | 63.5  | 49.22 | 4.39 | 2 1/4-16           | 22.2  | 9.11   | 46.56 |

Note: The dash number also indicates shell size.

**MS-25043**

**For receptacles** Has internal threads and is used on all receptacles. Gasket is provided in the dust cap forming a watertight seal.




All dimensions are in mm

| MS Part number | Shell size  | A Thread in inches | B     | C    | D   | E   |
|----------------|-------------|--------------------|-------|------|-----|-----|
| MS 25043-10D   | MS 10S-1-SL | 5/8-24             | 11.11 | 20.7 | 3.6 | 102 |
| MS 25043-12D   | MS 12-12S   | 3/4- 20            | 11.11 | 25.4 | 3.6 | 115 |
| MS 25043-14D   | MS 14-14S   | 7/8-20             | 11.11 | 28.6 | 3.6 | 115 |
| MS 25043-16D   | MS 16-16S   | 1-20               | 11.11 | 30.2 | 3.6 | 115 |
| MS 25043-18D   | MS 18       | 1 1/8-18           | 11.11 | 34.1 | 3.6 | 115 |
| MS 25043-20D   | MS 20       | 1 1/4-18           | 11.11 | 37.3 | 4.4 | 127 |
| MS 25043-22D   | MS 22       | 1 3/8-18           | 11.11 | 40.4 | 4.4 | 127 |
| MS 25043-24D   | MS 24       | 1 1/2-18           | 11.11 | 43.6 | 4.4 | 140 |
| MS 25043-28D   | MS 28       | 1 3/4-18           | 12.7  | 50   | 4.4 | 197 |
| MS 25043-32D   | MS 32       | 2-18               | 12.7  | 56.3 | 4.8 | 197 |
| MS 25043-36D   | MS 36       | 2 1/4-18           | 12.7  | 62.7 | 4.8 | 197 |
| MS 25043-40D   | MS 40       | 2 1/2-16           | 12.7  | 69   | 4.8 | 197 |

- Notes :**
1. For protective caps with nylon cord, contact factory.
  2. Standard - Plating is Cad. For alternative finishes, contact factory.
  3. Standard - straight knurling. For diamond knurling on caps, contact factory.
  4. Please add 07 suffix for bigger end link.

**Other Accessories****Protective cap for MS series****MS-25042**

**For plugs** Has external threads and is used on all plugs where a coupling ring is provided.



All dimensions are in mm

| MS Part number | Shell size  | A Thread in inches | B     | C    | D   | E   |
|----------------|-------------|--------------------|-------|------|-----|-----|
| MS 25042-10D   | MS 10S-1-SL | 5/8-24             | 16.67 | 17.4 | 4   | 102 |
| MS 25042-12D   | MS 12-12S   | 3/4- 20            | 21.4  | 20.6 | 4   | 115 |
| MS 25042-14D   | MS 14-14S   | 7/8-20             | 21.4  | 23.7 | 4   | 115 |
| MS 25042-16D   | MS 16-16S   | 1-20               | 21.4  | 26.9 | 4   | 115 |
| MS 25042-18D   | MS 18       | 1 1/8-18           | 21.4  | 30   | 4   | 115 |
| MS 25042-20D   | MS 20       | 1 1/4-18           | 21.4  | 33   | 4.8 | 127 |
| MS 25042-22D   | MS 22       | 1 3/8-18           | 21.4  | 36.4 | 4.8 | 127 |
| MS 25042-24D   | MS 24       | 1 1/2-18           | 21.4  | 39.6 | 4.8 | 140 |
| MS 25042-28D   | MS 28       | 1 3/4-18           | 21.4  | 46   | 4.8 | 197 |
| MS 25042-32D   | MS 32       | 2-18               | 21.4  | 52   | 5.6 | 197 |
| MS 25042-36D   | MS 36       | 2 1/4-18           | 21.4  | 58.7 | 5.6 | 197 |
| MS 25042-40D   | MS 40       | 2 1/2-16           | 21.4  | 65   | 5.6 | 197 |


# MIL -C-5015



97B Series Bayonet Version  
connector

## Wall mounting receptacle


100



| Shell Size | 'A'<br>+0.0 -0.15 | 'K'<br>±0.20 | 'M'<br>+0.41 - 0.0 | 'R'   | 'S'<br>±0.20 | 'L'<br>MAX | PG THD         |
|------------|-------------------|--------------|--------------------|-------|--------------|------------|----------------|
| 10SL       | 18.21             | 2.79         | 14.20              | 18.20 | 25.40        | 27.60      | 5/8"-24 UNEF   |
| 12S        | 21.40             | 3.20         | 14.20              | 20.60 | 28.00        | 27.60      | 5/8"-24 UNEF   |
| 14S        | 24.61             | 3.20         | 14.20              | 23.00 | 30.00        | 27.60      | 3/4"-24 UNEF   |
| 16S        | 27.41             | 3.20         | 14.20              | 24.60 | 32.50        | 27.60      | 7/8"-24 UNEF   |
| 16         | 27.41             | 3.20         | 19.00              | 24.60 | 32.50        | 33.80      | 7/8"-24 UNEF   |
| 18         | 30.81             | 3.99         | 19.00              | 27.00 | 35.00        | 33.80      | 1"-20 UNEF     |
| 20         | 34.19             | 3.99         | 19.00              | 29.40 | 38.00        | 33.80      | 1 1/8"-18 UNEF |
| 22         | 37.39             | 3.99         | 19.00              | 31.80 | 41.00        | 33.80      | 1 1/8"-18 UNEF |
| 24         | 40.89             | 3.99         | 20.60              | 34.90 | 44.00        | 35.70      | 1 3/8"-18 UNEF |
| 28         | 46.71             | 3.99         | 20.60              | 39.70 | 50.80        | 35.70      | 1 5/8"-18 UNEF |
| 32         | 53.39             | 3.99         | 22.20              | 44.50 | 57.00        | 37.30      | 1 7/8"-16 UN   |
| 36         | 59.59             | 3.99         | 22.20              | 49.20 | 63.50        | 37.30      | 2 1/16"-16 UN  |

## Cable connecting receptacle


101



| Shell Size | 'A'<br>+0.0 -0.15 | 'K'<br>±0.20 | 'M'<br>+0.41 - 0.0 | 'Q'<br>+0.20 | 'S'<br>±0.20 | 'L'<br>MAX | T<br>-2A THD   |
|------------|-------------------|--------------|--------------------|--------------|--------------|------------|----------------|
| 10SL       | 18.21             | 2.79         | 14.20              | 20.60        | 25.00        | 27.60      | 5/8"-24 UNEF   |
| 12S        | 21.40             | 3.20         | 14.20              | 23.60        | 27.60        | 27.60      | 5/8"-24 UNEF   |
| 14S        | 24.61             | 3.20         | 14.20              | 25.40        | 29.60        | 27.60      | 3/4"-24 UNEF   |
| 16S        | 27.41             | 3.20         | 14.20              | 28.60        | 32.10        | 27.60      | 7/8"-24 UNEF   |
| 16         | 27.41             | 3.20         | 19.00              | 28.60        | 32.10        | 33.80      | 7/8"-24 UNEF   |
| 18         | 30.81             | 3.99         | 19.00              | 31.70        | 34.60        | 33.80      | 1"-20 UNEF     |
| 20         | 34.19             | 3.99         | 19.00              | 34.90        | 37.60        | 33.80      | 1 1/8"-18 UNEF |
| 22         | 37.39             | 3.99         | 19.00              | 31.70        | 40.90        | 33.80      | 1 1/4"-18 UNEF |
| 24         | 40.89             | 3.99         | 20.60              | 41.30        | 44.40        | 35.70      | 1 3/8"-18 UNEF |
| 28         | 46.71             | 3.99         | 20.60              | 47.60        | 50.70        | 35.70      | 1 5/8"-18 UNEF |
| 32         | 53.39             | 3.99         | 22.20              | 54.00        | 56.90        | 37.30      | 1 7/8"-16 UN   |
| 36         | 59.59             | 3.99         | 22.20              | 60.60        | 63.40        | 37.30      | 2 1/16"-16 UN  |

## Box mounting receptacle


102



| SHELL SIZE | 'A'<br>+0.0 -0.15 | 'K'<br>±0.20 | 'M'<br>+0.41 -0.0 | 'R'   | 'S'<br>±0.20 | 'L'<br>MAX. |
|------------|-------------------|--------------|-------------------|-------|--------------|-------------|
| 10SL       | 18.21             | 2.79         | 14.20             | 18.20 | 25.40        | 24.70       |
| 12S        | 21.40             | 3.20         | 14.20             | 20.60 | 28.00        | 27.60       |
| 14S        | 24.61             | 3.20         | 14.20             | 23.00 | 30.00        | 24.70       |
| 16S        | 27.41             | 3.20         | 14.20             | 24.60 | 32.50        | 24.70       |
| 16         | 27.41             | 3.20         | 19.00             | 24.60 | 32.50        | 33.80       |
| 18         | 30.81             | 3.99         | 19.00             | 27.00 | 35.00        | 33.80       |
| 20         | 34.19             | 3.99         | 19.00             | 29.40 | 38.00        | 33.80       |
| 22         | 37.39             | 3.99         | 19.00             | 31.80 | 41.00        | 33.80       |
| 24         | 40.89             | 3.99         | 20.60             | 34.90 | 44.50        | 35.70       |
| 28         | 46.71             | 3.99         | 20.60             | 39.70 | 50.80        | 35.70       |
| 32         | 53.39             | 3.99         | 22.20             | 44.50 | 57.00        | 37.30       |
| 36         | 59.59             | 3.99         | 22.20             | 49.20 | 63.50        | 37.30       |

## Rear mounting Receptacle


103



| SHELL SIZE | 'A'<br>+0.0<br>-0.15 | 'K'<br>+0.20 | 'M'<br>+0.41<br>-0.0 | 'R'<br>±0.20 | 'S'<br>±0.20 | 'L'<br>MAX. |
|------------|----------------------|--------------|----------------------|--------------|--------------|-------------|
| 10SL       | 18.21                | 2.79         | 18.20                | 18.20        | 25.40        | 27.60       |
| 12S        | 21.40                | 3.20         | 18.20                | 20.60        | 28.00        | 27.60       |
| 14S        | 24.61                | 3.20         | 18.20                | 23.00        | 30.00        | 27.60       |
| 16S        | 27.41                | 3.20         | 18.20                | 24.60        | 32.50        | 27.60       |
| 16         | 27.41                | 3.20         | 23.05                | 24.60        | 32.50        | 33.80       |
| 18         | 30.81                | 3.99         | 23.05                | 27.00        | 35.00        | 33.80       |
| 20         | 34.19                | 3.99         | 23.05                | 29.40        | 38.00        | 33.80       |
| 22         | 37.39                | 3.99         | 23.05                | 31.80        | 41.00        | 33.80       |
| 24         | 40.89                | 3.99         | 23.05                | 34.90        | 44.50        | 35.70       |
| 28         | 46.71                | 3.99         | 24.05                | 39.70        | 50.80        | 35.70       |
| 32         | 53.39                | 3.99         | 24.05                | 44.50        | 57.00        | 37.30       |
| 36         | 59.59                | 3.99         | 24.05                | 49.20        | 63.50        | 37.30       |

## Plug connector


106



| SHELL SIZE | 'A'<br>MAX. | 'L'<br>MAX | 'T'<br>- 2A THD |
|------------|-------------|------------|-----------------|
| 10SL       | 22.80       | 56.00      | 5/8"-24 UNEF    |
| 12S        | 25.60       | 56.00      | 5/8"-24 UNEF    |
| 14S        | 29.20       | 54.00      | 3/4"-24 UNEF    |
| 16S        | 32.00       | 56.00      | 7/8"-24 UNEF    |
| 16         | 32.00       | 67.00      | 7/8"-24 UNEF    |
| 18         | 36.50       | 74.00      | 1"-20 UNEF      |
| 20         | 39.90       | 75.00      | 1 1/8"-18 UNEF  |
| 22         | 43.10       | 78.00      | 1 1/4"-18 UNEF  |
| 24         | 46.60       | 78.00      | 1 3/8"-18 UNEF  |
| 28         | 53.40       | 82.00      | 1 5/8"-18 UNEF  |
| 32         | 60.10       | 82.00      | 1 7/8"-18 UN    |
| 36         | 66.30       | 90.00      | 2 1/16"-16 UN   |


## Jam Nut Receptacles

107




| SHELL SIZE | A<br>-2A THREADS | B<br>+0.0<br>-0.15 | C     | D<br>WALL THICKNESS |      | E    | F<br>+0.25 | H     | L     |
|------------|------------------|--------------------|-------|---------------------|------|------|------------|-------|-------|
|            |                  |                    |       | MIN                 | MAX  |      |            |       |       |
| 10SL       | 7/8" - 20 UNEF   | 18.20              | 24.50 | 2.40                | 5.20 | 4.00 | 31.80      | 27.00 | 27.70 |
| 14S        | 1" 1/8-18 UNEF   | 24.60              | 26.80 | 2.40                | 7.50 | 4.80 | 41.30      | 33.00 | 30.00 |
| 16S        | 1" 1/4-18 UNEF   | 27.40              | 26.80 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 30.00 |
| 16         | 1" 1/4- 18 UNEF  | 27.40              | 32.10 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 35.30 |
| 18         | 1" 3/8- 18 UNEF  | 30.80              | 33.70 | 2.40                | 9.00 | 4.80 | 47.60      | 39.70 | 37.70 |
| 20         | 1" 1/2- 18 UNEF  | 34.20              | 33.70 | 2.40                | 9.00 | 4.80 | 50.80      | 44.00 | 37.70 |
| 22         | 1" 5/8- 18 UNEF  | 37.40              | 33.70 | 2.40                | 9.10 | 4.80 | 54.20      | 46.00 | 37.70 |
| 24         | 1" 3/4- 18 UNS   | 40.90              | 33.70 | 2.40                | 9.10 | 4.80 | 57.20      | 50.80 | 37.70 |
| 28         | 2" - 18 UNS      | 46.70              | 35.20 | 2.40                | 8.50 | 5.60 | 63.50      | 55.00 | 35.20 |
| 32         | 2" 1/4- 16 UN    | 53.40              | 35.20 | 2.40                | 6.50 | 5.60 | 69.80      | 62.00 | 35.20 |
| 36         | 2" 1/2- 16 UN    | 59.60              | 35.20 | 2.40                | 8.30 | 5.60 | 76.20      | 71.00 | 35.20 |

## Box mount Receptacle with PC Tail contacts




| Shell Size | 'A'<br>+0.0 -0.15 | 'K'<br>±0.20 | 'M'<br>+0.41 - 0.0 | 'R'   | 'S'<br>±0.20 | 'L'<br>±0.20 |
|------------|-------------------|--------------|--------------------|-------|--------------|--------------|
| 10SL       | 18.21             | 2.79         | 14.20              | 18.20 | 25.40        | 24.70        |
| 12S        | 21.40             | 3.20         | 14.20              | 20.60 | 28.00        | 24.70        |
| 14S        | 24.61             | 3.20         | 14.20              | 23.00 | 30.00        | 24.70        |
| 16S        | 27.41             | 3.20         | 14.20              | 24.60 | 32.50        | 24.70        |
| 6          | 27.41             | 3.20         | 19.00              | 24.60 | 32.50        | 33.80        |
| 18         | 30.81             | 3.99         | 19.00              | 27.00 | 35.00        | 33.80        |
| 20         | 34.19             | 3.99         | 19.00              | 29.40 | 38.00        | 33.80        |
| 22         | 37.39             | 3.99         | 19.00              | 31.80 | 41.00        | 33.80        |
| 24         | 40.89             | 3.99         | 20.60              | 34.90 | 44.50        | 33.80        |
| 28         | 46.71             | 3.99         | 20.60              | 39.70 | 50.80        | 33.80        |
| 32         | 53.39             | 3.99         | 22.20              | 44.50 | 57.00        | 33.80        |
| 36         | 59.59             | 3.99         | 22.20              | 49.20 | 63.50        | 33.80        |
| 40         | 65.51             | 3.99         | 22.20              | 55.50 | 69.90        | 33.80        |

## Rear Mount Receptacle with PC Tail contacts



| Shell Size | 'A'<br>+0.0 -0.15 | 'K'<br>±0.20 | 'M'<br>+0.41 - 0.0 | 'R'   | 'S'<br>±0.20 | 'L'<br>±0.20 |
|------------|-------------------|--------------|--------------------|-------|--------------|--------------|
| 10SL       | 18.21             | 2.79         | 18.20              | 18.20 | 25.40        | 24.70        |
| 12S        | 21.40             | 3.20         | 18.20              | 20.60 | 28.00        | 24.70        |
| 14S        | 24.61             | 3.20         | 18.20              | 23.00 | 30.00        | 24.70        |
| 16S        | 27.41             | 3.20         | 18.20              | 24.60 | 32.50        | 24.70        |
| 6          | 27.41             | 3.20         | 23.05              | 24.60 | 32.50        | 33.80        |
| 18         | 30.81             | 3.99         | 23.05              | 27.00 | 35.00        | 33.80        |
| 20         | 34.19             | 3.99         | 23.05              | 29.40 | 38.00        | 33.80        |
| 22         | 37.39             | 3.99         | 23.05              | 31.80 | 41.00        | 33.80        |
| 24         | 40.89             | 3.99         | 23.05              | 34.90 | 44.50        | 33.80        |
| 28         | 46.71             | 3.99         | 24.05              | 39.70 | 50.80        | 33.80        |
| 32         | 53.39             | 3.99         | 24.05              | 44.50 | 57.00        | 33.80        |
| 36         | 59.59             | 3.99         | 24.05              | 49.20 | 63.50        | 33.80        |
| 40         | 65.51             | 3.99         | 24.05              | 55.50 | 69.90        | 33.80        |


## Jam Nut receptacles with PC Tail contacts



| Shell Size | 'A'<br>-2A Threads | 'B'<br>+0.00 - 0.15 | 'C'  | 'D'  | 'E'   | F     | G     | H     | L1    | L2    | L3    | L4    |
|------------|--------------------|---------------------|------|------|-------|-------|-------|-------|-------|-------|-------|-------|
| 10SL       | 7/8"-20UNEF        | 18.20               | 5.00 | 2.50 | 31.80 | 35.00 | 31.50 | 22.70 | 29.20 | 13.50 | 12.50 | 20.90 |
| 14S        | 1" 1/8-18UNEF      | 24.60               | 6.00 | 2.50 | 38.10 | 41.30 | 37.90 | 28.80 | 29.20 | 13.50 | 12.50 | 27.20 |
| 16S        | 1" 1/4-18UNEF      | 27.40               | 6.00 | 2.50 | 41.20 | 44.40 | 41.00 | 32.00 | 29.20 | 13.50 | 12.50 | 30.40 |
| 16         | 1" 1/4-18UNEF      | 27.40               | 6.00 | 2.50 | 41.20 | 44.40 | 41.00 | 32.00 | 37.70 | 13.50 | 21.00 | 30.40 |
| 18         | 1" 3/8-18UNEF      | 30.80               | 7.00 | 3.00 | 45.00 | 48.20 | 44.80 | 35.10 | 40.00 | 15.00 | 21.00 | 33.60 |
| 20         | 1" 1/2-18UNEF      | 34.20               | 7.00 | 3.00 | 49.20 | 52.40 | 49.00 | 38.20 | 40.00 | 15.00 | 21.00 | 36.80 |
| 22         | 1" 5/8-18UNEF      | 37.40               | 7.00 | 3.00 | 52.40 | 55.50 | 52.20 | 42.00 | 40.00 | 15.00 | 21.00 | 39.90 |
| 24         | 1" 3/4-18UNS       | 40.90               | 7.00 | 3.00 | 55.20 | 59.00 | 55.00 | 44.70 | 40.00 | 15.00 | 21.00 | 43.10 |
| 28         | 2"-18UNS           | 46.70               | 7.00 | 3.00 | 62.20 | 66.00 | 62.00 | 51.10 | 40.00 | 15.00 | 21.00 | 49.20 |
| 32         | 2" 1/4-16UN        | 53.40               | 7.00 | 3.00 | 68.20 | 72.00 | 68.00 | 57.40 | 40.00 | 15.00 | 21.00 | 55.70 |
| 36         | 2" 1/2-16UN        | 59.60               | 8.00 | 3.00 | 75.20 | 80.00 | 75.00 | 63.80 | 40.00 | 15.00 | 21.00 | 62.00 |
| 40         | 2" 3/4-16 UN       | 65.50               | 8.00 | 3.00 | 82.20 | 87.00 | 82.00 | 70.20 | 40.00 | 15.00 | 21.00 | 68.50 |

## Wall Mount Receptacle with A type Solid B/S


### 100A



| Shell Size | 'A'<br>+0.0 -0.15 | 'K'<br>±0.20 | 'M'<br>+0.41 - 0.0 | 'R'   | 'S'<br>±0.20 | 'L'<br>MAX | 'T'<br>THD    |
|------------|-------------------|--------------|--------------------|-------|--------------|------------|---------------|
| 10SL       | 18.21             | 2.79         | 14.20              | 18.20 | 25.40        | 45.00      | 5/8-24 UNEF   |
| 12S        | 21.40             | 3.20         | 14.20              | 20.60 | 28.00        | 45.00      | 5/8-24 UNEF   |
| 14S        | 24.61             | 3.20         | 14.20              | 23.00 | 30.00        | 48.00      | 3/4-20 UNEF   |
| 16S        | 27.41             | 3.20         | 14.20              | 24.60 | 32.50        | 48.00      | 7/8-20 UNEF   |
| 6          | 27.41             | 3.20         | 19.00              | 24.60 | 32.50        | 55.00      | 7/8-20 UNEF   |
| 18         | 30.81             | 3.99         | 19.00              | 27.00 | 35.00        | 60.00      | 1-20 UNEF     |
| 20         | 34.19             | 3.99         | 19.00              | 29.40 | 38.00        | 65.00      | 1 3/16-18UNEF |
| 22         | 37.39             | 3.99         | 19.00              | 31.80 | 41.00        | 65.00      | 1 3/16-18UNEF |
| 24         | 40.89             | 3.99         | 20.60              | 34.90 | 44.50        | 68.00      | 1 7/16-18UNEF |
| 28         | 46.71             | 3.99         | 20.60              | 39.70 | 50.80        | 68.00      | 1 7/16-18UNEF |
| 32         | 53.39             | 3.99         | 22.20              | 44.50 | 57.00        | 70.00      | 1 3/4-18UNS   |
| 36         | 59.59             | 3.99         | 22.20              | 49.20 | 63.50        | 70.00      | 2-18 UNS      |

## Wall Mount Receptacle with A type solid B/S & Environmental sealing Grommet


### 100AG



| Shell Size | 'A'<br>+0.0 -0.15 | 'K'<br>±0.20 | 'M'<br>+0.41 - 0.0 | 'R'   | 'S'<br>±0.20 | 'L'<br>MAX | 'T'<br>THD    |
|------------|-------------------|--------------|--------------------|-------|--------------|------------|---------------|
| 10SL       | 18.21             | 2.79         | 14.20              | 18.20 | 25.40        | 68.60      | 5/8-24 UNEF   |
| 12S        | 21.40             | 3.20         | 14.20              | 20.60 | 28.00        | 68.60      | 5/8-24 UNEF   |
| 14S        | 24.61             | 3.20         | 14.20              | 23.00 | 30.00        | 68.60      | 3/4-20 UNEF   |
| 16S        | 27.41             | 3.20         | 14.20              | 24.60 | 32.50        | 68.60      | 7/8-20 UNEF   |
| 6          | 27.41             | 3.20         | 19.00              | 24.60 | 32.50        | 75.00      | 7/8-20 UNEF   |
| 18         | 30.81             | 3.99         | 19.00              | 27.00 | 35.00        | 75.00      | 1-20 UNEF     |
| 20         | 34.19             | 3.99         | 19.00              | 29.40 | 38.00        | 75.00      | 1 3/16-18UNEF |
| 22         | 37.39             | 3.99         | 19.00              | 31.80 | 41.00        | 75.00      | 1 3/16-18UNEF |
| 24         | 40.89             | 3.99         | 20.60              | 34.90 | 44.50        | 77.00      | 1 7/16-18UNEF |
| 28         | 46.71             | 3.99         | 20.60              | 39.70 | 50.80        | 77.00      | 1 7/16-18UNEF |
| 32         | 53.39             | 3.99         | 22.20              | 44.50 | 57.00        | 80.00      | 1 3/4-18UNS   |
| 36         | 59.59             | 3.99         | 22.20              | 49.20 | 63.50        | 80.00      | 2-18 UNS      |

## Wall Mount Receptacle with F type Strain Relief B/S & Environmental sealing Grommet


### 100F



| SHELL SIZE | 'A'<br>+0.0 -0.15 | 'K'<br>±0.20 | 'M'<br>+0.41 -0.0 | 'R'   | 'S'<br>±0.20 | 'L'<br>MAX. |
|------------|-------------------|--------------|-------------------|-------|--------------|-------------|
| 10SL       | 18.21             | 2.79         | 14.20             | 18.20 | 25.40        | 60.00       |
| 12S        | 21.40             | 3.20         | 14.20             | 20.60 | 28.00        | 60.00       |
| 14S        | 24.61             | 3.20         | 14.20             | 23.00 | 30.00        | 61.00       |
| 16S        | 27.41             | 3.20         | 14.20             | 24.60 | 32.50        | 61.00       |
| 16         | 27.41             | 3.20         | 19.00             | 24.60 | 32.50        | 68.00       |
| 18         | 30.81             | 3.99         | 19.00             | 27.00 | 35.00        | 72.00       |
| 20         | 34.19             | 3.99         | 19.00             | 29.40 | 38.00        | 74.00       |
| 22         | 37.39             | 3.99         | 19.00             | 31.80 | 41.00        | 74.00       |
| 24         | 40.89             | 3.99         | 20.60             | 34.90 | 44.50        | 78.00       |
| 28         | 46.71             | 3.99         | 20.60             | 39.70 | 50.80        | 78.00       |
| 32         | 53.39             | 3.99         | 22.20             | 44.50 | 57.00        | 82.00       |
| 36         | 59.59             | 3.99         | 22.20             | 49.20 | 63.50        | 82.00       |

## Wall Mount Receptacle with R type B/S & Environmental sealing Grommet


### 100R



| SHELL SIZE | 'A'<br>+0.0 -0.15 | 'K'<br>±0.20 | 'M'<br>+0.41 -0.0 | 'R'   | 'S'<br>±0.20 | 'L'<br>MAX. |
|------------|-------------------|--------------|-------------------|-------|--------------|-------------|
| 10SL       | 18.21             | 2.79         | 14.20             | 18.20 | 25.40        | 47.00       |
| 12S        | 21.40             | 3.20         | 14.20             | 20.60 | 28.00        | 47.00       |
| 14S        | 24.61             | 3.20         | 14.20             | 23.00 | 30.00        | 47.00       |
| 16S        | 27.41             | 3.20         | 14.20             | 24.60 | 32.50        | 48.00       |
| 16         | 27.41             | 3.20         | 19.00             | 24.60 | 32.50        | 54.40       |
| 18         | 30.81             | 3.99         | 19.00             | 27.00 | 35.00        | 56.40       |
| 20         | 34.19             | 3.99         | 19.00             | 29.40 | 38.00        | 56.40       |
| 22         | 37.39             | 3.99         | 19.00             | 31.80 | 41.00        | 56.40       |
| 24         | 40.89             | 3.99         | 20.60             | 34.90 | 44.50        | 57.40       |
| 28         | 46.71             | 3.99         | 20.60             | 39.70 | 50.80        | 57.40       |
| 32         | 53.39             | 3.99         | 22.20             | 44.50 | 57.00        | 58.10       |
| 36         | 59.59             | 3.99         | 22.20             | 49.20 | 63.50        | 58.10       |

## Wall Mount Receptacle with G type B/S for heatshrinkable & Environmental sealing Grommet


### 100G



| SHELL SIZE | 'A'<br>+0.0<br>-0.15 | 'K'<br>+0.20 | 'M'<br>+0.41<br>-0.0 | 'R'   | 'S'<br>+0.20 | 'L'<br>MAX. |
|------------|----------------------|--------------|----------------------|-------|--------------|-------------|
| 10SL       | 18.21                | 2.79         | 14.20                | 18.20 | 25.40        | 52.50       |
| 12S        | 21.40                | 3.20         | 14.20                | 20.60 | 28.00        | 52.50       |
| 14S        | 24.61                | 3.20         | 14.20                | 23.00 | 30.00        | 54.40       |
| 16S        | 27.41                | 3.20         | 14.20                | 24.60 | 32.50        | 54.40       |
| 16         | 27.41                | 3.20         | 19.00                | 24.60 | 32.50        | 61.00       |
| 18         | 30.81                | 3.99         | 19.00                | 27.00 | 35.00        | 62.00       |
| 20         | 34.19                | 3.99         | 19.00                | 29.40 | 38.00        | 62.00       |
| 22         | 37.39                | 3.99         | 19.00                | 31.80 | 41.00        | 65.00       |
| 24         | 40.89                | 3.99         | 20.60                | 34.90 | 44.50        | 65.00       |
| 28         | 46.71                | 3.99         | 20.60                | 39.70 | 50.80        | 66.00       |
| 32         | 53.39                | 3.99         | 22.20                | 44.50 | 57.00        | 71.00       |
| 36         | 59.59                | 3.99         | 22.20                | 49.20 | 63.50        | 75.00       |

## Wall Mount Receptacle with PG threaded type B/S suitable for PG Glands


### 100PG



| Shell Size | 'A'<br>+0.0 - 0.15 | 'K'<br>±0.20 | 'M'<br>+0.41 - 0.0 | 'R'   | 'S'<br>±0.20 | 'L'<br>MAX | PG THD           |
|------------|--------------------|--------------|--------------------|-------|--------------|------------|------------------|
| 10SL       | 18.21              | 2.79         | 14.20              | 18.20 | 25.40        | 56.00      | 7, 9, 11         |
| 12s        | 21.40              | 3.20         | 14.20              | 20.60 | 28.00        | 56.00      | 7, 9, 11         |
| 14S        | 24.61              | 3.20         | 14.20              | 23.00 | 30.00        | 56.00      | 11, 13.5         |
| 16s        | 27.41              | 3.20         | 14.20              | 24.60 | 32.50        | 58.00      | 9, 11, 16        |
| 6          | 27.41              | 3.20         | 19.00              | 24.60 | 32.50        | 66.00      | 9, 11, 16        |
| 18         | 30.81              | 3.99         | 19.00              | 27.00 | 35.00        | 74.00      | 9, 11, 16, 21    |
| 20         | 34.19              | 3.99         | 19.00              | 29.40 | 38.00        | 74.00      | 11, 16, 21       |
| 22         | 37.39              | 3.99         | 19.00              | 31.80 | 41.00        | 77.00      | 13.5, 16, 21     |
| 24         | 40.89              | 3.99         | 20.60              | 34.90 | 44.50        | 77.00      | 13.5, 16, 21, 29 |
| 28         | 46.71              | 3.99         | 20.60              | 39.70 | 50.80        | 78.00      | 16, 21, 29       |
| 32         | 53.39              | 3.99         | 22.20              | 44.50 | 57.00        | 78.00      | 21, 29           |
| 36         | 59.59              | 3.99         | 22.20              | 49.20 | 63.50        | 90.00      | 21, 29, 36       |

## Wall Mount Receptacle with EGM B/S for shielded cable & PHM B/S Unshielded cable with sealing rubber bush


### 100EGM/PHM



| SHELL SIZE | 'A'<br>+0.0<br>-0.15 | 'K'<br>+0.20 | 'M'<br>+0.41<br>-0.0 | 'R'   | 'S'<br>+0.20 | 'L'<br>MAX. |
|------------|----------------------|--------------|----------------------|-------|--------------|-------------|
| 10SL       | 18.21                | 2.79         | 14.20                | 18.20 | 25.40        | 95.60       |
| 12S        | 21.40                | 3.20         | 14.20                | 20.60 | 28.00        | 95.60       |
| 14S        | 24.61                | 3.20         | 14.20                | 23.00 | 30.00        | 95.60       |
| 16S        | 27.41                | 3.20         | 14.20                | 24.60 | 32.50        | 95.60       |
| 16         | 27.41                | 3.20         | 19.00                | 24.60 | 32.50        | 102.00      |
| 18         | 30.81                | 3.99         | 19.00                | 27.00 | 35.00        | 102.00      |
| 20         | 34.19                | 3.99         | 19.00                | 29.40 | 38.00        | 102.00      |
| 22         | 37.39                | 3.99         | 19.00                | 31.80 | 41.00        | 102.00      |
| 24         | 40.89                | 3.99         | 20.60                | 34.90 | 44.50        | 104.00      |
| 28         | 46.71                | 3.99         | 20.60                | 39.70 | 50.80        | 104.00      |
| 32         | 53.39                | 3.99         | 22.20                | 44.50 | 57.00        | 106.00      |
| 36         | 59.59                | 3.99         | 22.20                | 49.20 | 63.50        | 106.00      |

## Wall Mount Receptacle with SQ type Shielded B/S & Environmental sealing Grommet & Heat shrinkable option


### 100SQ



| SHELL SIZE | 'A'<br>+0.0<br>-0.15 | 'K'<br>+0.20 | 'M'<br>+0.41<br>-0.0 | 'R'   | 'S'<br>+0.20 | 'L'<br>MAX. |
|------------|----------------------|--------------|----------------------|-------|--------------|-------------|
| 10SL       | 18.21                | 2.79         | 14.20                | 18.20 | 25.40        | 57.00       |
| 12S        | 21.40                | 3.20         | 14.20                | 20.60 | 28.00        | 57.00       |
| 14S        | 24.61                | 3.20         | 14.20                | 23.00 | 30.00        | 59.00       |
| 16S        | 27.41                | 3.20         | 14.20                | 24.60 | 32.50        | 59.00       |
| 16         | 27.41                | 3.20         | 19.00                | 24.60 | 32.50        | 66.00       |
| 18         | 30.81                | 3.99         | 19.00                | 27.00 | 35.00        | 66.00       |
| 20         | 34.19                | 3.99         | 19.00                | 29.40 | 38.00        | 66.00       |
| 22         | 37.39                | 3.99         | 19.00                | 31.80 | 41.00        | 66.00       |
| 24         | 40.89                | 3.99         | 20.60                | 34.90 | 44.50        | 68.00       |
| 28         | 46.71                | 3.99         | 20.60                | 39.70 | 50.80        | 68.00       |
| 32         | 53.39                | 3.99         | 22.20                | 44.50 | 57.00        | 70.00       |
| 36         | 59.59                | 3.99         | 22.20                | 49.20 | 63.50        | 70.00       |

## Wall Mount Receptacle with Metric threaded type B/S suitable for Metric Glands


### 100M



| Shell Size | 'A'<br>+0.0 -0.15 | 'K'<br>+0.20 | 'M'<br>+0.41 - 0.0 | 'R'   | 'S'<br>±0.20 | 'L'<br>MAX. | M<br>THD |
|------------|-------------------|--------------|--------------------|-------|--------------|-------------|----------|
| 10SL       | 18.21             | 2.79         | 14.20              | 18.20 | 25.40        | 56.00       | M12X1.5  |
| 14s        | 24.61             | 3.20         | 14.20              | 23.00 | 30.00        | 56.00       | M16X1.5  |
| 16s        | 27.41             | 3.20         | 14.20              | 24.60 | 32.50        | 58.00       | M16X1.5  |
| 6          | 27.41             | 3.20         | 19.00              | 24.60 | 32.50        | 66.00       | M16X1.5  |
| 18         | 30.81             | 3.99         | 19.00              | 27.00 | 35.00        | 74.00       | M20X1.5  |
| 20         | 34.19             | 3.99         | 19.00              | 29.40 | 38.00        | 74.00       | M25X1.5  |
| 22         | 37.39             | 3.99         | 19.00              | 31.80 | 41.00        | 77.00       | M25X1.5  |
| 24         | 40.89             | 3.99         | 20.60              | 34.90 | 44.50        | 77.00       | M32X1.5  |
| 28         | 46.71             | 3.99         | 20.60              | 39.70 | 50.80        | 78.00       | M32X1.5  |
| 32         | 53.39             | 3.99         | 22.20              | 44.50 | 57.00        | 78.00       | M36X1.5  |
| 36         | 59.59             | 3.99         | 22.20              | 49.20 | 63.50        | 90.00       | M40X1.5  |

## Wall Mount Receptacle with 90° B/S & Environmental sealing Grommet


### 100RT



| SHELL SIZE | 'A'<br>+0.0 -0.15 | 'K'<br>+0.20 | 'M'<br>+0.41 -0.0 | 'R'   | 'S'<br>+0.20 | 'L'<br>MAX. | 'P'<br>MAX. |
|------------|-------------------|--------------|-------------------|-------|--------------|-------------|-------------|
| 10SL       | 18.21             | 2.79         | 14.20             | 18.20 | 25.40        | 40.50       | 21.50       |
| 12S        | 21.40             | 3.20         | 14.20             | 20.60 | 28.00        | 40.50       | 21.50       |
| 14S        | 24.61             | 3.20         | 14.20             | 23.00 | 30.00        | 42.00       | 23.00       |
| 16S        | 27.41             | 3.20         | 14.20             | 24.60 | 32.50        | 45.00       | 24.60       |
| 16         | 27.41             | 3.20         | 19.00             | 24.60 | 32.50        | 52.00       | 24.60       |
| 18         | 30.81             | 3.99         | 19.00             | 27.00 | 35.00        | 53.00       | 27.00       |
| 20         | 34.19             | 3.99         | 19.00             | 29.40 | 38.00        | 58.00       | 29.00       |
| 22         | 37.39             | 3.99         | 19.00             | 31.80 | 41.00        | 58.00       | 31.00       |
| 24         | 40.89             | 3.99         | 20.60             | 34.90 | 44.50        | 63.00       | 34.00       |
| 28         | 46.71             | 3.99         | 20.60             | 39.70 | 50.80        | 63.00       | 36.00       |
| 32         | 53.39             | 3.99         | 22.20             | 44.50 | 57.00        | 69.00       | 44.00       |
| 36         | 59.59             | 3.99         | 22.20             | 49.20 | 63.50        | 72.30       | 46.00       |

## Cable connecting Receptacle with A type Solid B/S


### 101A



| Shell Size | 'A'<br>+0.0 -0.15 | 'K'<br>±0.20 | 'M'<br>+0.41 - 0.0 | 'Q'   | 'S'<br>±0.20 | 'L'<br>MAX. | 'T'<br>THD    |
|------------|-------------------|--------------|--------------------|-------|--------------|-------------|---------------|
| 10SL       | 18.21             | 2.79         | 14.20              | 20.60 | 25.00        | 45.00       | 5/8-24 UNEF   |
| 12s        | 21.40             | 3.20         | 14.20              | 23.60 | 27.60        | 45.00       | 5/8-24 UNEF   |
| 14s        | 24.61             | 3.20         | 14.20              | 25.40 | 29.60        | 48.00       | 3/4-20 UNEF   |
| 16s        | 27.41             | 3.20         | 14.20              | 28.60 | 32.10        | 48.00       | 7/8-20 UNEF   |
| 6          | 27.41             | 3.20         | 19.00              | 28.60 | 32.10        | 55.00       | 7/8-20 UNEF   |
| 18         | 30.81             | 3.99         | 19.00              | 31.70 | 34.60        | 60.00       | 1-20 UNEF     |
| 20         | 34.19             | 3.99         | 19.00              | 34.90 | 37.60        | 65.00       | 1 3/16-18UNEF |
| 22         | 37.39             | 3.99         | 19.00              | 31.80 | 40.90        | 65.00       | 1 3/16-18UNEF |
| 24         | 40.89             | 3.99         | 20.60              | 41.30 | 44.40        | 68.00       | 1 7/16-18UNEF |
| 28         | 46.71             | 3.99         | 20.60              | 47.60 | 50.70        | 68.00       | 1 7/16-18UNEF |
| 32         | 53.39             | 3.99         | 22.20              | 54.0  | 56.90        | 70.00       | 1 3/4-18UNS   |
| 36         | 59.59             | 3.99         | 22.20              | 60.60 | 63.40        | 70.00       | 2-18 UNS      |


## Cable connecting Receptacle with F type Strain Relief B/S & Environmental sealing Grommet

### 101F




| SHELL SIZE | 'A'<br>+0.0 -0.15 | 'K'<br>+0.20 | 'M'<br>+0.41 -0.0 | 'Q'   | 'S'<br>+0.20 | 'L'<br>MAX. |
|------------|-------------------|--------------|-------------------|-------|--------------|-------------|
| 10SL       | 18.21             | 2.79         | 14.20             | 20.60 | 25.0         | 60.00       |
| 12S        | 21.40             | 3.20         | 14.20             | 23.60 | 27.60        | 60.00       |
| 14S        | 24.61             | 3.20         | 14.20             | 25.40 | 29.60        | 61.00       |
| 16S        | 27.41             | 3.20         | 14.20             | 28.60 | 32.10        | 61.00       |
| 16         | 27.41             | 3.20         | 19.00             | 28.60 | 32.10        | 68.00       |
| 18         | 30.81             | 3.99         | 19.00             | 31.70 | 34.60        | 72.00       |
| 20         | 34.19             | 3.99         | 19.00             | 34.90 | 37.60        | 74.00       |
| 22         | 37.39             | 3.99         | 19.00             | 31.80 | 40.90        | 74.00       |
| 24         | 40.89             | 3.99         | 20.60             | 41.30 | 44.40        | 78.00       |
| 28         | 46.71             | 3.99         | 20.60             | 47.60 | 50.70        | 78.00       |
| 32         | 53.39             | 3.99         | 22.20             | 54.0  | 56.90        | 82.00       |
| 36         | 59.59             | 3.99         | 22.20             | 60.60 | 63.40        | 82.00       |

## Cable connecting Receptacle with R type B/S & Environmental sealing Grommet




| SHELL SIZE | 'A'<br>+0.0<br>-0.15 | 'K'<br>+0.20 | 'M'<br>+0.41<br>-0.0 | 'Q'<br>+0.20 | 'S'<br>+0.20 | 'L'<br>MAX. |
|------------|----------------------|--------------|----------------------|--------------|--------------|-------------|
| 10SL       | 18.21                | 2.79         | 14.20                | 20.60        | 25.00        | 47.00       |
| 12S        | 21.40                | 3.20         | 14.20                | 23.60        | 27.60        | 47.00       |
| 14S        | 24.61                | 3.20         | 14.20                | 25.40        | 29.60        | 47.00       |
| 16S        | 27.41                | 3.20         | 14.20                | 28.60        | 32.10        | 48.00       |
| 16         | 27.41                | 3.20         | 19.00                | 28.60        | 32.10        | 54.40       |
| 18         | 30.81                | 3.99         | 19.00                | 31.70        | 34.60        | 56.40       |
| 20         | 34.19                | 3.99         | 19.00                | 34.90        | 37.60        | 56.40       |
| 22         | 37.39                | 3.99         | 19.00                | 31.80        | 40.90        | 56.40       |
| 24         | 40.89                | 3.99         | 20.60                | 41.30        | 44.40        | 57.40       |
| 28         | 46.71                | 3.99         | 20.60                | 47.60        | 50.70        | 57.40       |
| 32         | 53.39                | 3.99         | 22.20                | 54.00        | 56.90        | 58.10       |
| 36         | 59.59                | 3.99         | 22.20                | 60.00        | 63.40        | 58.10       |

## Cable connecting Receptacle with G type B/S for heatshrinkable & Environmental sealing Grommet




| SHELL SIZE | 'A'<br>+0.0<br>-0.15 | 'K'<br>+0.20 | 'M'<br>+0.41<br>-0.0 | 'Q'<br>+0.20 | 'S'<br>+0.20 | 'L'<br>MAX. |
|------------|----------------------|--------------|----------------------|--------------|--------------|-------------|
| 10SL       | 18.21                | 2.79         | 14.20                | 20.60        | 25.40        | 52.50       |
| 12S        | 21.40                | 3.20         | 14.20                | 23.60        | 28.00        | 52.50       |
| 14S        | 24.61                | 3.20         | 14.20                | 25.40        | 30.00        | 54.40       |
| 16S        | 27.41                | 3.20         | 14.20                | 28.60        | 32.50        | 54.40       |
| 16         | 27.41                | 3.20         | 19.00                | 28.60        | 32.50        | 61.00       |
| 18         | 30.81                | 3.99         | 19.00                | 31.70        | 35.00        | 62.00       |
| 20         | 34.19                | 3.99         | 19.00                | 34.90        | 38.00        | 63.00       |
| 22         | 37.39                | 3.99         | 19.00                | 31.80        | 41.00        | 65.00       |
| 24         | 40.89                | 3.99         | 20.60                | 41.30        | 44.50        | 65.00       |
| 28         | 46.71                | 3.99         | 20.60                | 47.60        | 50.80        | 66.00       |
| 32         | 53.39                | 3.99         | 22.20                | 54.0         | 57.00        | 71.00       |
| 36         | 59.59                | 3.99         | 22.20                | 60.60        | 63.50        | 75.00       |

## Cable connecting Receptacle with A type Solid B/S & Environmental sealing Grommet



| Shell Size | 'A'<br>+0.0 -0.15 | 'K'<br>±0.20 | 'M'<br>+0.41 - 0.0 | 'Q'<br>+0.20 | 'S'<br>±0.20 | 'L'<br>MAX | 'T'<br>THD    |
|------------|-------------------|--------------|--------------------|--------------|--------------|------------|---------------|
| 10SL       | 18.21             | 2.79         | 14.20              | 20.60        | 25.40        | 68.60      | 5/8-24 UNEF   |
| 12s        | 21.40             | 3.20         | 14.20              | 23.60        | 28.00        | 68.60      | 5/8-24 UNEF   |
| 14s        | 24.61             | 3.20         | 14.20              | 25.40        | 30.00        | 68.60      | 3/4-20 UNEF   |
| 16s        | 27.41             | 3.20         | 14.20              | 28.60        | 32.50        | 68.60      | 7/8-20 UNEF   |
| 6          | 27.41             | 3.20         | 19.00              | 28.60        | 32.50        | 75.00      | 7/8-20 UNEF   |
| 18         | 30.81             | 3.99         | 19.00              | 31.70        | 35.00        | 75.00      | 1-20 UNEF     |
| 20         | 34.19             | 3.99         | 19.00              | 34.90        | 38.00        | 75.00      | 1 3/16-18UNEF |
| 22         | 37.39             | 3.99         | 19.00              | 31.80        | 41.00        | 75.00      | 1 3/16-18UNEF |
| 24         | 40.89             | 3.99         | 20.60              | 41.30        | 44.50        | 77.00      | 1 7/16-18UNEF |
| 28         | 46.71             | 3.99         | 20.60              | 47.60        | 50.80        | 77.00      | 1 7/16-18UNEF |
| 32         | 53.39             | 3.99         | 22.20              | 54.0         | 57.00        | 80.00      | 1 3/4-18UNS   |
| 36         | 59.59             | 3.99         | 22.20              | 60.60        | 63.50        | 80.00      | 2-18 UNS      |


## Cable connecting Receptacle with PG threaded type B/S suitable for PG Glands



| Shell Size | 'A'<br>+0.0 -0.15 | 'K'<br>±0.20 | 'M'<br>+0.41 - 0.0 | 'Q'<br>+0.20 | 'S'<br>±0.20 | 'L'<br>MAX | PG THD           |
|------------|-------------------|--------------|--------------------|--------------|--------------|------------|------------------|
| 10SL       | 18.21             | 2.79         | 14.20              | 20.60        | 25.40        | 56.00      | 7, 9, 11         |
| 12s        | 21.40             | 3.20         | 14.20              | 23.60        | 28.00        | 56.00      | 7, 9, 11         |
| 14s        | 24.61             | 3.20         | 14.20              | 25.40        | 30.00        | 56.00      | 11, 13.5         |
| 16s        | 27.41             | 3.20         | 14.20              | 28.60        | 32.50        | 58.00      | 9, 11, 16        |
| 6          | 27.41             | 3.20         | 19.00              | 28.60        | 32.50        | 66.00      | 9, 11, 16        |
| 18         | 30.81             | 3.99         | 19.00              | 31.70        | 35.00        | 74.00      | 9, 11, 16, 21    |
| 20         | 34.19             | 3.99         | 19.00              | 34.90        | 38.00        | 74.00      | 11, 16, 21       |
| 22         | 37.39             | 3.99         | 19.00              | 31.80        | 41.00        | 77.00      | 13.5, 16, 21     |
| 24         | 40.89             | 3.99         | 20.60              | 41.30        | 44.50        | 77.00      | 13.5, 16, 21, 29 |
| 28         | 46.71             | 3.99         | 20.60              | 47.60        | 50.80        | 78.00      | 16, 21, 29       |
| 32         | 53.39             | 3.99         | 22.20              | 54.0         | 57.00        | 78.00      | 21, 29           |
| 36         | 59.59             | 3.99         | 22.20              | 60.60        | 63.50        | 90.00      | 21, 29, 36       |

## Cable connecting Receptacle with EGM B/S for shielded cable & PHM B/S Unshielded cable with sealing rubber bush


### 101EGM/PHM



| SHELL SIZE | 'A' +0.0 -0.15 | 'K' +0.20 | 'M' +0.41 -0.0 | 'Q' +0.20 | 'S' +0.20 | 'L' MAX. |
|------------|----------------|-----------|----------------|-----------|-----------|----------|
| 10SL       | 18.21          | 2.79      | 14.20          | 20.60     | 25.40     | 95.60    |
| 12S        | 21.40          | 3.20      | 14.20          | 23.60     | 28.00     | 95.60    |
| 14S        | 24.61          | 3.20      | 14.20          | 25.40     | 30.00     | 95.60    |
| 16S        | 27.41          | 3.20      | 14.20          | 28.60     | 32.50     | 95.60    |
| 16         | 27.41          | 3.20      | 19.00          | 28.60     | 32.50     | 102.00   |
| 18         | 30.81          | 3.99      | 19.00          | 31.70     | 35.00     | 102.00   |
| 20         | 34.19          | 3.99      | 19.00          | 34.90     | 38.00     | 102.00   |
| 22         | 37.39          | 3.99      | 19.00          | 31.80     | 41.00     | 102.00   |
| 24         | 40.89          | 3.99      | 20.60          | 41.30     | 44.50     | 104.00   |
| 28         | 46.71          | 3.99      | 20.60          | 47.60     | 50.80     | 104.00   |
| 32         | 53.39          | 3.99      | 22.20          | 54.0      | 57.00     | 106.00   |
| 36         | 59.59          | 3.99      | 22.20          | 60.60     | 63.50     | 106.00   |

## Cable connecting Receptacle with SQ type Shielded B/S & Environmental sealing Grommet & Heat Shrinkable option


### 101SQ



| SHELL SIZE | 'A' +0.0 -0.15 | 'K' +0.20 | 'M' +0.41 -0.0 | 'Q' +0.20 | 'S' +0.20 | 'L' MAX. |
|------------|----------------|-----------|----------------|-----------|-----------|----------|
| 10SL       | 18.21          | 2.79      | 14.20          | 20.60     | 25.40     | 57.00    |
| 12S        | 21.40          | 3.20      | 14.20          | 23.60     | 28.00     | 57.00    |
| 14S        | 24.61          | 3.20      | 14.20          | 25.40     | 30.00     | 59.00    |
| 16S        | 27.41          | 3.20      | 14.20          | 28.60     | 32.50     | 59.00    |
| 16         | 27.41          | 3.20      | 19.00          | 28.60     | 32.50     | 66.00    |
| 18         | 30.81          | 3.99      | 19.00          | 31.70     | 35.00     | 66.00    |
| 20         | 34.19          | 3.99      | 19.00          | 34.90     | 38.00     | 66.00    |
| 22         | 37.39          | 3.99      | 19.00          | 31.80     | 41.00     | 66.00    |
| 24         | 40.89          | 3.99      | 20.60          | 41.30     | 44.50     | 68.00    |
| 28         | 46.71          | 3.99      | 20.60          | 47.60     | 50.80     | 68.00    |
| 32         | 53.39          | 3.99      | 22.20          | 54.0      | 57.00     | 70.00    |
| 36         | 59.59          | 3.99      | 22.20          | 60.60     | 63.50     | 70.00    |

## Cable connecting Receptacle with Metric threaded type B/S suitable for Metric Glands


### 101M



| Shell Size | 'A' +0.0 -0.15 | 'K' +0.20 | 'M' +0.41 - 0.0 | 'Q' +0.20 | 'S' +0.20 | 'L' MAX. | M THD   |
|------------|----------------|-----------|-----------------|-----------|-----------|----------|---------|
| 10SL       | 18.21          | 2.79      | 14.20           | 20.60     | 25.40     | 56.00    | M12X1.5 |
| 14s        | 24.61          | 3.20      | 14.20           | 25.40     | 30.00     | 56.00    | M16X1.5 |
| 16s        | 27.41          | 3.20      | 14.20           | 28.60     | 32.50     | 58.00    | M16X1.5 |
| 6          | 27.41          | 3.20      | 19.00           | 28.60     | 32.50     | 66.00    | M16X1.5 |
| 18         | 30.81          | 3.99      | 19.00           | 31.70     | 35.00     | 74.00    | M20X1.5 |
| 20         | 34.19          | 3.99      | 19.00           | 34.90     | 38.00     | 74.00    | M25X1.5 |
| 22         | 37.39          | 3.99      | 19.00           | 31.80     | 41.00     | 77.00    | M25X1.5 |
| 24         | 40.89          | 3.99      | 20.60           | 41.30     | 44.50     | 77.00    | M32X1.5 |
| 28         | 46.71          | 3.99      | 20.60           | 47.60     | 50.80     | 78.00    | M32X1.5 |
| 32         | 53.39          | 3.99      | 22.20           | 54.0      | 57.00     | 78.00    | M36X1.5 |
| 36         | 59.59          | 3.99      | 22.20           | 60.60     | 63.50     | 90.00    | M40X1.5 |

## Rear wall Mount Receptacle with A type Solid B/S


### 103A



| Shell Size | 'A' +0.0 -0.15 | 'K' +0.20 | 'M' +0.41 - 0.0 | 'R' +0.10 | 'S' +0.20 | 'T' THD       | 'L' MAX |
|------------|----------------|-----------|-----------------|-----------|-----------|---------------|---------|
| 10SL       | 18.21          | 2.79      | 18.20           | 18.20     | 25.40     | 5/8-24 UNEF   | 45.00   |
| 12s        | 21.40          | 3.20      | 18.20           | 20.60     | 28.00     | 5/8-24 UNEF   | 45.00   |
| 14s        | 24.61          | 3.20      | 18.20           | 23.00     | 30.00     | 3/4-20 UNEF   | 48.00   |
| 16s        | 27.41          | 3.20      | 18.20           | 24.60     | 32.50     | 7/8-20 UNEF   | 48.00   |
| 6          | 27.41          | 3.20      | 23.05           | 24.60     | 32.50     | 7/8-20 UNEF   | 55.00   |
| 18         | 30.81          | 3.99      | 23.05           | 27.00     | 35.00     | 1-20 UNEF     | 60.00   |
| 20         | 34.19          | 3.99      | 23.05           | 29.40     | 38.00     | 1 3/16-18UNEF | 65.00   |
| 22         | 37.39          | 3.99      | 23.05           | 31.80     | 41.00     | 1 3/16-18UNEF | 65.00   |
| 24         | 40.89          | 3.99      | 23.05           | 34.90     | 44.50     | 1 7/16-18UNEF | 68.00   |
| 28         | 46.71          | 3.99      | 24.05           | 39.70     | 50.80     | 1 7/16-18UNEF | 68.00   |
| 32         | 53.39          | 3.99      | 24.05           | 44.50     | 57.00     | 1 3/4-18UNS   | 70.00   |
| 36         | 59.59          | 3.99      | 24.05           | 49.20     | 63.50     | 2-18 UNS      | 70.00   |

## Rear wall Mount Receptacle with F type Strain Relief B/S & Environmental sealing Grommet


### 103F



| SHELL SIZE | 'A'<br>+0.0<br>-0.15 | 'K'<br>+0.20 | 'M'<br>+0.41<br>-0.0 | 'R'<br>+0.10 | 'S'<br>+0.20 | 'T'<br>THD.    | 'L'<br>MAX |
|------------|----------------------|--------------|----------------------|--------------|--------------|----------------|------------|
| 10SL       | 18.21                | 2.79         | 18.20                | 18.20        | 25.40        | 5/8-24 UNEF    | 60.00      |
| 12S        | 21.40                | 3.20         | 18.20                | 20.60        | 28.00        | 5/8 24 UNEF    | 60.00      |
| 14S        | 24.61                | 3.20         | 18.20                | 23.00        | 30.00        | 3/4-20 UNEF    | 61.00      |
| 16S        | 27.41                | 3.20         | 18.20                | 24.60        | 32.50        | 7/8-20 UNEF    | 61.00      |
| 16         | 27.41                | 3.20         | 23.05                | 24.60        | 32.50        | 7/8-20 UNEF    | 68.00      |
| 18         | 30.81                | 3.99         | 23.05                | 27.00        | 35.00        | 1-20 UNEF      | 72.00      |
| 20         | 34.19                | 3.99         | 23.05                | 29.40        | 38.00        | 1 3/16-18 UNEF | 74.00      |
| 22         | 37.39                | 3.99         | 23.05                | 31.80        | 41.00        | 1 3/16-18 UNEF | 74.00      |
| 24         | 40.89                | 3.99         | 23.05                | 34.90        | 44.50        | 1 7/16-18 UNEF | 78.00      |
| 28         | 46.71                | 3.99         | 24.05                | 39.70        | 50.80        | 1 7/16-18 UNEF | 78.00      |
| 32         | 53.39                | 3.99         | 24.05                | 44.50        | 57.00        | 1 3/4-18 UNS   | 82.00      |
| 36         | 59.59                | 3.99         | 24.05                | 49.20        | 63.50        | 2-18 UNS       | 82.00      |

## Rear wall Mount Receptacle with R type B/S & Environmental sealing Grommet


### 103R



| SHELL SIZE | 'A'<br>+0.0<br>-0.15 | 'K'<br>+0.20 | 'M'<br>+0.41<br>-0.0 | 'R'   | 'S'<br>+0.20 | 'L'<br>MAX. |
|------------|----------------------|--------------|----------------------|-------|--------------|-------------|
| 10SL       | 18.21                | 2.79         | 18.20                | 18.20 | 25.40        | 47.00       |
| 12S        | 21.40                | 3.20         | 18.20                | 20.60 | 28.00        | 47.00       |
| 14S        | 24.61                | 3.20         | 18.20                | 23.00 | 30.00        | 47.00       |
| 16S        | 27.41                | 3.20         | 18.20                | 24.60 | 32.50        | 48.00       |
| 16         | 27.41                | 3.20         | 23.05                | 24.60 | 32.50        | 54.40       |
| 18         | 30.81                | 3.99         | 23.05                | 27.00 | 35.00        | 56.40       |
| 20         | 34.19                | 3.99         | 23.05                | 29.40 | 38.00        | 56.40       |
| 22         | 37.39                | 3.99         | 23.05                | 31.80 | 41.00        | 56.40       |
| 24         | 40.89                | 3.99         | 23.05                | 34.90 | 44.50        | 57.40       |
| 28         | 46.71                | 3.99         | 24.05                | 39.70 | 50.80        | 57.40       |
| 32         | 53.39                | 3.99         | 24.05                | 44.50 | 57.00        | 58.10       |
| 36         | 59.59                | 3.99         | 24.05                | 49.20 | 63.50        | 58.10       |

## Rear wall Mount Receptacle with G type B/S for heatshrinkable & Environmental sealing Grommet


### 103G



| SHELL SIZE | 'A'<br>+0.0<br>-0.15 | 'K'<br>+0.20 | 'M'<br>+0.41<br>-0.0 | 'R'<br>+0.10 | 'S'<br>+0.20 | 'L'<br>MAX. |
|------------|----------------------|--------------|----------------------|--------------|--------------|-------------|
| 10SL       | 18.21                | 2.79         | 18.20                | 18.20        | 25.40        | 52.50       |
| 12S        | 21.40                | 3.20         | 18.20                | 20.60        | 28.00        | 52.50       |
| 14S        | 24.61                | 3.20         | 18.20                | 23.00        | 30.00        | 54.40       |
| 16S        | 27.41                | 3.20         | 18.20                | 24.60        | 32.50        | 54.40       |
| 16         | 27.41                | 3.20         | 23.05                | 24.60        | 32.50        | 61.00       |
| 18         | 30.81                | 3.99         | 23.05                | 27.00        | 35.00        | 62.00       |
| 20         | 34.19                | 3.99         | 23.05                | 29.40        | 38.00        | 63.00       |
| 22         | 37.39                | 3.99         | 23.05                | 31.80        | 41.00        | 65.00       |
| 24         | 40.89                | 3.99         | 23.05                | 34.90        | 44.50        | 65.00       |
| 28         | 46.71                | 3.99         | 24.05                | 39.70        | 50.80        | 66.00       |
| 32         | 53.39                | 3.99         | 24.05                | 44.50        | 57.00        | 71.00       |
| 36         | 59.59                | 3.99         | 24.05                | 49.20        | 63.50        | 75.00       |

## Rear wall Mount Receptacle with A type Solid B/S & Environmental sealing Grommet


### 103AG



| Shell Size | 'A'<br>+0.0 -0.15 | 'K'<br>±0.20 | 'M'<br>+0.41 - 0.0 | 'R'<br>+0.10 | 'S'<br>±0.20 | 'T'<br>THD    | 'L'<br>MAX |
|------------|-------------------|--------------|--------------------|--------------|--------------|---------------|------------|
| 10SL       | 18.21             | 2.79         | 18.20              | 18.20        | 25.40        | 5/8-24 UNEF   | 68.60      |
| 12s        | 21.40             | 3.20         | 18.20              | 20.60        | 28.00        | 5/8-24 UNEF   | 68.60      |
| 14s        | 24.61             | 3.20         | 18.20              | 23.00        | 30.00        | 3/4-20 UNEF   | 68.60      |
| 16s        | 27.41             | 3.20         | 18.20              | 24.60        | 32.50        | 7/8-20 UNEF   | 68.60      |
| 6          | 27.41             | 3.20         | 23.05              | 24.60        | 32.50        | 7/8-20 UNEF   | 75.00      |
| 18         | 30.81             | 3.99         | 23.05              | 27.00        | 35.00        | 1-20 UNEF     | 75.00      |
| 20         | 34.19             | 3.99         | 23.05              | 29.40        | 38.00        | 1 3/16-18UNEF | 75.00      |
| 22         | 37.39             | 3.99         | 23.05              | 31.80        | 41.00        | 1 3/16-18UNEF | 75.00      |
| 24         | 40.89             | 3.99         | 23.05              | 34.90        | 44.50        | 1 7/16-18UNEF | 77.00      |
| 28         | 46.71             | 3.99         | 24.05              | 39.70        | 50.80        | 1 7/16-18UNEF | 77.00      |
| 32         | 53.39             | 3.99         | 24.05              | 44.50        | 57.00        | 1 3/4-18UNS   | 80.00      |
| 36         | 59.59             | 3.99         | 24.05              | 49.20        | 63.50        | 2-18 UNS      | 80.00      |

## Rear wall Mount Receptacle with PG threaded type B/S suitable for PG Glands


### 103PG



| Shell Size | 'A'<br>+0.0 -0.15 | 'K'<br>±0.20 | 'M'<br>+0.41 -0.0 | 'R'<br>+0.10 | 'S'<br>±0.20 | 'L'<br>MAX | PG THD           |
|------------|-------------------|--------------|-------------------|--------------|--------------|------------|------------------|
| 10SL       | 18.21             | 2.79         | 18.20             | 18.20        | 25.40        | 56.00      | 7, 9, 11         |
| 12s        | 21.40             | 3.20         | 18.20             | 20.60        | 28.00        | 56.00      | 7, 9, 11         |
| 14s        | 24.61             | 3.20         | 18.20             | 23.00        | 30.00        | 56.00      | 11, 13.5         |
| 16s        | 27.41             | 3.20         | 18.20             | 24.60        | 32.50        | 58.00      | 9, 11, 16        |
| 6          | 27.41             | 3.20         | 23.05             | 24.60        | 32.50        | 66.00      | 9, 11, 16        |
| 18         | 30.81             | 3.99         | 23.05             | 27.00        | 35.00        | 74.00      | 9, 11, 16, 21    |
| 20         | 34.19             | 3.99         | 23.05             | 29.40        | 38.00        | 74.00      | 11, 16, 21       |
| 22         | 37.39             | 3.99         | 23.05             | 31.80        | 41.00        | 77.00      | 13.5, 16, 21     |
| 24         | 40.89             | 3.99         | 23.05             | 34.90        | 44.50        | 77.00      | 13.5, 16, 21, 29 |
| 28         | 46.71             | 3.99         | 24.05             | 39.70        | 50.80        | 78.00      | 16, 21, 29       |
| 32         | 53.39             | 3.99         | 24.05             | 44.50        | 57.00        | 78.00      | 21, 29           |
| 36         | 59.59             | 3.99         | 24.05             | 49.20        | 63.50        | 90.00      | 21, 29, 36       |

## Rear wall Mount Receptacle with EGM B/S for shielded cable & PHM B/S Unshielded cable with sealing rubber bush


### 103 EGM/PHM



| SHELL SIZE | 'A'<br>+0.0 -0.15 | 'K'<br>+0.20 | 'M'<br>+0.41 -0.0 | 'R'   | 'S'<br>+0.20 | 'L'<br>MAX. |
|------------|-------------------|--------------|-------------------|-------|--------------|-------------|
| 10SL       | 18.21             | 2.79         | 14.20             | 18.20 | 25.40        | 95.60       |
| 12S        | 21.40             | 3.20         | 14.20             | 20.60 | 28.00        | 95.60       |
| 14S        | 24.61             | 3.20         | 14.20             | 23.00 | 30.00        | 95.60       |
| 16S        | 27.41             | 3.20         | 14.20             | 24.60 | 32.50        | 95.60       |
| 16         | 27.41             | 3.20         | 19.00             | 24.60 | 32.50        | 102.00      |
| 18         | 30.81             | 3.99         | 19.00             | 27.00 | 35.00        | 102.00      |
| 20         | 34.19             | 3.99         | 19.00             | 29.40 | 38.00        | 102.00      |
| 22         | 37.39             | 3.99         | 19.00             | 31.80 | 41.00        | 102.00      |
| 24         | 40.89             | 3.99         | 20.60             | 34.90 | 44.50        | 104.00      |
| 28         | 46.71             | 3.99         | 20.60             | 39.70 | 50.80        | 104.00      |
| 32         | 53.39             | 3.99         | 22.20             | 44.50 | 57.00        | 106.00      |
| 36         | 59.59             | 3.99         | 22.20             | 49.20 | 63.50        | 106.00      |

## Rear wall Mount Receptacle with SQ type Shielded B/S & Environmental sealing Grommet & Heat Shrinkable Option


### 103SQ



| SHELL SIZE | 'A'<br>+0.0 -0.15 | 'K'<br>+0.20 | 'M'<br>+0.41 -0.0 | 'R'<br>+0.10 | 'S'<br>+0.20 | 'L'<br>MAX. |
|------------|-------------------|--------------|-------------------|--------------|--------------|-------------|
| 10SL       | 18.21             | 2.79         | 18.20             | 18.20        | 25.40        | 57.00       |
| 12S        | 21.40             | 3.20         | 18.20             | 20.60        | 28.00        | 57.00       |
| 14S        | 24.61             | 3.20         | 18.20             | 23.00        | 30.00        | 59.00       |
| 16S        | 27.41             | 3.20         | 18.20             | 24.60        | 32.50        | 59.00       |
| 16         | 27.41             | 3.20         | 23.05             | 24.60        | 32.50        | 66.00       |
| 18         | 30.81             | 3.99         | 23.05             | 27.00        | 35.00        | 66.00       |
| 20         | 34.19             | 3.99         | 23.05             | 29.40        | 38.00        | 66.00       |
| 22         | 37.39             | 3.99         | 23.05             | 31.80        | 41.00        | 66.00       |
| 24         | 40.89             | 3.99         | 23.05             | 34.90        | 44.50        | 68.00       |
| 28         | 46.71             | 3.99         | 24.05             | 39.70        | 50.80        | 68.00       |
| 32         | 53.39             | 3.99         | 24.05             | 44.50        | 57.00        | 70.00       |
| 36         | 59.59             | 3.99         | 24.05             | 49.20        | 63.50        | 70.00       |

## Rear wall Mount Receptacle with Metric threaded type B/S suitable for Metric Glands


### 103M



| Shell Size | 'A'<br>+0.0 -0.15 | 'K'<br>+0.20 | 'M'<br>+0.41 -0.0 | 'R'   | 'S'<br>±0.20 | 'L'<br>MAX. | M THD   |
|------------|-------------------|--------------|-------------------|-------|--------------|-------------|---------|
| 10SL       | 18.21             | 2.79         | 18.20             | 18.20 | 25.40        | 56.00       | M12X1.5 |
| 14s        | 24.61             | 3.20         | 18.20             | 23.00 | 30.00        | 56.00       | M16X1.5 |
| 16s        | 27.41             | 3.20         | 18.20             | 24.60 | 32.50        | 58.00       | M16X1.5 |
| 6          | 27.41             | 3.20         | 23.05             | 24.60 | 32.50        | 66.00       | M16X1.5 |
| 18         | 30.81             | 3.99         | 23.05             | 27.00 | 35.00        | 74.00       | M20X1.5 |
| 20         | 34.19             | 3.99         | 23.05             | 29.40 | 38.00        | 74.00       | M25X1.5 |
| 22         | 37.39             | 3.99         | 23.05             | 31.80 | 41.00        | 77.00       | M25X1.5 |
| 24         | 40.89             | 3.99         | 23.05             | 34.90 | 44.50        | 77.00       | M32X1.5 |
| 28         | 46.71             | 3.99         | 24.05             | 39.70 | 50.80        | 78.00       | M32X1.5 |
| 32         | 53.39             | 3.99         | 24.05             | 44.50 | 57.00        | 78.00       | M36X1.5 |
| 36         | 59.59             | 3.99         | 24.05             | 49.20 | 63.50        | 90.00       | M40X1.5 |

## Rear wall Mount Receptacle with 90° B/S & Environmental sealing Grommet


### 103RT



| SHELL SIZE | 'A' +0.0 -0.15 | 'K' +0.20 | 'M' +0.41 -0.0 | 'R'   | 'S' +0.20 | 'L' MAX. | 'P' MAX. |
|------------|----------------|-----------|----------------|-------|-----------|----------|----------|
| 10SL       | 18.21          | 2.79      | 14.20          | 18.20 | 25.40     | 40.50    | 21.50    |
| 12S        | 21.40          | 3.20      | 14.20          | 20.60 | 28.00     | 40.50    | 21.50    |
| 14S        | 24.61          | 3.20      | 14.20          | 23.00 | 30.00     | 42.00    | 23.00    |
| 16S        | 27.41          | 3.20      | 14.20          | 24.60 | 32.50     | 45.00    | 24.60    |
| 16         | 27.41          | 3.20      | 19.00          | 24.60 | 32.50     | 52.00    | 24.60    |
| 18         | 30.81          | 3.99      | 19.00          | 27.00 | 35.00     | 53.00    | 27.00    |
| 20         | 34.19          | 3.99      | 19.00          | 29.40 | 38.00     | 58.00    | 29.00    |
| 22         | 37.39          | 3.99      | 19.00          | 31.80 | 41.00     | 58.00    | 31.00    |
| 24         | 40.89          | 3.99      | 20.60          | 34.90 | 44.50     | 63.00    | 34.00    |
| 28         | 46.71          | 3.99      | 20.60          | 39.70 | 50.80     | 63.00    | 36.00    |
| 32         | 53.39          | 3.99      | 22.20          | 44.50 | 57.00     | 69.00    | 44.00    |
| 36         | 59.59          | 3.99      | 22.20          | 49.20 | 63.50     | 72.30    | 46.00    |

## Straight Plug with A type solid B/S


### 106A



| SHELL SIZE | 'A' MAX. | 'L' MAX. | 'T' THD        |
|------------|----------|----------|----------------|
| 10SL       | 22.80    | 44.00    | 5/8-24 UNEF    |
| 12S        | 25.60    | 44.00    | 5/8-24 UNEF    |
| 14S        | 29.20    | 46.00    | 3/4-20 UNEF    |
| 16S        | 32.00    | 46.00    | 7/8-20 UNEF    |
| 16         | 32.00    | 46.00    | 7/8-20 UNEF    |
| 18         | 36.50    | 55.00    | 1-20 UNEF      |
| 20         | 39.90    | 62.00    | 1 3/16-18 UNEF |
| 22         | 46.10    | 65.00    | 1 3/16-18 UNEF |
| 24         | 46.60    | 65.00    | 1 7/16-18 UNEF |
| 28         | 53.40    | 68.00    | 1 7/16-18 UNEF |
| 32         | 60.10    | 70.00    | 1 3/4-18 UNS   |
| 36         | 66.30    | 70.00    | 2-18 UNS       |

## Rear wall Mount Receptacle with SQ type Shielded B/S & Environmental sealing Grommet


### 106F



| SHELL SIZE | 'A' MAX. | 'L' MAX | 'T' THD.       |
|------------|----------|---------|----------------|
| 10SL       | 22.80    | 60.00   | 5/8-24 UNEF    |
| 12S        | 25.60    | 60.00   | 5/8-24 UNEF    |
| 14S        | 29.20    | 60.00   | 3/4-20 UNEF    |
| 16S        | 32.00    | 60.00   | 7/8-20 UNEF    |
| 16         | 32.00    | 68.00   | 7/8-20 UNEF    |
| 18         | 36.50    | 72.00   | 1-20 UNEF      |
| 20         | 39.90    | 74.00   | 1 3/16-18 UNEF |
| 22         | 43.10    | 74.00   | 1 3/16-18 UNEF |
| 24         | 46.60    | 78.00   | 1 7/16-18 UNEF |
| 28         | 53.40    | 78.00   | 1 7/16-18 UNEF |
| 32         | 60.10    | 82.00   | 1 3/4-18 UNS   |
| 36         | 66.30    | 82.00   | 2-18 UNS       |

## Straight Plug with R type B/S & Environmental sealing Grommet


### 106R



| SHELL SIZE | 'A' MAX. | 'L' MAX. |
|------------|----------|----------|
| 10SL       | 22.80    | 47.00    |
| 12S        | 25.60    | 47.00    |
| 14S        | 29.20    | 47.00    |
| 16S        | 32.00    | 47.00    |
| 16         | 32.00    | 55.40    |
| 18         | 36.50    | 57.40    |
| 20         | 39.90    | 57.40    |
| 22         | 43.10    | 57.40    |
| 24         | 46.60    | 57.40    |
| 28         | 53.40    | 57.40    |
| 32         | 60.10    | 58.10    |
| 36         | 66.30    | 58.10    |

## Straight Plug with G type B/S for Heat Shrinkable & Environmental sealing Grommet


### 106G



| SHELL SIZE | 'A' MAX | 'L' MAX |
|------------|---------|---------|
| 10SL       | 22.80   | 53.00   |
| 12S        | 25.60   | 53.00   |
| 14S        | 29.20   | 53.00   |
| 16S        | 32.00   | 53.00   |
| 16         | 32.00   | 61.00   |
| 18         | 36.50   | 62.00   |
| 20         | 39.90   | 63.00   |
| 22         | 43.10   | 65.00   |
| 24         | 46.60   | 65.00   |
| 28         | 53.40   | 68.00   |
| 32         | 60.10   | 71.00   |
| 36         | 66.30   | 75.00   |

## Straight Plug with A type Solid B/S & Environmental sealing Grommet


### 106AG



| SHELL SIZE | 'A' MAX. | 'L' MAX. | 'T' THD       |
|------------|----------|----------|---------------|
| 10SL       | 22.80    | 68.60    | 5/8-24 UNEF   |
| 12S        | 25.60    | 68.60    | 5/8-24 UNEF   |
| 14S        | 29.20    | 67.00    | 3/4-20 UNEF   |
| 16S        | 32.00    | 67.00    | 7/8-20 UNEF   |
| 16         | 32.00    | 76.00    | 7/8-20 UNEF   |
| 18         | 36.50    | 76.00    | 1-20 UNEF     |
| 20         | 39.90    | 76.00    | 1 3/16-18UNEF |
| 22         | 43.10    | 76.00    | 1 3/16-18UNEF |
| 24         | 46.60    | 78.00    | 1 7/16-18UNEF |
| 28         | 53.40    | 78.00    | 1 7/16-18UNEF |
| 32         | 60.10    | 80.00    | 1 3/4-18UNS   |
| 36         | 66.30    | 80.00    | 2-18 UNS      |


## Straight Plug with PG threaded type B/S suitable for PG Glands

### 106PG



| SHELL SIZE | 'A' MAX. | 'L' MAX | PG THD           |
|------------|----------|---------|------------------|
| 10SL       | 22.80    | 56.00   | 7, 9, 11         |
| 12S        | 25.60    | 56.00   | 7, 9, 11         |
| 14S        | 29.20    | 56.00   | 11, 13.5         |
| 16S        | 32.00    | 58.00   | 9, 11, 16        |
| 16         | 32.00    | 66.00   | 9, 11, 16        |
| 18         | 36.50    | 74.00   | 9, 11, 16, 21    |
| 20         | 39.90    | 74.00   | 11, 16, 21       |
| 22         | 43.10    | 77.00   | 13.5, 16, 21     |
| 24         | 46.60    | 77.00   | 13.5, 16, 21, 29 |
| 28         | 53.40    | 78.00   | 16, 21, 29       |
| 32         | 60.10    | 78.00   | 21, 29           |
| 36         | 66.30    | 90.00   | 21, 29, 36       |


### 106 EGM/PHM



| SHELL SIZE | 'A' MAX | 'L' MAX |
|------------|---------|---------|
| 10SL       | 22.80   | 53.00   |
| 12S        | 25.60   | 53.00   |
| 14S        | 29.20   | 53.00   |
| 16S        | 32.00   | 53.00   |
| 16         | 32.00   | 61.00   |
| 18         | 36.50   | 62.00   |
| 20         | 39.90   | 63.00   |
| 22         | 43.10   | 65.00   |
| 24         | 46.60   | 65.00   |
| 28         | 53.40   | 68.00   |
| 32         | 60.10   | 71.00   |
| 36         | 66.30   | 75.00   |

## Straight Plug with SQ type Shielded B/S & Environmental sealing Grommet & Heat Shrinkable option


### 106SQ



| SHELL SIZE | 'A' MAX. | 'L' MAX. |
|------------|----------|----------|
| 10SL       | 22.80    | 56.60    |
| 12S        | 25.60    | 56.60    |
| 14S        | 29.20    | 57.00    |
| 16S        | 32.00    | 57.00    |
| 16         | 32.00    | 66.00    |
| 18         | 36.50    | 66.00    |
| 20         | 39.90    | 66.00    |
| 22         | 43.10    | 66.00    |
| 24         | 46.60    | 68.00    |
| 28         | 53.40    | 66.00    |
| 32         | 60.10    | 70.00    |
| 36         | 66.30    | 70.00    |

## Straight Plug with Metric threaded type B/S suitable for Metric Glands


### 106M



| Shell Size | 'A' MAX. | 'L' MAX. | M THD   |
|------------|----------|----------|---------|
| 10SL       | 22.80    | 56.00    | M12X1.5 |
| 14s        | 29.20    | 56.00    | M16X1.5 |
| 16s        | 32.00    | 58.00    | M16X1.5 |
| 6          | 32.00    | 66.00    | M16X1.5 |
| 18         | 36.50    | 74.00    | M20X1.5 |
| 20         | 39.90    | 74.00    | M25X1.5 |
| 22         | 43.10    | 77.00    | M25X1.5 |
| 24         | 46.60    | 77.00    | M32X1.5 |
| 28         | 53.40    | 78.00    | M32X1.5 |
| 32         | 60.10    | 78.00    | M36X1.5 |
| 36         | 66.30    | 90.00    | M40X1.5 |

## Jam Nut Receptacle with A type Solid B/S


### 107TA



| SHELL SIZE | A<br>-2A THREADS | B<br>+0.0<br>-0.15 | C     | D<br>WALL THICKNESS |      | E    | F<br>+0.25 | H     | L     |
|------------|------------------|--------------------|-------|---------------------|------|------|------------|-------|-------|
|            |                  |                    |       | MIN                 | MAX  |      |            |       |       |
| 10SL       | 7/8" - 20 UNEF   | 18.20              | 24.50 | 2.40                | 5.20 | 4.00 | 31.80      | 27.00 | 52.00 |
| 14S        | 1" 1/8-18 UNEF   | 24.60              | 26.80 | 2.40                | 7.50 | 4.80 | 41.30      | 33.00 | 58.00 |
| 16S        | 1" 1/4-18 UNEF   | 27.40              | 26.80 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 58.00 |
| 16         | 1" 1/4-18 UNEF   | 27.40              | 32.10 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 68.00 |
| 18         | 1" 3/8- 18 UNEF  | 30..80             | 33.70 | 2.40                | 9.00 | 4.80 | 47.60      | 39.70 | 76.00 |
| 20         | 1" 1/2- 18 UNEF  | 34.20              | 33.70 | 2.40                | 9.00 | 4.80 | 50.80      | 44.00 | 80.00 |
| 22         | 1" 5/8- 18 UNEF  | 37.40              | 33.70 | 2.40                | 9.10 | 4.80 | 54.20      | 46.00 | 80.00 |
| 24         | 1" 3/4- 18 UNS   | 40.90              | 33.70 | 2.40                | 9.10 | 4.80 | 57.20      | 50.80 | 82.00 |
| 28         | 2" - 18 UNS      | 46.70              | 35.20 | 2.40                | 8.50 | 5.60 | 63.50      | 55.00 | 84.00 |
| 32         | 2" 1/4- 16 UN    | 53.40              | 35.20 | 2.40                | 6.50 | 5.60 | 69.80      | 62.00 | 85.00 |
| 36         | 2" 1/2- 16 UN    | 59.60              | 35.20 | 2.40                | 8.30 | 5.60 | 76.20      | 71.00 | 85.00 |

## Jam Nut Receptacle with F type Strain Relief B/S with Environmental sealing Grommet


### 107TF



| SHELL SIZE | A<br>-2A THREADS | B<br>+0.0<br>-0.15 | C     | D<br>WALL THICKNESS |      | E    | F<br>+0.25 | H     | L     |
|------------|------------------|--------------------|-------|---------------------|------|------|------------|-------|-------|
|            |                  |                    |       | MIN                 | MAX  |      |            |       |       |
| 10SL       | 7/8" - 20 UNEF   | 18.20              | 24.50 | 2.40                | 5.20 | 4.00 | 31.80      | 27.00 | 69.00 |
| 14S        | 1" 1/8-18 UNEF   | 24.60              | 26.80 | 2.40                | 7.50 | 4.80 | 41.30      | 33.00 | 72.00 |
| 16S        | 1" 1/4-18 UNEF   | 27.40              | 26.80 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 72.00 |
| 16         | 1" 1/4- 18 UNEF  | 27.40              | 32.10 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 83.00 |
| 18         | 1" 3/8- 18 UNEF  | 30..80             | 33.70 | 2.40                | 9.00 | 4.80 | 47.60      | 39.70 | 87.00 |
| 20         | 1" 1/2- 18 UNEF  | 34.20              | 33.70 | 2.40                | 9.00 | 4.80 | 50.80      | 44.00 | 89.00 |
| 22         | 1" 5/8- 18 UNEF  | 37.40              | 33.70 | 2.40                | 9.10 | 4.80 | 54.20      | 46.00 | 89.00 |
| 24         | 1" 3/4- 18 UNS   | 40.90              | 33.70 | 2.40                | 9.10 | 4.80 | 57.20      | 50.80 | 92.00 |
| 28         | 2" - 18 UNS      | 46.70              | 35.20 | 2.40                | 8.50 | 5.60 | 63.50      | 55.00 | 95.00 |
| 32         | 2" 1/4- 16 UN    | 53.40              | 35.20 | 2.40                | 6.50 | 5.60 | 69.80      | 62.00 | 97.00 |
| 36         | 2" 1/2- 16 UN    | 59.60              | 35.20 | 2.40                | 8.30 | 5.60 | 76.20      | 71.00 | 97.00 |

## Jam Nut Receptacle with R type B/S with Environmental sealing Grommet


### 107TR



| SHELL SIZE | A<br>-2A THREADS | B<br>+0.0<br>-0.15 | C     | D<br>WALL THICKNESS |      | E    | F<br>+0.25 | H     | L     |
|------------|------------------|--------------------|-------|---------------------|------|------|------------|-------|-------|
|            |                  |                    |       | MIN                 | MAX  |      |            |       |       |
| 10SL       | 7/8" - 20 UNEF   | 18.20              | 24.50 | 2.40                | 5.20 | 4.00 | 31.80      | 27.00 | 56.00 |
| 14S        | 1" 1/8-18 UNEF   | 24.60              | 26.80 | 2.40                | 7.50 | 4.80 | 41.30      | 33.00 | 59.00 |
| 16S        | 1" 1/4-18 UNEF   | 27.40              | 26.80 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 70.00 |
| 16         | 1" 1/4- 18 UNEF  | 27.40              | 32.10 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 72.00 |
| 18         | 1" 3/8- 18 UNEF  | 30..80             | 33.70 | 2.40                | 9.00 | 4.80 | 47.60      | 39.70 | 72.00 |
| 20         | 1" 1/2- 18 UNEF  | 34.20              | 33.70 | 2.40                | 9.00 | 4.80 | 50.80      | 44.00 | 72.00 |
| 22         | 1" 5/8- 18 UNEF  | 37.40              | 33.70 | 2.40                | 9.10 | 4.80 | 54.20      | 46.00 | 72.00 |
| 24         | 1" 3/4- 18 UNS   | 40.90              | 33.70 | 2.40                | 9.10 | 4.80 | 57.20      | 50.80 | 72.00 |
| 28         | 2" - 18 UNS      | 46.70              | 35.20 | 2.40                | 8.50 | 5.60 | 63.50      | 55.00 | 74.00 |
| 32         | 2" 1/4- 16 UN    | 53.40              | 35.20 | 2.40                | 6.50 | 5.60 | 69.80      | 62.00 | 74.00 |
| 36         | 2" 1/2- 16 UN    | 59.60              | 35.20 | 2.40                | 8.30 | 5.60 | 76.20      | 71.00 | 74.00 |

## Jam Nut Receptacle with G type B/S for Heat shrinkable & Environmental sealing Grommet


### 107G



| Shell Size | 'A'<br>-2A Threads | 'B'<br>+0.00 - 0.15 | 'C'   | D<br>Wall Thickness |      | E    | F<br>+0.25 | H     | L     |
|------------|--------------------|---------------------|-------|---------------------|------|------|------------|-------|-------|
|            |                    |                     |       | MIN.                | MAX. |      |            |       |       |
| 10SL       | 7/8"-20UNEF        | 18.20               | 24.50 | 2.40                | 5.20 | 4.00 | 31.80      | 27.00 | 61.00 |
| 14S        | 1" 1/8-18UNEF      | 24.60               | 26.80 | 2.40                | 7.50 | 4.80 | 41.30      | 33.00 | 66.00 |
| 16S        | 1" 1/4-18UNEF      | 27.40               | 26.80 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 66.00 |
| 16         | 1" 1/4-18UNEF      | 27.40               | 32.10 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 76.00 |
| 18         | 1" 3/8-18UNEF      | 30.80               | 33.70 | 2.40                | 9.00 | 4.80 | 47.60      | 39.70 | 78.00 |
| 20         | 1" 1/2-18UNEF      | 34.20               | 33.70 | 2.40                | 9.00 | 4.80 | 50.80      | 44.00 | 79.00 |
| 22         | 1" 5/8-18UNEF      | 37.40               | 33.70 | 2.40                | 9.10 | 4.80 | 54.20      | 46.00 | 81.00 |
| 24         | 1" 3/4-18UNS       | 40.90               | 33.70 | 2.40                | 9.10 | 4.80 | 57.20      | 50.80 | 79.00 |
| 28         | 2"-18UNS           | 46.70               | 35.20 | 2.40                | 8.50 | 5.60 | 63.50      | 55.00 | 82.00 |
| 32         | 2" 1/4-16UN        | 53.40               | 35.20 | 2.40                | 6.50 | 5.60 | 69.80      | 62.00 | 85.00 |
| 36         | 2" 1/2-16UN        | 59.60               | 35.20 | 2.40                | 8.30 | 5.60 | 76.20      | 71.00 | 90.00 |

## Jam Nut Receptacle with AG type B/S for heat shrinkable & Environmental sealing Grommet


### 107AG



| SHELL SIZE | A<br>-2A THREADS | B<br>+0.0<br>-0.15 | C     | D<br>WALL THICKNESS |      | E    | F<br>+0.25 | H     | L     |
|------------|------------------|--------------------|-------|---------------------|------|------|------------|-------|-------|
|            |                  |                    |       | MIN                 | MAX  |      |            |       |       |
| 10SL       | 7/8" - 20 UNEF   | 18.20              | 24.50 | 2.40                | 5.20 | 4.00 | 31.80      | 27.00 | 77.00 |
| 14S        | 1" 1/8-18 UNEF   | 24.60              | 26.80 | 2.40                | 7.50 | 4.80 | 41.30      | 33.00 | 80.00 |
| 16S        | 1" 1/4-18 UNEF   | 27.40              | 26.80 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 80.00 |
| 16         | 1" 1/4- 18 UNEF  | 27.40              | 32.10 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 90.00 |
| 18         | 1" 3/8- 18 UNEF  | 30..80             | 33.70 | 2.40                | 9.00 | 4.80 | 47.60      | 39.70 | 92.00 |
| 20         | 1" 1/2- 18 UNEF  | 34.20              | 33.70 | 2.40                | 9.00 | 4.80 | 50.80      | 44.00 | 92.00 |
| 22         | 1" 5/8- 18 UNEF  | 37.40              | 33.70 | 2.40                | 9.10 | 4.80 | 54.20      | 46.00 | 92.00 |
| 24         | 1" 3/4- 18 UNS   | 40.90              | 33.70 | 2.40                | 9.10 | 4.80 | 57.20      | 50.80 | 92.00 |
| 28         | 2" - 18 UNS      | 46.70              | 35.20 | 2.40                | 8.50 | 5.60 | 63.50      | 55.00 | 94.00 |
| 32         | 2" 1/4- 16 UN    | 53.40              | 35.20 | 2.40                | 6.50 | 5.60 | 69.80      | 62.00 | 94.00 |
| 36         | 2" 1/2- 16 UN    | 59.60              | 35.20 | 2.40                | 8.30 | 5.60 | 76.20      | 71.00 | 94.00 |

## Jam Nut Receptacle with PG threaded type B/S suitable for PG Glands


### 107TPG



| SHELL SIZE | A<br>-2A THREADS | B<br>+0.0<br>-0.15 | C     | D<br>WALL THICKNESS |      | E    | F<br>+0.25 | H     | L      | PG THD        |
|------------|------------------|--------------------|-------|---------------------|------|------|------------|-------|--------|---------------|
|            |                  |                    |       | MIN                 | MAX  |      |            |       |        |               |
| 10SL       | 7/8" - 20 UNEF   | 18.20              | 24.50 | 2.40                | 5.20 | 4.00 | 31.80      | 27.00 | 64.60  | 7, 9, 11      |
| 14S        | 1" 1/8-18 UNEF   | 24.60              | 26.80 | 2.40                | 7.50 | 4.80 | 41.30      | 33.00 | 68.00  | 11, 13.5      |
| 16S        | 1" 1/4-18 UNEF   | 27.40              | 26.80 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 70.00  | 9, 11, 16     |
| 16         | 1" 1/4- 18 UNEF  | 27.40              | 32.10 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 81.00  | 9, 11, 16     |
| 18         | 1" 3/8- 18 UNEF  | 30..80             | 33.70 | 2.40                | 9.00 | 4.80 | 47.60      | 39.70 | 89.00  | 9, 11, 16, 21 |
| 20         | 1" 1/2- 18 UNEF  | 34.20              | 33.70 | 2.40                | 9.00 | 4.80 | 50.80      | 44.00 | 90.00  | 11, 16, 21    |
| 22         | 1" 5/8- 18 UNEF  | 37.40              | 33.70 | 2.40                | 9.10 | 4.80 | 54.20      | 46.00 | 93.00  | 13.5, 16, 21  |
| 24         | 1" 3/4- 18 UNS   | 40.90              | 33.70 | 2.40                | 9.10 | 4.80 | 57.20      | 50.80 | 91.00  | 13.5, 16, 21  |
| 28         | 2" - 18 UNS      | 46.70              | 35.20 | 2.40                | 8.50 | 5.60 | 63.50      | 55.00 | 95.00  | 16, 21, 29    |
| 32         | 2" 1/4- 16 UN    | 53.40              | 35.20 | 2.40                | 6.50 | 5.60 | 69.80      | 62.00 | 94.00  | 21, 29        |
| 36         | 2" 1/2- 16 UN    | 59.60              | 35.20 | 2.40                | 8.30 | 5.60 | 76.20      | 71.00 | 105.00 | 21, 29, 36    |

## Jam Nut Receptacle with EGM B/S for shielded cable & PHM B/S Unshielded cable with sealing rubber bush


### 107TEGM/PHM



| SHELL SIZE | A<br>-2A THREADS | B<br>+0.0<br>-0.15 | C     | D<br>WALL THICKNESS |      | E    | F<br>+0.25 | H     | L      |
|------------|------------------|--------------------|-------|---------------------|------|------|------------|-------|--------|
|            |                  |                    |       | MIN                 | MAX  |      |            |       |        |
| 10SL       | 7/8" - 20 UNEF   | 18.20              | 24.50 | 2.40                | 5.20 | 4.00 | 31.80      | 27.00 | 104.20 |
| 14S        | 1" 1/8-18 UNEF   | 24.60              | 26.80 | 2.40                | 7.50 | 4.80 | 41.30      | 33.00 | 107.00 |
| 16S        | 1" 1/4-18 UNEF   | 27.40              | 26.80 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 107.00 |
| 16         | 1" 1/4- 18 UNEF  | 27.40              | 32.10 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 107.00 |
| 18         | 1" 3/8- 18 UNEF  | 30.80              | 33.70 | 2.40                | 9.00 | 4.80 | 47.60      | 39.70 | 118.00 |
| 20         | 1" 1/2- 18 UNEF  | 34.20              | 33.70 | 2.40                | 9.00 | 4.80 | 50.80      | 44.00 | 118.00 |
| 22         | 1" 5/8- 18 UNEF  | 37.40              | 33.70 | 2.40                | 9.10 | 4.80 | 54.20      | 46.00 | 118.00 |
| 24         | 1" 3/4- 18 UNS   | 40.90              | 33.70 | 2.40                | 9.10 | 4.80 | 57.20      | 50.80 | 118.00 |
| 28         | 2" - 18 UNS      | 46.70              | 35.20 | 2.40                | 8.50 | 5.60 | 63.50      | 55.00 | 120.00 |
| 32         | 2" 1/4- 16 UN    | 53.40              | 35.20 | 2.40                | 6.50 | 5.60 | 69.80      | 62.00 | 120.00 |
| 36         | 2" 1/2- 16 UN    | 59.60              | 35.20 | 2.40                | 8.30 | 5.60 | 76.20      | 71.00 | 120.00 |

## Jam Nut Receptacle with SQ type Shielded B/S & Environmental sealing Grommet & Heat Shrinkable Option


### 107TSQ



| SHELL SIZE | A<br>-2A THREADS | B<br>+0.0<br>-0.15 | C     | D<br>WALL THICKNESS |      | E    | F<br>+0.25 | H     | L     |
|------------|------------------|--------------------|-------|---------------------|------|------|------------|-------|-------|
|            |                  |                    |       | MIN                 | MAX  |      |            |       |       |
| 10SL       | 7/8" - 20 UNEF   | 18.20              | 24.50 | 2.40                | 5.20 | 4.00 | 31.80      | 27.00 | 66.00 |
| 14S        | 1" 1/8-18 UNEF   | 24.60              | 26.80 | 2.40                | 7.50 | 4.80 | 41.30      | 33.00 | 70.20 |
| 16S        | 1" 1/4-18 UNEF   | 27.40              | 26.80 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 70.20 |
| 16         | 1" 1/4- 18 UNEF  | 27.40              | 32.10 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 80.00 |
| 18         | 1" 3/8- 18 UNEF  | 30.80              | 33.70 | 2.40                | 9.00 | 4.80 | 47.60      | 39.70 | 81.00 |
| 20         | 1" 1/2- 18 UNEF  | 34.20              | 33.70 | 2.40                | 9.00 | 4.80 | 50.80      | 44.00 | 81.00 |
| 22         | 1" 5/8- 18 UNEF  | 37.40              | 33.70 | 2.40                | 9.10 | 4.80 | 54.20      | 46.00 | 82.00 |
| 24         | 1" 3/4- 18 UNS   | 40.90              | 33.70 | 2.40                | 9.10 | 4.80 | 57.20      | 50.80 | 82.00 |
| 28         | 2" - 18 UNS      | 46.70              | 35.20 | 2.40                | 8.50 | 5.60 | 63.50      | 55.00 | 84.00 |
| 32         | 2" 1/4- 16 UN    | 53.40              | 35.20 | 2.40                | 6.50 | 5.60 | 69.80      | 62.00 | 84.00 |
| 36         | 2" 1/2- 16 UN    | 59.60              | 35.20 | 2.40                | 8.30 | 5.60 | 76.20      | 71.00 | 84.00 |

## Jam Nut Receptacle with Metric threaded type B/S suitable for Metric Glands


### 107TM



| SHELL SIZE | A<br>-2A THREADS | B<br>+0.0<br>-0.15 | C     | D<br>WALL THICKNESS |      | E    | F<br>+0.25 | H     | L     | M<br>THD |
|------------|------------------|--------------------|-------|---------------------|------|------|------------|-------|-------|----------|
|            |                  |                    |       | MIN                 | MAX  |      |            |       |       |          |
| 10SL       | 7/8" - 20 UNEF   | 18.20              | 24.50 | 2.40                | 5.20 | 4.00 | 31.80      | 27.00 | 66.00 | M12X1.5  |
| 14S        | 1" 1/8-18 UNEF   | 24.60              | 26.80 | 2.40                | 7.50 | 4.80 | 41.30      | 33.00 | 70.20 | M16X1.5  |
| 16S        | 1" 1/4-18 UNEF   | 27.40              | 26.80 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 70.20 | M16X1.5  |
| 16         | 1" 1/4- 18 UNEF  | 27.40              | 32.10 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 80.00 | M16X1.5  |
| 18         | 1" 3/8- 18 UNEF  | 30.80              | 33.70 | 2.40                | 9.00 | 4.80 | 47.60      | 39.70 | 81.00 | M20X1.5  |
| 20         | 1" 1/2- 18 UNEF  | 34.20              | 33.70 | 2.40                | 9.00 | 4.80 | 50.80      | 44.00 | 81.00 | M25X1.5  |
| 22         | 1" 5/8- 18 UNEF  | 37.40              | 33.70 | 2.40                | 9.10 | 4.80 | 54.20      | 46.00 | 82.00 | M25X1.5  |
| 24         | 1" 3/4- 18 UNS   | 40.90              | 33.70 | 2.40                | 9.10 | 4.80 | 57.20      | 50.80 | 82.00 | M32X1.5  |
| 28         | 2" - 18 UNS      | 46.70              | 35.20 | 2.40                | 8.50 | 5.60 | 63.50      | 55.00 | 84.00 | M32X1.5  |
| 32         | 2" 1/4- 16 UN    | 53.40              | 35.20 | 2.40                | 6.50 | 5.60 | 69.80      | 62.00 | 84.00 | M36X1.5  |
| 36         | 2" 1/2- 16 UN    | 59.60              | 35.20 | 2.40                | 8.30 | 5.60 | 76.20      | 71.00 | 84.00 | M40X1.5  |

## Jam Nut Receptacle with 90° B/S & Environmental sealing Grommet


### 107TRT



| SHELL SIZE | A<br>-2A THREADS | B<br>+0.0<br>-0.15 | C     | D<br>WALL THICKNESS |      | E    | F<br>+0.25 | H     | L     | 'P'<br>MAX. |
|------------|------------------|--------------------|-------|---------------------|------|------|------------|-------|-------|-------------|
|            |                  |                    |       | MIN                 | MAX  |      |            |       |       |             |
| 10SL       | 7/8" - 20 UNEF   | 18.20              | 24.50 | 2.40                | 5.20 | 4.00 | 31.80      | 27.00 | 49.00 | 21.50       |
| 14S        | 1" 1/8-18 UNEF   | 24.60              | 26.80 | 2.40                | 7.50 | 4.80 | 41.30      | 33.00 | 54.00 | 23.00       |
| 16S        | 1" 1/4-18 UNEF   | 27.40              | 26.80 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 57.00 | 24.60       |
| 16         | 1" 1/4- 18 UNEF  | 27.40              | 32.10 | 2.40                | 7.50 | 4.80 | 44.40      | 38.10 | 66.00 | 24.60       |
| 18         | 1" 3/8- 18 UNEF  | 30.80              | 33.70 | 2.40                | 9.00 | 4.80 | 47.60      | 39.70 | 69.00 | 27.00       |
| 20         | 1" 1/2- 18 UNEF  | 34.20              | 33.70 | 2.40                | 9.00 | 4.80 | 50.80      | 44.00 | 75.00 | 29.00       |
| 22         | 1" 5/8- 18 UNEF  | 37.40              | 33.70 | 2.40                | 9.10 | 4.80 | 54.20      | 46.00 | 75.00 | 31.00       |
| 24         | 1" 3/4- 18 UNS   | 40.90              | 33.70 | 2.40                | 9.10 | 4.80 | 57.20      | 50.80 | 77.00 | 34.00       |
| 28         | 2" - 18 UNS      | 46.70              | 35.20 | 2.40                | 8.50 | 5.60 | 63.50      | 55.00 | 80.00 | 36.00       |
| 32         | 2" 1/4- 16 UN    | 53.40              | 35.20 | 2.40                | 6.50 | 5.60 | 69.80      | 62.00 | 84.00 | 44.00       |
| 36         | 2" 1/2- 16 UN    | 59.60              | 35.20 | 2.40                | 8.30 | 5.60 | 76.20      | 71.00 | 87.00 | 46.00       |

## 90° Plug Connector


108A=Supplied without grommet  
108R=Supplied with grommet



| SHELL SIZE | 'A' MAX. | 'L' MAX. | 'P' MAX. | 'T' THD        |
|------------|----------|----------|----------|----------------|
| 10SL       | 22.80    | 41.00    | 21.50    | 5/8-24 UNEF    |
| 12S        | 25.60    | 41.00    | 21.50    | 5/8-24 UNEF    |
| 14S        | 29.20    | 41.00    | 23.00    | 3/4-20 UNEF    |
| 16S        | 32.00    | 43.00    | 24.60    | 7/8-20 UNEF    |
| 16         | 32.00    | 53.00    | 24.60    | 7/8-20 UNEF    |
| 18         | 36.50    | 55.00    | 27.00    | 1-20 UNEF      |
| 20         | 39.90    | 60.00    | 29.00    | 1 3/16-18 UNEF |
| 22         | 43.10    | 60.00    | 31.00    | 1 3/16-18 UNEF |
| 24         | 46.60    | 64.00    | 34.00    | 1 7/16-18 UNEF |
| 28         | 53.40    | 64.00    | 36.00    | 1 7/16-18 UNEF |
| 32         | 60.10    | 70.00    | 44.00    | 1 3/4-18 UNS   |
| 36         | 66.30    | 74.00    | 46.00    | 2-18 UNS       |

## 90° Plug connector with G type B/S for Heat Shrinkable & Environmental sealing Grommet


### 108G



| SHELL SIZE | 'A' MAX | 'L' MAX | 'P' MAX |
|------------|---------|---------|---------|
| 10SL       | 22.80   | 41.00   | 46.00   |
| 12S        | 25.60   | 41.00   | 46.20   |
| 14S        | 29.20   | 41.00   | 50.00   |
| 16S        | 32.00   | 43.00   | 52.00   |
| 16         | 32.00   | 53.00   | 52.00   |
| 18         | 36.50   | 55.00   | 55.00   |
| 20         | 39.90   | 60.00   | 58.00   |
| 22         | 43.10   | 60.00   | 62.00   |
| 24         | 46.60   | 64.00   | 63.00   |
| 28         | 53.40   | 64.00   | 65.00   |
| 32         | 60.10   | 76.00   | 76.00   |

## 90° Plug connector with Strain Relief B/S & Environmental sealing Grommet


### 108E



| SHELL SIZE | 'A' MAX. | 'L' MAX. | 'P' MAX. |
|------------|----------|----------|----------|
| 10SL       | 22.80    | 41.00    | 38.00    |
| 12S        | 25.60    | 41.00    | 40.00    |
| 14S        | 29.20    | 43.00    | 41.00    |
| 16S        | 32.00    | 53.00    | 45.00    |
| 16         | 32.00    | 55.00    | 45.00    |
| 18         | 36.50    | 60.00    | 48.00    |
| 20         | 39.90    | 60.00    | 50.00    |
| 22         | 46.10    | 64.00    | 52.00    |
| 24         | 46.60    | 64.00    | 56.00    |
| 28         | 53.40    | 70.00    | 58.00    |
| 32         | 60.10    | 70.00    | 68.00    |
| 36         | 36.30    | 74.00    | 70.00    |


## 90° Plug connector with PG threaded type B/S suitable for PG Glands

### 108PG




| SHELL SIZE | 'A' MAX. | 'L' MAX. | 'P' MAX. | PG THD           |
|------------|----------|----------|----------|------------------|
| 10SL       | 22.80    | 41.00    | 50.00    | 7, 9, 11         |
| 12S        | 25.60    | 41.00    | 50.00    | 7, 9, 11         |
| 14S        | 29.20    | 41.00    | 52.00    | 11, 13.5         |
| 16S        | 32.00    | 43.00    | 55.00    | 9, 11, 16        |
| 16         | 32.00    | 53.00    | 57.00    | 9, 11, 16        |
| 18         | 36.50    | 55.00    | 67.00    | 9, 11, 16, 21    |
| 20         | 39.90    | 60.00    | 69.00    | 11, 16, 21       |
| 22         | 43.10    | 60.00    | 74.00    | 13.5, 16, 21     |
| 24         | 46.60    | 64.00    | 75.00    | 13.5, 16, 21, 29 |
| 28         | 53.40    | 64.00    | 78.00    | 16, 21, 29       |
| 32         | 60.10    | 70.00    | 85.00    | 21, 29           |
| 36         | 66.30    | 74.00    | 98.00    | 21, 29, 36       |

## 90° Plug connector with EGM B/S for shielded cable & PHM B/S Unshielded cable with sealing rubber bush 108EGM/PHM




| SHELL SIZE | 'A' MAX. | 'L' MAX. | 'P' MAX. |
|------------|----------|----------|----------|
| 10SL       | 22.80    | 41.00    | 91.00    |
| 12S        | 25.60    | 41.00    | 91.00    |
| 14S        | 29.20    | 41.00    | 91.00    |
| 16S        | 32.00    | 43.00    | 93.00    |
| 16         | 32.00    | 53.00    | 93.00    |
| 18         | 36.50    | 55.00    | 95.00    |
| 20         | 39.90    | 60.00    | 97.00    |
| 22         | 43.10    | 60.00    | 99.00    |
| 24         | 46.60    | 64.00    | 102.00   |
| 28         | 53.40    | 64.00    | 103.00   |
| 32         | 60.10    | 70.00    | 111.00   |
| 36         | 66.30    | 74.00    | 113.00   |

## 90° Plug connector with SQ type Shielded B/S & Environmental sealing Grommet & Heat Shrinkable Option 108SQ




| SHELL SIZE | 'A' MAX. | 'L' MAX. | 'P' MAX. |
|------------|----------|----------|----------|
| 10SL       | 22.80    | 41.00    | 49.00    |
| 12S        | 25.60    | 41.00    | 51.00    |
| 14S        | 29.20    | 41.00    | 55.00    |
| 16S        | 32.00    | 43.00    | 56.00    |
| 16         | 32.00    | 53.00    | 56.00    |
| 18         | 36.50    | 55.00    | 59.00    |
| 20         | 39.90    | 60.00    | 60.00    |
| 22         | 43.10    | 60.00    | 63.00    |
| 24         | 46.60    | 64.00    | 66.00    |
| 28         | 53.40    | 64.00    | 67.00    |
| 32         | 60.10    | 70.00    | 75.00    |
| 36         | 66.30    | 74.00    | 77.00    |

## 90° Plug connector with Metric threaded type B/S suitable for Metric Glands 108M



| Shell Size | 'A' MAX. | 'L' MAX. | 'P' MAX. | M THD   |
|------------|----------|----------|----------|---------|
| 10SL       | 22.80    | 41.00    | 49.50    | M12X1.5 |
| 14s        | 29.20    | 41.00    | 49.50    | M16X1.5 |
| 16s        | 32.00    | 43.00    | 49.50    | M16X1.5 |
| 6          | 32.00    | 53.00    | 52.00    | M16X1.5 |
| 18         | 36.50    | 55.00    | 63.00    | M20X1.5 |
| 20         | 39.90    | 60.00    | 65.00    | M25X1.5 |
| 22         | 43.10    | 60.00    | 67.00    | M25X1.5 |
| 24         | 46.60    | 64.00    | 73.00    | M32X1.5 |
| 28         | 53.40    | 64.00    | 75.00    | M32X1.5 |
| 32         | 60.10    | 70.00    | 85.00    | M36X1.5 |
| 36         | 66.30    | 74.00    | 98.00    | M40X1.5 |

## Panel mounting plug connector 97B - 3164 97B-4164




All dimensions are in mm

| Shell Size | d <sub>1</sub><br>Max | d <sub>2</sub><br>H13 | e<br>±0.1 | l <sub>1</sub><br>~ | l <sub>3</sub><br>±0.2 | l <sub>4</sub><br>±0.3 |
|------------|-----------------------|-----------------------|-----------|---------------------|------------------------|------------------------|
| 10SL       | 22.8                  | 3.2                   | 18.2      | 28.1                | 2.8                    | 25.4                   |
| 14S        | 29.2                  | 3.2                   | 23        | 28.1                | 3.2                    | 30                     |
| 16S        | 32                    | 3.2                   | 24.6      | 28.1                | 3.2                    | 32.5                   |
| 16         | 32                    | 3.2                   | 24.6      | 37.6                | 3.2                    | 32.5                   |
| 18         | 36.5                  | 3.2                   | 27        | 38.6                | 4                      | 35                     |
| 20         | 39.9                  | 3.2                   | 29.4      | 38.6                | 4                      | 38                     |
| 22         | 43.1                  | 3.2                   | 31.8      | 38.6                | 4                      | 41                     |
| 24         | 46.6                  | 3.7                   | 34.9      | 41                  | 4                      | 44.5                   |
| 28         | 53.4                  | 3.7                   | 39.7      | 41.8                | 4                      | 50.8                   |
| 32         | 60.1                  | 4.3                   | 44.5      | 45                  | 4                      | 57                     |
| 36         | 66.3                  | 4.3                   | 49.2      | 45                  | 4                      | 63.5                   |
| 40         | 72.5                  | 4.3                   | 55.5      | 45                  | 4                      | 69.9                   |

## Solid backshell without grommet and sleeve

### Class A




All dimensions are in mm

| Connector Size | A Thread in inches | L max for MS | L max for 97B | Q max | V Thread in inches |
|----------------|--------------------|--------------|---------------|-------|--------------------|
| 10SL           | 5/8-24 NEF         | 32.54        | 37.60         | 19.05 | 5/8-24 UNEF        |
| 12S            | 11/16-24 NEF       | 37.31        | ---           | 19.84 | 5/8-24 UNEF        |
| 12             | 11/16-24 NEF       | 46.83        | ---           | 19.84 | 5/8-24 UNEF        |
| 14S            | 3/4-20 UNEF        | 36.51        | 37.64         | 22.22 | 3/4-20 UNEF        |
| 14             | 3/4-20 UNEF        | 46.83        | ---           | 22.22 | 3/4-20 UNEF        |
| 16S            | 7/8-20 UNEF        | 37.70        | 38.83         | 25.40 | 7/8-20 UNEF        |
| 16             | 7/8-20 UNEF        | 48.02        | 48.00         | 25.40 | 7/8-20 UNEF        |
| 18             | 1-20 UNEF          | 50.80        | 51.58         | 28.57 | 1-20 UNEF          |
| 20             | 1 1/8-18 NS        | 53.97        | 54.75         | 31.75 | 1 3/16-18 UNEF     |
| 22             | 1 1/4-18 NEF       | 53.97        | 54.75         | 34.92 | 1 3/16-18 UNEF     |
| 24             | 1 3/8-18 NEF       | 57.15        | 57.94         | 38.10 | 1 7/16-18 UNEF     |
| 28             | 1 5/8-18 NEF       | 57.15        | 57.94         | 44.45 | 1 7/16-18 UNEF     |
| 32             | 1 7/8-16UN         | 59.0         | 59.78         | 51.75 | 1 3/4-18 UNS       |
| 36             | 2 1/16-16UN        | 60.32        | 61.13         | 57.15 | 2-18 UNS           |
| 40             | 2 5/16-16 UN       | 71.80        | 80.00         | 63.50 | 2 1/4 - 16 UN      |

## Solid Backshell With Grommet & Sleeve

### Class R




All dimensions are in mm

| Connector Size | A Thread class 2B in inches | For Plug type L max for MS | For Receptacle L max for 97B | Q max |
|----------------|-----------------------------|----------------------------|------------------------------|-------|
| 10SL           | 5/8-24 NEF                  | 47                         | 48                           | 21.50 |
| 12S            | 11/16-24 NEF                | 47                         | ---                          | 20.35 |
| 12             | 11/16-24 NEF                | 55                         | ---                          | 20.35 |
| 14S            | 3/4-20 UNEF                 | 47                         | 48                           | 23.40 |
| 14             | 3/4-20 UNEF                 | 55                         | ---                          | 23.40 |
| 16S            | 7/8-20 UNEF                 | 47                         | 48                           | 26.71 |
| 16             | 7/8-20 UNEF                 | 55                         | 56                           | 26.71 |
| 18             | 1-20 UNEF                   | 57                         | 57                           | 29.50 |
| 20             | 1 1/8-18 NS                 | 57                         | 57                           | 35.70 |
| 22             | 1 1/4-18 NEF                | 57                         | 57                           | 35.85 |
| 24             | 1 3/8-18 NEF                | 57                         | 57                           | 44.40 |
| 28             | 1 5/8-18 NEF                | 57                         | 57                           | 45.08 |
| 32             | 1 7/8-16UN                  | 58.25                      | 60                           | 52.36 |
| 36             | 2 1/16-16UN                 | 58.25                      | 60                           | 56.81 |
| 40             | 2 5/16-16 UN                | 58.25                      | 60                           | 64.50 |

Note - Both versions, straight and diamond knurling available on back accessories. For details, contact factory.

## Back Accessories


### Strain relief backshell with grommet and sleeve Class E and F



All dimensions are in mm

| Connector Size | A Thread class 2B in inches | L max for MS | L max for 97B | N max |
|----------------|-----------------------------|--------------|---------------|-------|
| 10SL           | 5/8-24 NEF                  | 54.07        | 59.10         | 21.97 |
| 12S            | 11/16-24 NEF                | 54.07        | ---           | 21.97 |
| 14S            | 3/4-20 UNEF                 | 55.90        | 61.34         | 25.15 |
| 16S            | 7/8-20 UNEF                 | 55.90        | 62.86         | 28.45 |
| 16             | 7/8-20 UNEF                 | 64.41        |               | 28.45 |
| 18             | 1-20 UNEF                   | 65.94        | 71.10         | 30.76 |
| 20             | 1 1/8-18 NS                 | 67.41        | 72.55         | 37.29 |
| 22             | 1 1/4-18 NEF                | 67.41        | 72.55         | 37.29 |
| 24             | 1 3/8-18 NEF                | 73.28        | 76.82         | 44.45 |
| 28             | 1 5/8-18 NEF                | 73.28        | 77.82         | 44.45 |
| 32             | 1 7/8-16UN                  | 74.75        |               | 52.22 |
| 36             | 2 1/16-16UN                 | 74.75        | 77.64         | 57.15 |
| 40             | 2 5/16-16 UN                | 86.0         | 125.0         | 67.10 |

### Right Angle Backshell With Or Without Grommet Class A, F & R




All dimensions are in mm

| Connector Size | A Thread class 2B in inches | L max for MS | L max for 97B | L1 max | Q max | V Thread in inches |
|----------------|-----------------------------|--------------|---------------|--------|-------|--------------------|
| 10SL           | 5/8-24 NEF                  | 37.60        | 45.00         | 25.00  | 22.22 | 5/8-24 UNEF        |
| 12S            | 11/16-24 NEF                | 37.80        | ---           | 25.00  | 25.40 | 5/8-24 UNEF        |
| 12             | 11/16-24 NEF                | 47.30        | ---           | 25.00  | 25.40 | 5/8-24 UNEF        |
| 14S            | 3/4-20 UNEF                 | 39.40        | 47.00         | 27.00  | 28.57 | 3/4-20 UNEF        |
| 14             | 3/4-20 UNEF                 | 48.90        | ---           | 27.00  | 28.57 | 3/4-20 UNEF        |
| 16S            | 7/8-20 UNEF                 | 42.60        | 48.00         | 28.00  | 31.75 | 7/8-20 UNEF        |
| 16             | 7/8-20 UNEF                 | 52.10        | 57.00         | 28.00  | 31.75 | 7/8-20 UNEF        |
| 18             | 1-20 UNEF                   | 53.70        | 58.00         | 31.00  | 34.13 | 1-20 UNEF          |
| 20             | 1 1/8-18 NS                 | 58.80        | 61.00         | 34.00  | 37.30 | 1 3/16-18 UNEF     |
| 22             | 1 1/4-18 NEF                | 58.80        | 61.00         | 34.00  | 40.48 | 1 3/16-18 UNEF     |
| 24             | 1 3/8-18 NEF                | 63.60        | 66.00         | 37.00  | 43.66 | 1 7/16-18 UNEF     |
| 28             | 1 5/8-18 NEF                | 63.60        | 66.00         | 39.00  | 50.00 | 1 7/16-18 UNEF     |
| 32             | 1 7/8-16UN                  | 69.60        | 72.00         | 45.00  | 56.50 | 1 3/4-18 UNS       |
| 36             | 2 1/16-16UN                 | 72.80        | 75.00         | 48.00  | 62.71 | 2-18 UNS           |
| 40             | 2 5/16-26 UN                | 76.00        | 78.00         | 55.00  | 62.71 | 2 1/4 -16 UN       |

Note - Both versions, straight and diamond knurling available on back accessories. For details, contact factory.

## Heat Shrink Boot adaptor (G)




| Shell size | A Min. | B     | L Max. | C- THD        |
|------------|--------|-------|--------|---------------|
| 10SL       | 7.70   | 20.30 | 30.00  | 5/8-24 NEF    |
| 12S        | 8.20   |       |        |               |
| 14S        | 10.60  | 22.30 | 27.00  | 3/4-20 UNEF   |
| 16S        | 13.50  | 24.80 | 29.50  | 7/8-20 UNEF   |
| 16         |        |       |        |               |
| 18         | 14.60  | 28.50 | 33.50  | 1-20 UNEF     |
| 20         | 18.70  | 34.50 |        | 1 1/8-18 NEF  |
| 22         | 20.80  | 35.10 | 35.70  | 1 1/4-18 UNEF |
| 24         | 24.60  | 41.00 | 34.00  | 1 3/8-18 NEF  |
| 28         | 27.00  | 44.80 | 34.10  | 1 5/8-18 NEF  |
| 32         | 33.30  | 51.50 | 34.20  | 1 7/8-16 UN   |
| 36         | 38.50  | 56.00 | 34.20  | 2 1/16-16 UN  |
| 40         | 48.20  | 62.00 | 36.60  | 2 5/16-16 UN  |

## Back Accessories

### Cable clamp

#### MS-3057


Use MS-3420 sleeves



All dimensions are in mm

| Part number | Shell size | Max OD of cable | A     | B     | C     | Thread in inches |
|-------------|------------|-----------------|-------|-------|-------|------------------|
| MS-3057-4A  | 10SL, 12S  | 5.59            | 20.90 | 21.39 | 7.94  | 5/8-24           |
| MS-3057-6A  | 14, 14S    | 7.92            | 21.59 | 25.27 | 11.11 | 3/4-20           |
| MS-3057-8A  | 16, 16S    | 11.10           | 23.37 | 28.45 | 14.29 | 7/8-20           |
| MS-3057-10A | 18         | 14.27           | 23.37 | 30.89 | 15.87 | 1-20             |
| MS-3057-12A | 20,22      | 15.87           | 23.07 | 35.03 | 19.50 | 1 3/16-18        |
| MS-3057-16A | 24,28      | 19.05           | 25.78 | 42.75 | 23.81 | 1 7/16-18        |
| MS-3057-20A | 32         | 23.80           | 28.00 | 51.00 | 31.70 | 1 3/4-18         |
| MS-3057-24A | 36         | 31.75           | 29.36 | 57.02 | 34.92 | 2-18             |


## PG Adaptor



| Shell size | G Thread in inches | PG 9 |    |    | PG 11 |    |    | PG 13 |    |    | PG 16 |    |    | PG 21 |    |    | PG 29 |    |    | PG 36 |    |    |
|------------|--------------------|------|----|----|-------|----|----|-------|----|----|-------|----|----|-------|----|----|-------|----|----|-------|----|----|
|            |                    | A    | B  | L  | A     | B  | L  | A     | B  | L  | A     | B  | L  | A     | B  | L  | A     | B  | L  | A     | B  | L  |
| 10SL       | 5/8-24             |      |    |    |       |    |    |       |    |    |       |    |    |       |    |    |       |    |    |       |    |    |
| 12S        | 11/16-24           |      |    |    |       |    |    |       |    |    |       |    |    |       |    |    |       |    |    |       |    |    |
| 14         | 3/4-20             |      |    |    | 23    | 23 | 30 | 23    | 23 | 30 |       |    |    |       |    |    |       |    |    |       |    |    |
| 16         | 7/8-20             |      |    |    | 25    | 25 | 30 |       |    |    | 25    | 25 | 30 |       |    |    |       |    |    |       |    |    |
| 18         | 1-20               | 30   | 21 | 26 | 30    | 26 | 37 |       |    |    | 30    | 28 | 37 |       |    |    |       |    |    |       |    |    |
| 20         | 1 1/8-18           |      |    |    | 35    | 26 | 40 |       |    |    | 35    | 28 | 40 | 35    | 35 | 40 |       |    |    |       |    |    |
| 22         | 1 1/4-18           |      |    |    |       |    |    |       |    |    | 35    | 28 | 40 | 35    | 35 | 40 |       |    |    |       |    |    |
| 24         | 1 3/8-18           |      |    |    |       |    |    |       |    |    |       |    |    | 38    | 35 | 40 | 40    | 40 | 40 |       |    |    |
| 28         | 1 5/8-18           |      |    |    |       |    |    |       |    |    |       |    |    | 45    | 37 | 45 | 45    | 45 | 45 |       |    |    |
| 36         | 2 1/8-18           |      |    |    |       |    |    |       |    |    |       |    |    |       |    |    | 57    | 44 | 55 | 57    | 57 | 55 |

Ordering Information  
MS - XX-PGY  
Where XX- Shell Size  
YY-PG-Thread Size

## EGM/PHM Backshell Accessories



| Shell size | G Thread in inches | EGM/PHM 11 |       | EGM/PHM 21 |       |
|------------|--------------------|------------|-------|------------|-------|
|            |                    | D          | L     | D          | L     |
| 10SL       | 5/8"-24            | 25.00      | 37.00 | 27.00      | 41.00 |
| 12SL       | 11/16"-24          | 25.00      | 37.00 | 27.00      | 41.00 |
| 14         | 3/4"-20            | 25.00      | 37.00 | 27.00      | 41.00 |
| 16         | 7/8"-20            | 25.00      | 40.00 | 27.00      | 43.00 |
| 18         | 1"-20              | 29.00      | 40.00 | 31.00      | 43.00 |
| 20         | 1.1/8"-18          | 31.50      | 52.00 | 33.50      | 55.00 |
| 22         | 1.1/4"-18          | 35.00      | 60.00 | 35.00      | 60.00 |
| 24         | 1.3/8"-18          | 35.00      | 60.00 | 35.00      | 60.00 |
| 32         | 1.29/32"-18        | 52.00      | 70.00 | 52.00      | 70.00 |
| 36         | 2.1/6"-18          | 52.00      | 70.00 | 52.00      | 70.00 |


Note:- Rubber Bush supplied in Packing  
In case of PHM inner metal Furrele is not required/supplied

EGM/PHM11 Can accept cable Min. 5.70 mm & Max. 10.85 mm  
EGM/PHM21 Can accept cable Min. 12.70 mm & Max. 17.85 mm

## Neoprene Sleeve

### MS-3420

Rubber bushing. Protects wire bundles and unjacketed cables from possible damage by cable clamp.




All dimensions are in mm

| Part number | A     | B     | C     | D     | E Rad<br>in inches | F Rad<br>in inches |
|-------------|-------|-------|-------|-------|--------------------|--------------------|
| MS-3420-3   | 3.30  | 5.33  | 9.50  | 73.02 | 0.79               | 0.79               |
| MS-3420-4   | 5.59  | 7.67  | 12.70 | 69.85 | 0.79               | 0.79               |
| MS-3420-6   | 7.92  | 10.84 | 15.59 | 66.67 | 0.79               | 1.59               |
| MS-3420-8   | 11.10 | 14.02 | 18.77 | 63.50 | 1.59               | 1.59               |
| MS-3420-10  | 14.27 | 15.62 | 21.94 | 60.32 | 1.59               | 1.59               |
| MS-3420-12  | 15.87 | 18.80 | 26.23 | 56.20 | 1.59               | 1.59               |
| MS-3420-16  | 19.05 | 23.54 | 26.39 | 53.97 | 1.59               | 1.59               |
| MS-3420-20  | 23.80 | 31.50 | 40.41 | 50.80 | 1.59               | 1.59               |
| MS-3420-24  | 31.75 | 34.67 | 46.79 | 47.62 | 1.59               | 1.59               |

## Plain Flat Gasket


For MS and 97B flange mounted receptacles



All dimensions are in mm

| Part number | Shell size | A max | B     | C     | D    | T   |
|-------------|------------|-------|-------|-------|------|-----|
| MS-101000   | 10SL       | 18.26 | 15.90 | 25.40 | 4.35 | 1.5 |
| MS-108686   | 12S & 12   | 20.62 | 19.05 | 27.80 | 4.35 | 1.5 |
| MS-101001   | 14S & 14   | 23.01 | 22.20 | 30.15 | 4.35 | 1.5 |
| MS-101002   | 16S & 16   | 24.61 | 25.40 | 32.50 | 4.35 | 1.5 |
| MS-101003   | 18         | 27.00 | 28.57 | 34.90 | 5.15 | 1.5 |
| MS-101004   | 20         | 29.36 | 31.75 | 38.10 | 5.15 | 1.5 |
| MS-101005   | 22         | 31.75 | 34.90 | 41.20 | 5.15 | 1.5 |
| MS-108687   | 24         | 34.90 | 38.10 | 44.45 | 5.15 | 1.5 |
| MS-101006   | 28         | 39.70 | 44.45 | 50.80 | 5.15 | 1.5 |
| MS-108688   | 32         | 44.45 | 50.80 | 57.15 | 5.55 | 1.5 |
| MS-101007   | 36         | 49.22 | 55.57 | 63.50 | 5.55 | 1.5 |
| MS-110831   | 40         | 55.77 | 61.92 | 69.85 | 5.55 | 1.5 |


### 97B-25042 For Plugs



All dimensions are in mm

| SHELL SIZE | 'A' MAX. | 'B' MAX. | 'D' + 0.60/-0 | 'E' MIN. |
|------------|----------|----------|---------------|----------|
| 10 SL      | 21.0     | 23.50    | 4.30          | 90.0     |
| 14 S       | 27.50    |          |               | 100.0    |
| 16 S       | 30.0     |          |               | 115.0    |
| 16         | 30.0     | 31.50    | 4.70          | 130.0    |
| 18         | 33.50    |          |               | 130.0    |
| 20         | 37.0     |          |               | 130.0    |
| 22         | 40.0     |          |               | 130.0    |
| 24         | 43.0     |          | 5.50          | 190.0    |
| 28         | 49.50    |          |               | 190.0    |
| 32         | 56.0     |          |               | 190.0    |
| 36         | 62.50    |          |               | 190.0    |
| 40         | 73.0     |          |               | 190.0    |

### Protective cap For 97B series 97B-25043 For Receptacle




All dimensions are in mm

| SHELL SIZE | 'A' MAX. | 'B' ± 0.20 | 'D' + 0.60/-0 | 'E' MIN. |
|------------|----------|------------|---------------|----------|
| 10 SL      | 23.0     | 16.0       | 4.30          | 90.0     |
| 14 S       | 30.0     |            |               | 100.0    |
| 16 S       | 32.50    |            |               | 115.0    |
| 16         | 32.50    | 20.70      | 4.30          | 100.0    |
| 18         | 37.0     |            |               | 115.0    |
| 20         | 40.50    |            |               | 115.0    |
| 22         | 43.50    |            |               | 115.0    |
| 24         | 47.0     |            | 5.50          | 160.0    |
| 28         | 54.0     |            |               | 160.0    |
| 32         | 60.50    |            |               | 160.0    |
| 36         | 67.0     |            |               | 160.0    |
| 40         | 73.0     |            |               | 160.0    |

Note :- Please add 07 suffix for bigger end link. Applicable for Jam Nut


## Pin - Male Crimp Contact




| CONTACT PART NO | CONTACT SIZE | 'A'  | 'B'   | 'C'   | 'D'   | 'L'   |
|-----------------|--------------|------|-------|-------|-------|-------|
| 97B - 106433    | 16S          | 1.59 | 3.10  | 1.72  | 2.60  | 26.00 |
| 97B - 108295    | 16           | 1.59 | 3.10  | 1.72  | 2.60  | 30.50 |
| 97B - 109388    | 12           | 2.39 | 4.78  | 2.51  | 3.96  | 36.60 |
| 97B - 108386    | 8            | 3.60 | 7.85  | 4.57  | 6.75  | 40.70 |
| 97B - 108384    | 4            | 5.70 | 11.10 | 7.15  | 9.50  | 40.70 |
| 97B - 112067    | 0            | 9.05 | 15.00 | 11.90 | 13.90 | 44.45 |

## Socket - Female Crimp Contact


Contact Size 12, 16, 16S




Contact Size 8



Contact Size 4




Contact Size 0




| CONTACT PART NO | CONTACT SIZE | 'B'   | 'C'   | 'D'   | 'L'   |
|-----------------|--------------|-------|-------|-------|-------|
| 97B - 108456    | 16S          | 3.10  | 1.72  | 2.60  | 26.30 |
| 97B - 108457    | 16           | 3.10  | 1.72  | 2.60  | 34.20 |
| 97B - 110262    | 12           | 4.78  | 2.51  | 3.96  | 37.00 |
| 97B - 108387    | 8            | 7.85  | 4.57  | 6.75  | 37.00 |
| 97B - 111878    | 4            | 11.10 | 7.15  | 9.50  | 40.00 |
| 97B - 112068    | 0            | 15.00 | 11.90 | 13.90 | 44.45 |

## Dummy Receptacle Rear Side Closed



| SHELL<br>SIZE | oD<br>+0.0<br>-0.13 | 'K'<br>+0.38<br>-0.0 | 'M'<br>+0.18 | Q<br>+0.10<br>-0.0 | Q1 | R<br>+0.18<br>0.20 | S<br>+0.13 | T<br>+0.23<br>-0.25 |
|---------------|---------------------|----------------------|--------------|--------------------|----|--------------------|------------|---------------------|
| 10SL          | 18.19               | 14.20                | 2.79         | 3.23               | M4 | 25.40              | 18.21      | 33.32               |
| 12S           | 21.30               |                      | 3.20         |                    |    | 28.05              | 20.60      | 36.20               |
| 14S           | 24.59               |                      |              |                    |    | 30.0               | 23.01      | 39.67               |
| 16S           | 27.38               |                      |              |                    |    | 32.51              | 24.61      | 42.87               |
| 16            | 27.38               | 19.0                 | 3.99         | 3.73               | M5 | 35.05              | 27.0       | 46.02               |
| 18            | 30.78               |                      |              |                    |    | 38.0               | 29.39      | 50.80               |
| 20            | 34.16               |                      |              |                    |    | 40.99              | 31.80      | 53.98               |
| 22            | 37.36               |                      |              |                    |    | 44.45              | 34.90      | 60.32               |
| 24            | 40.87               | 20.60                | 4.32         | 4.32               | M5 | 50.80              | 39.70      | 66.68               |
| 28            | 46.68               |                      |              |                    |    | 57.10              | 44.50      | 76.20               |
| 32            | 53.36               |                      |              |                    |    | 63.50              | 49.20      | 84.12               |
| 36            | 59.56               | 22.20                |              |                    |    |                    |            |                     |

## Dummy Receptacle Rear Side Open (Hollow)



| SHELL<br>SIZE | oD<br>+0.0<br>-0.13 | 'K'<br>+0.38<br>-0.0 | 'M'<br>+0.18 | Q<br>+0.10<br>-0.0 | Q1   | R<br>+0.18<br>0.20 | S<br>+0.13 | T<br>+0.23<br>-0.25 |
|---------------|---------------------|----------------------|--------------|--------------------|------|--------------------|------------|---------------------|
| 10SL          | 18.19               | 14.20                | 2.79         | 3.23               | M4   | 25.40              | 18.21      | 33.32               |
| 12S           | 21.30               |                      | 3.20         |                    |      | 28.05              | 20.60      | 36.20               |
| 14S           | 24.59               |                      |              |                    |      | 30.0               | 23.01      | 39.67               |
| 16S           | 27.38               |                      |              |                    |      | 32.51              | 24.61      | 42.87               |
| 16            | 30.78               | 19.0                 |              | 3.99               | 3.73 | M5                 | 35.05      | 27.0                |
| 18            | 30.78               |                      | 38.0         |                    |      |                    | 29.39      | 50.80               |
| 20            | 34.16               |                      | 40.99        |                    |      |                    | 31.80      | 53.98               |
| 22            | 37.36               |                      | 44.45        |                    |      |                    | 34.90      | 60.32               |
| 24            | 40.87               | 20.60                | 4.32         | 4.32               | M5   | 50.80              | 39.70      | 66.68               |
| 28            | 46.68               |                      |              |                    |      | 57.10              | 44.50      | 76.20               |
| 32            | 53.36               | 22.20                | 4.32         | 4.32               | M5   | 63.50              | 49.20      | 84.12               |
| 36            | 59.56               |                      |              |                    |      |                    |            |                     |

## ORDERING INFO

**97B-3105-XX-CF**


SERIES DESIGNATION

CF-CLOSED FLANGE  
HF-HOLLOW FLANGE

DESIGNATION FOR  
DUMMY RECEPTACLE

SHELL SIZE

## Thru Bulkhead Receptacle



| SHELL SIZE | 'A'<br>+0.0<br>-0.15 | 'K'<br>+0.20 | 'M'<br>+0.41<br>-0.0 | 'R'<br>+0.10 | 'S'<br>+0.20 | 'L'<br>MAX. |
|------------|----------------------|--------------|----------------------|--------------|--------------|-------------|
| 10SL       | 18.21                | 2.79         | 14.20                | 18.20        | 25.40        | 37.75       |
| 12S        | 21.40                | 3.20         | 14.20                | 20.60        | 28.00        | 37.75       |
| 14S        | 24.61                | 3.20         | 14.20                | 23.00        | 30.00        | 37.75       |
| 16S        | 27.41                | 3.20         | 14.20                | 24.60        | 32.50        | 37.75       |
| 18         | 30.81                | 3.99         | 19.00                | 27.00        | 35.00        | 51.40       |
| 20         | 34.19                | 3.99         | 19.00                | 29.40        | 38.00        | 51.40       |
| 22         | 37.39                | 3.99         | 19.00                | 31.80        | 41.00        | 51.40       |
| 24         | 40.89                | 3.99         | 20.60                | 34.90        | 44.50        | 51.40       |
| 28         | 46.71                | 3.99         | 20.60                | 39.70        | 50.80        | 51.40       |
| 32         | 53.39                | 3.99         | 22.20                | 44.50        | 57.00        | 51.40       |
| 36         | 59.59                | 3.99         | 22.20                | 49.20        | 63.50        | 51.40       |

**ORDERING INFO**  
**TBH-97BS-XX-YY PS**

THRU BULKHEAD SERIES  
SERIES DESIGNATION

PIN & SOCKET CONTACT  
INSERT ARRANGEMENT

## MS/97B Connector- Accessories

### Crimp contact

Contacts for MS/97B connectors are machined from copper alloys and silver plated for maximum corrosion resistance, with a minimum millivolt drop and a maximum current carrying capacity; the size 16 and 12 socket contacts are of the closed entry design. Gold plated contacts are also available.

| Part Number<br>For Crimp Contacts<br>only* | Pin/<br>Socket | Mating End<br>Size | Wire Barrel<br>Size | Allowable<br>Wire size | Test Current***<br>Amps | Insertion/Removal<br>Tool |
|--------------------------------------------|----------------|--------------------|---------------------|------------------------|-------------------------|---------------------------|
| MS-106433<br>MS-108456                     | Pin<br>Socket  | 16 Short†          | 16                  | 16<br>18<br>60<br>22** | 13<br>10<br>7.5<br>5    | 97B-IR-16                 |
| MS-108295<br>MS-108457                     | Pin<br>Socket  | 16 Long            | 16                  | 16<br>18<br>20<br>22** | 13<br>10<br>7.5<br>5    | 97B-IR-16                 |
| MS-108388<br>MS-110262                     | Pin<br>Socket  | 12                 | 12                  | 12<br>14               | 23<br>17                | 97B-IR-12                 |
| MS-108386<br>MS-108387                     | Pin<br>Socket  | 8                  | 8                   | 8<br>10**              | 46<br>33                | 97B-IR-8                  |
| MS-108384<br>MS-111878                     | Pin<br>Socket  | 4                  | 4                   | 4<br>6**               | 80<br>60                | 97B-IR-4                  |
| MS-112067<br>MS-112068                     | Pin<br>Socket  | 0                  | 0                   | 0<br>1<br>2**          | 150<br>125              | 97B-IR-0                  |

\* Solder contacts are not sold as separate items. Part numbers shown here are for crimp contacts only.

\*\* When using wire adapter sleeve shown.

\*\*\* Contact rating as stated are test ratings only. The connector may not withstand full rated current through all contacts continuously. Please note that the electrical data given is not an establishment of electrical safety factors. This is left entirely in the designer's hands as he can best determine which peak voltage, switching surges, transients, etc. can be expected in a particular circuit.

## MS/97B Connectors

### Application tools

When proprietary crimp contacts are employed rather than the standard MS approved solder contacts, the following application tools are recommended for use. There is a possibility of additional crimping tools other than those included being available at present or in the future for this specific application.

TOOLING CHART


| Crimping<br>Tool | Positioner/<br>Turret |
|------------------|-----------------------|
| M22520/1-01      | *                     |
| M22520/1-01      | *                     |
| **               | **                    |
| **               | **                    |
| **               | **                    |

\* Use Daniels Turret TH29-1 or Astro Tool Co. Turret 616266

\*\* For appropriate crimp tool and positioner refer to Pico Crimping Tool Co.

† Tools used with Arbor Press 11-7364

To obtain the specific connector required, write down the connector number from the typical example below. Only inserts shown in the availability chart shown on page 7 can be specified. Connectors are delivered with protective plastic dust covers. Include premating contact designation only if premating contact is required. The second letter in the premating contact designation stands for the actual contact position. **B** at the end of the connector number indicates telescopic bushing provided.



Notice : All information, including illustrations given herein is believed to be accurate at the time of printing. In lieu of design advances, Amphenol reserves the right to change specifications without notice. This publication ACRMS02 03/13 MS AND 97B Series Connectors supercedes all existing Amphenol literature on MS AND 97 B Series Connectors.

## NORTH AMERICA

### Sales & Product Support

Amphenol PCD  
72 Cherry Hill Drive  
Beverly, MA 01915 USA  
Tel: +1-978-624-3400  
Fax: +1-978-927-1513  
info@amphenolpcd.com  
www.amphenolpcd.com  
www.backshellworld.com

Amphenol Aerospace Operations  
40-60, Delaware Avenue  
Sidney, NY 13838-1395  
Tel: +1-607-563-5011  
Fax: +1-607-563-5357

Amphenol Canada  
Meford Drive  
Scarborough,  
ON M1B 2X6  
Tel: +416-291-4401  
Fax: +416-292-0647

Amphenol Fiber Systems International  
1300 Central Expressway North  
Suite 100 Allen, Texas 75013, USA  
Tel: +1-214-547-2400  
Fax: +1-214-547-9344

## EUROPE

### France

Amphenol Socapex S.A.S.  
948, Promenade de l'Arve  
Bp29, Thyez Cedex  
74311, France  
Tel: +33-4-5089-2800  
Fax: +33-4-5096-1941

### United Kingdom

Amphenol Limited  
Thanet Way, Whitstable  
Kent CT5 3JF, England  
Tel: +44-1227-773-200  
Fax: 44-1227-276-571

### Germany

Amphenol-Air LB GmbH  
Am Kleinbahnhof 4  
Saarlouis  
D-66740, Germany  
Tel: 49-6831-9810-00  
Fax: 49-6831-9810-30

### Italy

Via Barbaiana 5  
20020 Lainate (Milano)  
Italy  
Tel: +39-02-93254.209  
+39-02-93254.214  
Fax: +39-02-93254-444

### Center & East Europe

Amphenol  
Wiener Gasse 68  
2380 Perchtoldsdorf  
Tel: +43-699-10396071  
Fax: +43 699 40396071

Amphenol Air-LB  
Immeuble Le Doublon  
11, Avenue Dobonnet  
Courbevoie-Cedex  
92407, France  
Ph: +33-1-4905-3000  
Fax: +33-1-4905-3043

### Spain

Amphenol Iberica  
Edificio Burgosol Oficina  
N 55 C/Comunidad de  
Madrid 35 bis -  
Las Rozas (Madrid)  
Tel: +34-91-6407302  
+34-91-6407306  
Fax: +34-91-6407307

### Austria

Amphenol Austria  
Wiener Gasse 68  
2380, Erchtoldsdarf,  
Austria  
Tel: + 43-69910396071  
Fax: + 43-69940306071

### Holland

Amphenol Benelux  
Zadelmaker 121  
NL-2401 PD Alphen  
aan den Rijn Holland  
Tel: +31-172-444903  
Fax: +31-172 240254

### Sweden

Amphenol  
Industrial and Military &  
Aerospace  
Nordic & Baltic  
Military Phone/  
Mobile +46702129200  
Industrial +46 767909560

## ASIA

### India

Amphenol Interconnect India Pvt. Ltd.  
105 Bhosari Industrial Area  
Pune-411026, India  
Tel: +9120-3068-8305  
Fax: +9120-2712-9158

Amphenol Interconnect India Pvt. Ltd.  
61 Electronics City  
Bangalore-560 100, India  
Ph: +9180-2852-3838  
Fax: +9180-2852-0418

### Japan

Amphenol Japan  
471-1, Deba, Ritto City  
Shiga 520-3041, Japan  
Tel: +81-77-553-8501  
Fax: +81-77-551-2200

### Korea

Amphenol Daeshin Electronics  
558 SoSa, SongNae, Bucheon-City  
Kyunggi-Do, Korea 420-130  
Tel: +82-32-610-3800  
Fax: +92-32-673-2507

### Singapore

Amphenol East Asia Ltd.  
72 Bendemeer Road  
# 03-33 Luzerne  
Singapore 339 941  
Tel: 65-6294-2128  
Fax: 65-6294-3522

### China

Amphenol PCD Shenzhen  
3/F Building, A4 Songbai  
Industrial Park  
East Road of Minghuan  
Gongming Town, Baon District  
Shenzhen, China  
Tel: +86-755-8173-8000  
Fax: +86-755-8173-8180

## ROW

### Australia

Amphenol Australia Pty Ltd  
2 Fiveways Boulevard  
Keysborough  
VIC 3173  
Ph: +61-3-8796-8888  
Fax: +61-3-8796-8801

### Africa

Amphenol South Africa  
30 Impala Road  
2196 Sandton-Chistlehurst  
South Africa  
Tel: +27-11-783-9517  
Fax: +27-11-783-9519

### Russia

Amphenol Russia  
8-2 Yaroslavskaja Str  
129164 Moscow, Russia  
Tel: +7-495-937-6341  
Fax: +7-495-937-6319

### Argentina

Amphenol Argentina  
Avenida Callao 930  
2nd Floor, Office B Plaza  
C1023AAP Buenos Aires  
Argentina  
Tel: 54-11-4815-6886  
Fax: 54-11-4814-5779

### Israel

Bar-Tec Ltd.  
P.O. Box 279  
Kfar Sava, 44102 Israel  
Tel: +972-9-7644100  
Fax: +972-9-7674324

### Maslak

34396 Istanbul  
Tel: +90-212-335-2501  
Fax: +90-212-335-2500

### Brazil

Amphenol do Brasil Ltda  
Rua Diogo Moreira 132  
CEP 05423-010  
Sao Paulo-SP, Brazil  
Tel: +55-11-3815-1003  
Fax: +55-11-3815-1629

# Amphenol

*A Global Company*



Pune Operations



Bangalore Operations

# Amphenol

**Interconnect India Pvt. Ltd.**

## Our offices in India:

### MARKETING HEADQUARTERS

105, Bhosari Industrial Area,  
Pune - 411 026.  
Tel.: 91-20-30688303, 30688304  
Fax : 91-20-30688321  
Email : vbhavsar@amphenol-in.com  
sales@amphenol-in.com

### Southern Region

4931, 11th Floor, High Point IV  
45, Palace Road, Bangalore 560 001.  
Tel.: 91-80-22281392, 22281002  
Fax : 91-80-22253859  
Email : kmanoj@amphenol-in.com

### Northern and Eastern Region

1414, 14th Floor, Chiranjiv Tower,  
43, Nehru Place, New Delhi - 110 019.  
Tel. : 91-11-26449177  
Telefax : 91-11-26449176  
Email : sunily@amphenol-in.com

### Export

105, Bhosari Industrial Area,  
Pune - 411 026, India.  
Tel.: 91-20-30688305, 30688353  
Fax : 91-20-27129158  
Email : svpatil@amphenol-in.com

### Western Region

105, Bhosari Industrial Area,  
Pune - 411 026.  
Tel.: 91-20-27119735, 30688334  
Fax: 91-20-27120581, 27119735  
Email : sunilp@amphenol-in.com

### Central Region

107, 1st Floor, 'Am Sri Classic',  
Sarojinidevi Road, Secunderabad - 500 003.  
Telefax : 91-40-66332906  
Email : pprasad@amphenol-in.com