




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO. **	PANEL THICKNESS	A	B	C	D	E	F *	G *
						REF.	REF.	REF.
GE_36FR-C (Y)	TO 0.036 (0.91)	0.025 (0.64)	0.045 (1.14)	0.087 (2.21)	0.030 (0.76)	0.106 (2.69)	.105	0.150 (3.81)
GE_62FR-C (Y)	0.036 - 0.062 (0.91) - (1.57)	0.035 (0.89)	0.070 (1.78)	0.130 (3.30)	0.030 (0.76)	0.131 (3.33)	.105	0.150 (3.81)
GE_99FR-C (Y)	0.062 - 0.099 (1.57) - (2.51)	0.054 (1.37)	0.108 (2.74)	0.155 (3.94)	0.030 (0.76)	0.169 (4.29)	.125	0.150 (3.81)
GE_144FR-C (Y)	0.099 - 0.144 (2.51) - (3.66)	0.090 (2.29)	0.152 (3.86)	0.192 (4.88)	0.030 (0.76)	0.213 (5.41)	.160	0.150 (3.81)



SOLID WALL



SLOTTED WALL

NOTES:

- * 1) DIM'S F & G APPLY ONLY TO SLOTTED GROMMET EDGING.
 ** 2) PART NO. EXAMPLE:

GE S 36 FR - C (Y)
 GE: GROMMET EDGING
 S: SOLID
 E: SLOTTED
 36: MAX. PANEL THICKNESS
 FR: FLAME RETARDANT POLYETHYLENE
 C: 100 FOOT ROLL
 (Y): RoHS COMPLIANT PART DESIGNATION

- 3) SEE CURRENT PRICE SHEET FOR PART NO. SUFFIX DESIGNATION FOR PACKAGE SIZE.
 4) COLOR: NATURAL
 5) SLOTTED WALL STYLE IS RECOMMENDED FOR INSIDE EDGE OF PANEL CUT OUTS.
 SOLID WALL STYLE IS RECOMMENDED FOR STRAIGHT, OUTSIDE EDGES.

(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

CAD FILENAME/LAYERS

G03597D0_DC_GB0281BA_05/00A

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

FLAME RETARDANT POLYETHYLENE
 GROMMET EDGING
 (CUSTOMER DRAWING)



UNLESS OTHERWISE SPECIFIED,
 DIMENSIONAL TOLERANCES ARE:
 (.X) ± 0.1 (2.5) (.XXX) ± 0.020 (.5)
 (.XX) ± 0.05 (1.3) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
 ALL DIMENSIONS ARE GIVEN
 IN INCHES, THIRD ANGLE PROJECTION.

5	7/19/12	LEF	VJS	A: REMOVE OBSOLETE PART GE_189FR-C B: ADD CUSTOMER DRW TO TITLE BLK.	GB0281BA	5	RAMI			DRAWN BY SJSU	MAT'L:	SCALE NONE	
4	5/29/08	JAD		ADDED (Y) PART NUMBERS	GB0281BA	4				DATE 4-15-93	SEE NOTE #2	DRAWING NO. GB0281BA	DWG A
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP		CHK'D			SIZE