





PRODUCT NUMBER
SEE SHEET 2

NOTES :

1. MINI PUSH-OUT FORCE TERMINAL IN BOTH DIRECTIONS 22N.
2. TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW
EXAMPLE: 8 POS: $(N \times 2.54) - 1 = 19.32$ mm



mat'l. code SEE NOTES				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family DUBOX			
ltr	ecn no	dr	date	tolerances unless		otherwise specified				title SHR. HEADER STR SR TMT			
N	F06-0228	LMU	06.07.11	angles	linear	.X ±0.3		scale 5:1					
P	F06-0319	LMU	06.11.10			.XX ±0.15							
R	F07-0147	LMU	07.03.01			.XXX ±0.05							
S	F07-0220	J.CO	07.06.14	dr	D LEGRAND		99.03.03			dwg no		sheet 1 of 2	size
T	F08-0147	YOV	08.04.14	engr	JM PHAMVAN		99.03.03			76384		A	
				chr	JM PHAMVAN		99.03.03						
M	F05-0159	LMU	05.03.31	appd	JM PHAMVAN		99.03.03			type		CUSTOMER Drawing	
sheet index		revision		T	E								
		sheet		1	2								

