






LOC		DIST		REVISIONS					
AD		25		P	LTR	DESCRIPTION	DATE	DWN	APVD
					01	REVISED PER ECO-08-013371	05JUN08	DH	DB

- 1 HOUSING MATERIAL: GLASS-FILLED POLYMER.
- 2 CONTACT MATERIAL: COPPER ALLOY.
- 3 PART NUMBER, DATE CODE IDENTIFICATION, CSA LOGO IN THIS APPROXIMATE AREA.
- 4 ACTION PIN POSTS REQUIRE 1.57[.062] MINIMUM THICK PC BOARD. RECOMMENDED PC BOARD DRILLED HOLES ARE $\varnothing 1.151 \pm 0.025 [.0453 \pm .0010]$ WITH $0.02 - 0.08 [.001 - .003]$ COPPER AND $0.008 [.0003]$ MINIMUM TIN-LEAD PLATING. FINISHED HOLES AFTER PLATING $\varnothing 0.94 - 1.09 [.037 - .043]$.
- 5 CONTACT FINISH: DIN 41612 CLASS 2 IN CONTACT AREA. TIN PLATE ON POSTS.
- 6 CONTACT POINT.
- 7 MARKING ON THIS SIDE.



SECTION X-X



PC BOARD LAYOUT

5148423-5
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. POLIGNONE	14APROS	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK A. SHARPE	14APROS	NAME ASSEMBLY, RECEPTACLE, TYPE M, EUROCARD, 42+6, PRESS-FIT, 4.83[.190]	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. SHARPE	14APROS	PRODUCT SPEC	
0 PLC ± -		APPLICATION SPEC		SIZE	
1 PLC ± -		WEIGHT		CAGE CODE	
2 PLC ± 0.15[.005]		CUSTOMER DRAWING		DRAWING NO	
3 PLC ± -		SCALE		SHEET	
4 PLC ± -		4:1		1 OF 1	
5 ANGLES ± -		REV		01	
FINISH		5			