

This document was generated on 02/25/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [43160-3102](#)

Status: **Active**

Overview: **Sabre™**

Description: 7.50mm Pitch Sabre™ Header, Right Angle, 2 Circuits, Glow Wire Compatible. Recommended PCB Thickness 1.60mm, with Board Lock

Documents:

[3D Model](#)

[Drawing \(PDF\)](#)

[Product Specification PSX-44441-9999 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)



Series

image - Reference only

Agency Certification

CSA
UL

General

Product Family
Series
Application
Comments

LR19980
E29179

PCB Headers

43160

Power, Wire-to-Board

"Fully Polarized, high power wire to board and wire to wire connector system<P><P>This Molex product is manufactured from material that has the following ratings, tested by independent agencies:.. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options."

Sabre™

987650-5662

Sabre™

800754378185

Overview

Product Literature Order No

Product Name

UPC

Physical

Breakaway
Circuits (Loaded)
Circuits (maximum)
Color - Resin
Durability (mating cycles max)
First Mate / Last Break
Flammability
Glow-Wire Compliant
Guide to Mating Part
Keying to Mating Part
Lock to Mating Part

No

2

2

Black

25

No

94V-0

Yes

No

Yes

Yes

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[43160Series](#)

Mates With

[444412002 Sabre™ Receptacle Housing](#)

Material - Metal
Material - Plating Mating
Material - Plating Termination
Material - Resin
Net Weight
Number of Rows
Orientation
PC Tail Length
PCB Locator
PCB Retention
PCB Thickness - Recommended
Packaging Type
Pitch - Mating Interface
Pitch - Termination Interface
Plating min - Mating
Plating min - Termination
Polarized to Mating Part
Polarized to PCB
Shrouded
Stackable
Surface Mount Compatible (SMC)
Temperature Range - Operating
Termination Interface: Style

Brass
Tin
onlinecomponents.com
THE ONLINE DISTRIBUTOR OF ELECTRONIC COMPONENTS
High Temperature Thermoplastic
3.331/g
1
Right Angle
3.81mm
Yes
Yes
1.60mm
Tray
7.50mm
7.50mm
0.889µm
0.889µm
Yes
Yes
Fully
No
No
-40°C to +75°C
Through Hole

Electrical

Current - Maximum per Contact
Voltage - Maximum

18A
600V

Solder Process Data

Duration at Max. Process Temperature (seconds)
Lead-free Process Capability
Max. Cycles at Max. Process Temperature
Process Temperature max. C

5
Wave Capable (TH only)
1
235

Material Info

Reference - Drawing Numbers

Product Specification
Sales Drawing

PSX-44441-9999
SDA-43160-****

This document was generated on 02/25/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION