


Single Phase Bridge Rectifier




CP6 Series



Features:

- High surge current capability
- PCB mounted / screw fixing
- Surge overload ratings to 125 Amperes
- Low forward voltage, and reverse leakage
- Small size, simple installation
- Reliable low cost construction utilizing moulded plastic technique



Dimensions : Millimetres

Mechanical Data :

Mounting Position	: Any
Weight	: 0.2 ounce, 5.6 g
Terminals	: Lead solderable per MIL-STD-202 Method 208
Mounting Torque	: 5 Inches lb maximum

Maximum Ratings and Electrical Characteristics :

Ratings at 25°C ambient temperature unless otherwise specified

Single phase, half wave, 60 Hz, resistive or inductive load

For capacitive load, derate current by 20%

Single Phase Bridge Rectifier



CP6 Series

	CP600	CP601	CP602	CP606	Units
Maximum Recurrent Peak Reverse Voltage	50	100	200	600	V
Maximum RMS Bridge Input Voltage	35	70	140	420	
Maximum DC Blocking Voltage	50	100	200	600	
Maximum Average Forward Current at T _A = 50°C See Figure 2	6				A
Peak Forward Surge Current, 8.3 ms Single Half Sine-Wave Superimposed on Rated Load	125				
Maximum Forward Voltage Per Bridge Element Specified Current at 3 A dc and 50°C See Figure 3	1.1				V
Maximum Reverse Leakage at Rated DC Blocking Voltage per Element at 25°C See Figure 4 at 100°C	10 1				μA mA
I ² t Rating for Fusing (t <8.35 ms)	127				A ² S
Typical Junction Capacitance Per Leg (Note 4) C _J	186				pF
Typical Thermal Resistance Per Leg (Note 3) R _{θJA} Typical Thermal Resistance Per Leg (Note 2) R _{θJC}	22 7.3				°C / W
Operating Temperature Range T _J	-55 to +125				°C
Storage Temperature Range T _A	-55 to +150				

Notes:

1. Bolt down on heat-sink with silicon thermal compound between bridge and mounting surface for maximum heat transfer with number 6 screw
2. Unit mounted on $5 \times 6 \times 0.11$ Inches thick ($14 \times 15 \times 0.3 \text{ cm}$) Aluminium plate
3. Unit mounted on PCB at 0.395 Inches (9.5 mm) lead length with 0.5×0.5 Inches ($12 \times 12 \text{ mm}$) copper pads
4. Measured at 1 MHz and applied reverse voltage of 4 V

Rating and Characteristics Curves

Figure 1 - Derating Curve for Output Rectified Current





Figure 2 - Typical Instantaneous Forward Characteristics (25°C)



Single Phase Bridge Rectifier



CP6 Series

Figure 3 -Typical Peak Reverse Characteristics





Figure 4 -Maximum Non- Repetitive Peak Forward Surge Current



Specifications

I_O (A) at $T_A = 50^\circ\text{C}$	I_{FSM} (A)	Body		Lead			Part Number
		Height	Width / Depth	Length	Spacing	Diameter (Typical)	
6	125	6.86	15.75	19.1	11.3	1.01	CP600
							CP601
							CP602
							CP606

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

