



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS	POWER										SIGNAL								
		E1	P1	P2	P3	P4	P5	P6	P7	P8	P9	P10	P11	1	2	3	4	5	6	E2
51732-039-- NOTE 3	D C B A		PA	PA	PA	PA	PA	PA	PA	PA	PA	PA	PA	UH	UH	UH	UH	UH	UH	
			TT	TT	TT	TT	TT	TT	TT	TT	TT	TT	TT	GG	GG	GG	GG	GG	GG	
			SS	SS	SS	SS	SS	SS	SS	SS	SS	SS	SS	FF	FF	FF	FF	FF	FF	
			RR	RR	RR	RR	RR	RR	RR	RR	RR	RR	RR	EE	EE	EE	EE	EE	EE	



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
U	[6.86]	SIGNAL
T	[6.86]	SIGNAL
S	[6.86]	SIGNAL
R	[6.86]	SIGNAL
PA	[N/A]	POWER
G	[5.59]	SIGNAL
H	[5.59]	SIGNAL
E	[5.59]	SIGNAL
F	[5.59]	SIGNAL

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI	
ltr	ecn no.	dr	date	linear		0.X ±0.3		COPY		www.fciconnect.com	
A	DG07-0243	JULIA	06/12/07			0.XX ±0.13		projection		title	
B	DG10-0047	WL	02/01/10			0.XXX ±0.051				IIP + 24S RIGHT ANGLE SOLDER HEADER	
				angles		0° ±2°				product family	
				dr	JULIA WANG	06/12/07				PwrBlade	code
				enrg	RYAN YUAN	06/13/07				size	213
				chr	BEER FU	06/12/07				dwg no	sheet
				appd	JOSEPH HSIA	06/12/07				51732-039	1 of 4
sheet index	revision sheet	B	B	B	B			scale	1:1		
		1	2	3	4						

Pro/E

cage code 22526


All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

mat'l code				SEE NOTE				tolerances unless otherwise specified				CUSTOMER				 www.fciconnect.com									
lfr	ecn no.	dr	date	linear	0.X $\pm$ 0.3				COPY				projection 	title IIP + 24S RIGHT ANGLE SOLDER HEADER											
B					0.XX $\pm$ 0.13																				
					0.XXX $\pm$ 0.051																				
					0° $\pm$ 2°																				
				angles									product family PwrBlade code												
				dr	JULIA WANG 06/12/07								size		dwg no		213								
				engr	RYAN YUAN 06/13/07												sheet								
				chr	BEER FU 06/12/07								scale		A 51732-039		2 of 4								
				appd	JOSEPH HSIA 06/12/07				1:1																
sheet index		revision sheet																							
Pro/E								3								cage code 22526								4	

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.



mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date			linear	$0.X \pm 0.3$	COPY		www.fciconnect.com	
B						linear	$0.XX \pm 0.13$	projection		title	
						angles	$0.XXX \pm 0.051$			IIP + 24S	
						dr	$0^\circ \pm 2^\circ$			RIGHT ANGLE SOLDER HEADER	
						enr	JULIA WANG 06/12/07			product family	
						enr	RYAN YUAN 06/13/07			PwrBlade	
						chr	BEER FU 06/12/07			code	
						appd	JOSEPH HSIA 06/12/07			213	
sheet index	revision sheet							scale	1:1	size	
										dwg no	
										51732-039	
										sheet	
										3 of 4	
										cage code	
										22526	

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51732-039_- NOTE: 3

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH
ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

2. HOUSING MATERIAL: UL 94 V-0 GLASS FILLED
HIGH-TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY
3. 51732-039;51732-039LF PLATING SPEC. SEE PRINT:10064183
4. MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON
THIS SURFACE.
5. PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.
6. PACKAGED IN TRAYS.

PCB NOTES:

7. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
8. MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.
9. $\varnothing 1.151 \pm 0.025$ DRILLED HOLES PLATED WITH
0.008 MIN SnPb OR Sn OVER 0.03
TO 0.08 Cu PLATING TO ACHIEVE
 $\varnothing 1.02 \pm .07$ HOLE.
10. "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.
11. CONNECTOR KEEP-OUT ZONE.

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date					COPY		www.fciconnect.com	
B				linear		$0.X \pm 0.3$		projection		title	
						$0.XX \pm 0.13$				11P + 24S	
				angles		$0.XXX \pm 0.051$				RIGHT ANGLE SOLDER HEADER	
						$0^\circ \pm 2^\circ$					
				dr	JULIA WANG	06/12/07		MIM		product family	PwrBlade
				enrg	RYAN YUAN	06/13/07				size	code
				chr	BEER FU	06/12/07		scale		dwg no	213
				appd	JOSEPH HSIA	06/12/07		1:1	A	51732-039	sheet
sheet	revision										4 of 4
index	sheet										

cage code 22526