



THREE PORT CONNECTOR BLOCK SHOWN  
WITH PLASTIC CLOSURE PLUGS REMOVED.  
SEE TABLE FOR DIMENSIONS OF PARTS  
WITH ADDITIONAL PORTS



PANDUIT FINISHED GOODS PIN	CONDUCTOR RANGE	HEX KEY	SCREW QTY.	CAP (SCREW PORT) QTY.	CAP (WIRE PORT) QTY.	A	L	N	TIGHTENING TORQUE
PC SB 250 -2 -6 Y	250 kcmil - # 10 STR	5/16	2	2	4	2.03	1.781	2	2.75 in/lb
PC SB 250 -3 -6 Y		5/16	3	3	6	2.97	2.718	3	
PC SB 250 -4 -6 Y		5/16	4	4	8	3.91	3.656	4	
PC SB 250 -5 -4 Y		5/16	5	5	10	4.84	4.593	5	
PC SB 250 -6 -4 Y		5/16	6	6	12	5.78	5.531	6	
PC SB 250 -8 -3 Y		5/16	8	8	16	7.66	7.406	8	
PC SB 250 -10 -2 Y		5/16	10	10	20	9.53	9.281	10	
PC SB 250 -12 -2 Y		5/16	12	12	24	11.41	11.156	12	
PC SB 250 -14 -1 Y		5/16	14	14	28	13.28	13.031	14	



NOTES:

1. UL486A-UL486B LISTED, DUAL RATED CU9AL FOR ALUMINUM OR COPPER CONDUCTORS. MEETS OR EXCEEDS ANSI C119.4
2. SEE TABLE FOR WIRE RANGE.
3. STRIP LENGTH: .88 +.06/-0
4. FOR TIGHTENING TORQUE SEE TABLE
5. VOLTAGE RATING: 600 V. MAX. BUILDING WIRE, 1000 V. MAX. IN SIGNS & FIXTURES.
6. TEMPERATURE RATING: 90 °C (CU9AL).
7. CONNECTOR BLOCK BODY ARE MADE FROM ALUMINUM. CONDUCTOR PORTS IN CONNECTOR BLOCK ARE PREFILLED WITH AN OXIDE-INHIBITING COMPOUND.
8. CONNECTOR TO INCLUDE TIN PLATED ALUMINUM CLAMPING SCREWS FOR EACH CONDUCTOR PORT.
9. INSULATION MATERIAL IS CLEAR PVC.
10. CLAMPING SCREW ACCESS PORTS AND ALL WIRE ENTRY PORTS ARE PROVIDED WITH REMOVABLE PLASTIC CLOSURE PLUGS.
11. ALL DIMENSIONS SHOWN ARE NOMINAL.
12. ONLY ONE CONDUCTOR PER PORT ALLOWED.
13. PACKAGE QTY: -12 = 12 PCS.  
-6 = 6 PCS.  
-4 = 4 PCS.
14. THIS PART IS RoHS COMPLIANT.

TITLE MULTI-TAP INSULATED CONNECTORS PCSB250 SERIES CUSTOMER DRAWING															
ITEM REVISION NAME C41571BB-C41571/05															
DATASET FILE NAME C41571/05.SLDDRW															
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]															
$.X \pm .XX$ $.XX \pm .02$					$.XXX \pm ANGLES \pm$										
MATERIAL PANDUIT															
SEE NOTES															
DRAWN BY MS															
DATE 8/99															
CHK RLS															
SCALE NONE															
DRAWING NUMBER C41571_05															
SIZE B															
05	2/13	JHNU	JHNU	RGB	REV DATE BY CHK APR					DESCRIPTION		ECN		SHEET 1 OF 1	