

## Schottky Rectifier New Generation 3 D-61 Package, 2 x 40 A


VS-81CNQ...APbF




D-61-8



VS-81CNQ...ASMPbF



D-61-8-SM



VS-81CNQ...ASLPbF



D-61-8-SL



### FEATURES

- 175 °C  $T_J$  operation
- Center tap module
- Low forward voltage drop
- High frequency operation
- High purity, high temperature epoxy encapsulation for enhanced mechanical strength and moisture resistance
- Guard ring for enhanced ruggedness and long term reliability
- New fully transfer-mold low profile, small footprint, high current package
- Through-hole versions are currently available for use in lead (Pb)-free applications ("PbF" suffix)
- Compliant to RoHS directive 2002/95/EC
- Designed and qualified for industrial level



Available  
**RoHS\***  
COMPLIANT

### DESCRIPTION

The center tap Schottky rectifier module has been optimized for low reverse leakage at high temperature. The proprietary barrier technology allows for reliable operation up to 175 °C junction temperature. Typical applications are in switching power supplies, converters, freewheeling diodes, and reverse battery protection.

### PRODUCT SUMMARY

|             |              |
|-------------|--------------|
| $I_{F(AV)}$ | 2 x 40 A     |
| $V_R$       | 35 V to 45 V |

### MAJOR RATINGS AND CHARACTERISTICS

| SYMBOL      | CHARACTERISTICS                       | VALUES      | UNITS |
|-------------|---------------------------------------|-------------|-------|
| $I_{F(AV)}$ | Rectangular waveform                  | 80          | A     |
| $V_{RRM}$   | Range                                 | 35 to 45    | V     |
| $I_{FSM}$   | $t_p = 5 \mu s$ sine                  | 4600        | A     |
| $V_F$       | 40 Apk, $T_J = 125^\circ C$ (per leg) | 0.54        | V     |
| $T_J$       | Range                                 | - 55 to 175 | °C    |

### VOLTAGE RATINGS

| PARAMETER                            | SYMBOL    | VS-81CNQ035APbF | VS-81CNQ040APbF | VS-81CNQ045APbF | UNITS |
|--------------------------------------|-----------|-----------------|-----------------|-----------------|-------|
| Maximum DC reverse voltage           | $V_R$     | 35              | 40              | 45              | V     |
| Maximum working peak reverse voltage | $V_{RWM}$ |                 |                 |                 |       |

\* Pb containing terminations are not RoHS compliant, exemptions may apply

**ABSOLUTE MAXIMUM RATINGS**

| PARAMETER                                                                    | SYMBOL      | TEST CONDITIONS                                                                                                           | VALUES | UNITS |
|------------------------------------------------------------------------------|-------------|---------------------------------------------------------------------------------------------------------------------------|--------|-------|
| Maximum average forward current<br>See fig. 5                                | $I_{F(AV)}$ | 50 % duty cycle at $T_C = 141\text{ }^{\circ}\text{C}$ , rectangular waveform                                             | 80     | A     |
| Maximum peak one cycle<br>non-repetitive surge current per leg<br>See fig. 7 | $I_{FSM}$   | 5 $\mu\text{s}$ sine or 3 $\mu\text{s}$ rect. pulse                                                                       | 4600   |       |
|                                                                              |             | 10 ms sine or 6 ms rect. pulse                                                                                            | 790    |       |
| Non-repetitive avalanche energy per leg                                      | $E_{AS}$    | $T_J = 25\text{ }^{\circ}\text{C}$ , $I_{AS} = 8\text{ A}$ , $L = 1.7\text{ mH}$                                          | 54     | mJ    |
| Repetitive avalanche current per leg                                         | $I_{AR}$    | Current decaying linearly to zero in 1 $\mu\text{s}$<br>Frequency limited by $T_J$ maximum $V_A = 1.5 \times V_R$ typical | 8      | A     |

**ELECTRICAL SPECIFICATIONS**

| PARAMETER                                                | SYMBOL         | TEST CONDITIONS                                                                           | VALUES | UNITS            |
|----------------------------------------------------------|----------------|-------------------------------------------------------------------------------------------|--------|------------------|
| Maximum forward<br>voltage drop per leg<br>See fig. 1    | $V_{FM}^{(1)}$ | 40 A                                                                                      | 0.60   | V                |
|                                                          |                | 80 A                                                                                      | 0.74   |                  |
|                                                          |                | 40 A                                                                                      | 0.54   |                  |
|                                                          |                | 80 A                                                                                      | 0.66   |                  |
| Maximum reverse<br>leakage current per leg<br>See fig. 2 | $I_{RM}^{(1)}$ | $T_J = 25\text{ }^{\circ}\text{C}$                                                        | 5      | mA               |
|                                                          |                | $T_J = 125\text{ }^{\circ}\text{C}$                                                       | 45     |                  |
| Maximum junction capacitance per leg                     | $C_T$          | $V_R = 5\text{ V}_{DC}$ (test signal range 100 kHz to 1 MHz) $25\text{ }^{\circ}\text{C}$ | 2600   | pF               |
| Typical series inductance per leg                        | $L_S$          | Measured lead to lead 5 mm from package body                                              | 5.5    | nH               |
| Maximum voltage rate of change                           | $dV/dt$        | Rated $V_R$                                                                               | 10 000 | V/ $\mu\text{s}$ |

**Note**(1) Pulse width < 300  $\mu\text{s}$ , duty cycle < 2 %**THERMAL - MECHANICAL SPECIFICATIONS**

| PARAMETER                                                   | SYMBOL         | TEST CONDITIONS                                                  | VALUES      | UNITS                  |
|-------------------------------------------------------------|----------------|------------------------------------------------------------------|-------------|------------------------|
| Maximum junction and storage<br>temperature range           | $T_J, T_{Stg}$ |                                                                  | - 55 to 175 | $^{\circ}\text{C}$     |
| Maximum thermal resistance,<br>junction to case per leg     | $R_{thJC}$     | DC operation<br>See fig. 4                                       | 0.85        | $^{\circ}\text{C/W}$   |
| Maximum thermal resistance,<br>junction to case per package |                | DC operation                                                     | 0.42        |                        |
| Typical thermal resistance,<br>case to heatsink             | $R_{thCS}$     | Mounting surface, smooth and greased<br>Device flatness < 5 mils | 0.30        |                        |
| Approximate weight                                          |                |                                                                  | 7.8         | g                      |
|                                                             |                |                                                                  | 0.28        | oz.                    |
| Mounting torque                                             | minimum        |                                                                  | 40 (35)     | kgf · cm<br>(lbf · in) |
|                                                             | maximum        |                                                                  | 58 (50)     |                        |
| Marking device                                              |                | Case style D-61                                                  | 81CNQ035A   |                        |
|                                                             |                |                                                                  | 81CNQ040A   |                        |
|                                                             |                |                                                                  | 81CNQ045A   |                        |
|                                                             |                | Case style D-61-8-SM                                             | 81CNQ035ASM |                        |
|                                                             |                |                                                                  | 81CNQ040ASM |                        |
|                                                             |                |                                                                  | 81CNQ045ASM |                        |
|                                                             |                | Case style D-61-8-SL                                             | 81CNQ035ASL |                        |
|                                                             |                |                                                                  | 81CNQ040ASL |                        |
|                                                             |                |                                                                  | 81CNQ045ASL |                        |



Schottky Rectifier  
New Generation 3 D-61 Package, 2 x 40 A

VS-81CNQ...A PbF Series

Vishay High Power Products




Fig. 1 - Maximum Forward Voltage Drop Characteristics (Per Leg)




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage (Per Leg)




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage (Per Leg)




Fig. 4 - Maximum Thermal Impedance  $Z_{thJC}$  Characteristics (Per Leg)




Fig. 5 - Maximum Allowable Case Temperature vs. Average Forward Current (Per Leg)




Fig. 6 - Forward Power Loss Characteristics (Per Leg)




Fig. 7 - Maximum Non-Repetitive Surge Current (Per Leg)




Fig. 8 - Unclamped Inductive Test Circuit



## VS-81CNQ...A PbF Series

Schottky Rectifier  
New Generation 3 D-61 Package, 2 x 40 A

Vishay High Power Products

### ORDERING INFORMATION TABLE

|             |     |    |   |   |   |     |   |     |
|-------------|-----|----|---|---|---|-----|---|-----|
| Device code | VS- | 81 | C | N | Q | 045 | A | PbF |
|             | 1   | 2  | 3 | 4 | 5 | 6   | 7 | 8   |

- |          |   |                              |                                        |
|----------|---|------------------------------|----------------------------------------|
| <b>1</b> | - | HPP product suffix           |                                        |
| <b>2</b> | - | Current rating (80 A)        |                                        |
| <b>3</b> | - | Circuit configuration:       |                                        |
|          |   | C = Common cathode           |                                        |
| <b>4</b> | - | Package:                     |                                        |
|          |   | N = D-61                     |                                        |
| <b>5</b> | - | Schottky "Q" series          |                                        |
| <b>6</b> | - | Voltage ratings              | 035 = 35 V<br>040 = 40 V<br>045 = 45 V |
| <b>7</b> | - | Package style:               |                                        |
|          |   | • A = D-61-8                 |                                        |
|          |   | • ASM = D-61-8-SM            |                                        |
|          |   | • ASL = D-61-8-SL            |                                        |
| <b>8</b> | - | • None = Standard production |                                        |
|          |   | • PbF = Lead (Pb)-free       |                                        |

Standard pack quantity: A = 10 pieces; ASM/ASL = 20 pieces

| LINKS TO RELATED DOCUMENTS |                                                                        |
|----------------------------|------------------------------------------------------------------------|
| Dimensions                 | <a href="http://www.vishay.com/doc?95354">www.vishay.com/doc?95354</a> |
| Part marking information   | <a href="http://www.vishay.com/doc?95356">www.vishay.com/doc?95356</a> |



## D-61-8, D-61-8-SM, D-61-8-SL

### DIMENSIONS - D-61-8 in millimeters (inches)





## DIMENSIONS - D-61-8-SM in millimeters (inches)





## DIMENSIONS - D-61-8-SL in millimeters (inches)





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**