



TST, HTST, ZST SERIES

SHROUDED .025" SQ POST IDC HEADERS

SPECIFICATIONS

TYPE STRIP

1

NO. PINS
PER ROW

LEAD
STYLE

PLATING
OPTION

ROW
OPTION

OTHER
OPTION

TST

= Cable Strip

HTST

= High Temp
Cable Strip

05, 07, 08, 10,
12, 13, 15, 17,
20, 25, 32, 36
(Standard sizes.)

Specify
LEAD
STYLE
from
chart.

-F

= Gold flash on post,
Matte Tin on tail
(Not available on -DV)

-L

= 10 μ " (0,25 μ m)
Gold on post,
Matte Tin on tail

-T

= Matte Tin

-D

= Double Row
Through-hole
(lead style -01,
-02 & -03 only)

-DV

= Double Row
Surface Mount
(lead style
-01 only)
(HTST only)

-D-RA

= Double Row
Right Angle
(lead style -04
& -05 only)

Surface
Mount
(lead style
-01 only)
(HTST only)

-P

= Pick &
Place Pad

-TR

= Tape
& Reel
Packaging

LEAD STYLE	T/H (A)
-01	(2,92) .115
-02	(4,19) .165
-03	(14,35) .565

LEAD STYLE	RIGHT ANGLE (B)
-04	(3,30) .130
-05	(5,84) .230

-D

-DV
(HTST ONLY)

-D-RA

RECOGNITIONS

UL
FILE NO. E111594

OTHER SOLUTIONS

- Shrouded board-to-board headers and stackers to mate with SSW, SSQ, ESW, ESQ, SSM and BCS Series. See TSS, HTSS and ZSS Series.

ALSO AVAILABLE
(MOQ Required)

- Other platings & sizes
 - Alignment Pins
 - Single Row
 - Locking Leads
 - Polarized
- Contact Samtec.

Note: Some lengths, styles and options are non-standard, non-returnable. ZST is non-standard, non-returnable.

ZST — **1** — **NO. PINS PER ROW** — **LEAD STYLE** — **PLATING OPTION** — **D** — **BODY HEIGHT**

05, 07, 08, 10, 12, 13, 15, 17, 20, 25, 32, 36
(Standard sizes.)

Specify LEAD STYLE from chart.

—F
= Gold flash on post,
Matte Tin on tail

—L
= 10μ" (0,25 μm)
Gold on post,
Matte Tin on tail

—T
= Matte Tin

—“XXXX”
= Body Height

LEAD STYLE	C (OAL)	MAX BODY HEIGHT
—01	(16,00) .630	(13,72) .540
—02	(18,54) .730	(16,26) .640
—03	(21,08) .830	(18,80) .740
—04	(23,62) .930	(21,34) .840
—05	(26,16) 1.030	(23,88) .940
—06	(28,70) 1.130	(26,42) 1.040
—07	(31,24) 1.230	(28,96) 1.140
—08	(33,78) 1.330	(31,50) 1.240
—09	(36,32) 1.430	(34,04) 1.340

Note: For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

Note: For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact jpg@samtec.com for more information.