

INTERCONNECTS

SERIES 310, 311, 315 • .100" GRID SOLDER TAIL • SINGLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3





FIG. 4

- SIP sockets accept .015 - .025" diameter pins and standard IC leads
- Various solder tails available: standard length, long for multi-layer boards, very low and ultra low profile. See Mill-Max #1001, #0134, #0501 or #1534 pins. See pages 161, 162 and 165 for details
- Hi-Rel, 4-finger BeCu #12 and #30 contact are rated at 3 amps. See pages 252 and 253 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 310...001	Standard Solder Tail						
	310-XX-1-41-001000 Specify number of pins 01-64							
FIG. 2	Series 311...001	Long Solder Tail						
	311-XX-1-41-001000 Specify number of pins 01-64							
FIG. 3	Series 315...001	Very Low Profile						
	315-XX-1-41-001000 Specify number of pins 01-64							
FIG. 4	Series 315...003	Ultra Low Profile						
	315-XX-1-41-003000 Specify number of pins 01-64							
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Environmental Data, See page 264								
SPECIFY PLATING CODE XX=								
Sleeve (Pin)	11	13	91	93	99	41	43	44
Contact (Clip)	10	10	10	30	100	200	200	200

★ 41 & 91 Platings Non-Standard

