




REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 ₃	REVISED	5/28/96 5/27/96	RAC

NOTES:
1. CAPTURED CENTER CONTACT

.XXX = in
XX.X = mm

HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER QQ-P-35
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204
CONTACT EXT BUSHING	IRON-NICKEL-COBALT ALLOY PER MIL-I-23011 CLASS 1 (KOVAR)	GOLD PLATE PER MIL-G-45204
HERMETIC SEAL	GLASS BEAD	N/A
COMPONENT	MATERIAL	FINISH
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES FRAC. ± 1/64 DEC. ± .005 ANGLES ± 1° These drawings and specifications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.		
DRAWN BY N.K. DATE 2/11/86 CHECKED BY J.J. 3/17/86 APP'D BY R.V. 3/27/86 AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599		
TITLE "OSM", PANEL FEEDTHROUGH, JACK RECEPTACLE, KNIFE EDGE, HERMETIC SEAL USE ASSY PROCEDURE (20-607) NO. A.P. 408-04851		
SIZE B	CODE IDENT NO. 26805	2058-5219-02
SCALE 8:1	REV 01 ₃	
SHEET 1 OF 1		