





LOC	DIST	REVISIONS				
		REV	LTR	DESCRIPTION	DATE	DWN
AF	50	A1		REVISED PER ECR-12-007322	20APR12	KH

- 1
- SPECIFICATION: WIRE RANGE; #18-#34 AWG.
0.16-1.02 mm [.006-.040] DIA. COPPER MAGNET WIRE.
- 2
- POCKET RECOMMENDATION: 1601425 EXCEPT 7.61 [.300] HIGH,
ALTERNATE POCKET 1601431
- 3
- TERMINAL APPLICATION TO COMPLY WITH
TYCO ELECTRONICS SPEC 114-13166, CONSULT
TYCO ELECTRONICS PRODUCT ENGINEERING FOR PROPER
INSERTION DEPTH.
- 4
- POST PLATED TIN OVER COPPER
- 5
- 2 TERMINALS SHOWN FOR ILLUSTRATION PURPOSES.
- 6
- NON-STANDARD PACKAGING. REDUCED QUANTITY. REEL WITH
FLUTED PLASTIC FLANGES AND PAPER CORE. PAPER INTERLEAVING.
PLACED IN A PLASTIC BAG.
- 7
- NON-STANDARD PACKAGING. ALL PLASTIC REEL. PLASTIC INTERLEAVING.
PLACED IN A PLASTIC BAG.
- 8
- NON-STANDARD DOUBLE BAG.
- 9
- PRELIMINARY - NOT FOR PRODUCTION



8	9	4-1601264-2
7		1601264-4
6	9	1601264-3
STANDARD	9	1601264-2
PACKAGING		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR. RUTH 10MAR11	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK G. JACONO 10MAR11	NAME		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD G. JACONO 10MAR11	PRODUCT SPEC 108-2085 APPLICATION SPEC		
	0 PLC ± -				
	1 PLC ± -				
	2 PLC ± 0.13 [.005]				
	3 PLC ± -				
	4 PLC ± -				
MATERIAL FULL HARD BRASS		WEIGHT		RESTRICTED TO	
FINISH		A1 00779		1601264	
4		CUSTOMER DRAWING			
		SCALE		11:1	
		SHEET		1 OF 1	
		REV		A1	